

20A, 35V - 100V Isolated Schottky Barrier Rectifiers

FEATURES

- Low power loss, high efficiency
- Guard ring for over-voltage protection
- High surge current capability
- UL Recognized File # E-326243
- Compliant to RoHS Directive 2011/65/EU and in accordance to WEEE 2002/96/EC
- Halogen-free according to IEC 61249-2-21



MECHANICAL DATA

Case: ITO-220AC

Molding compound: UL flammability classification rating 94V-0

Part no. with suffix "H" means AEC-Q101 qualified

Packing code with suffix "G" means green compound (halogen-free)

Terminal: Matte tin plated leads, solderable per JESD22-B102


Meet JESD 201 class 2 whisker test

Polarity: As marked

Mounting torque: 0.56 Nm max.

Weight: 1.8 g (approximately)

ITO-220AC



MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS (T _A =25°C unless otherwise noted)								
PARAMETER	SYMBOL	MBRF 2035	MBRF 2045	MBRF 2050	MBRF 2060	MBRF 2090	MBRF 20100	UNIT
Maximum repetitive peak reverse voltage	V _{RRM}	35	45	50	60	90	100	V
Maximum RMS voltage	V _{RMS}	24	31	35	42	63	70	V
Maximum DC blocking voltage	V _{DC}	35	45	50	60	90	100	V
Maximum average forward rectified current	I _{F(AV)}	20						A
Peak repetitive forward current (Rated V _R , square wave, 20KHz)	I _{FRM}	40						A
Peak forward surge current, 8.3 ms single half sine-wave superimposed on rated load	I _{FSM}	150						A
Peak repetitive reverse surge current (Note 1)	I _{RRM}	1		0.5				A
Maximum instantaneous forward voltage (Note 2) I _F =20A, T _J =25°C I _F =20A, T _J =125°C	V _F	0.75		0.82		0.95		V
		0.65		0.72		0.87		
Maximum reverse current @ rated V _R T _J =25°C T _J =125°C	I _R	0.2				0.1		mA
		15		10		5		
Voltage rate of change (Rated V _R)	dV/dt	10000						V/μs
Typical thermal resistance	R _{θJC}	3						°C/W
Operating junction temperature range	T _J	- 55 to +150						°C
Storage temperature range	T _{STG}	- 55 to +150						°C

Note 1: tp = 2.0 μs, 1.0KHz

Note 2: Pulse test with PW=300μs, 1% duty cycle

ORDERING INFORMATION					
PART NO.	PART NO. SUFFIX	PACKING CODE	PACKING CODE SUFFIX (*)	PACKAGE	PACKING
MBRF20xx (Note 1)	H	C0	G	ITO-220AC	50 / Tube

Note 1: "xx" defines voltage from 35V (MBRF2035) to 100V (MBRF20100)

*: Optional available

EXAMPLE					
EXAMPLE P/N	PART NO.	PART NO. SUFFIX	PACKING CODE	PACKING CODE SUFFIX	DESCRIPTION
MBRF2060HC0G	MBRF2060	H	C0	G	AEC-Q101 qualified Green compound

RATINGS AND CHARACTERISTICS CURVES

(T_A=25°C unless otherwise noted)

FIG. 1 FORWARD CURRENT DERATING CURVE




FIG. 2 MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT PER LEG




FIG. 3 TYPICAL FORWARD CHARACTERISTICS PER LEG




FIG. 4 TYPICAL REVERSE CHARACTERISTICS PER LEG




FIG. 5 TYPICAL JUNCTION CAPACITANCE PER LEG






FIG. 6 TYPICAL TRANSIENT THERMAL IMPEDANCE PER LEG




PACKAGE OUTLINE DIMENSIONS
ITO-220AC



DIM.	Unit (mm)		Unit (inch)	
	Min	Max	Min	Max
A	4.30	4.70	0.169	0.185
B	2.50	3.10	0.098	0.122
C	2.30	2.90	0.091	0.114
D	0.46	0.76	0.018	0.030
E	6.30	6.90	0.248	0.272
F	9.60	10.30	0.378	0.406
G	3.00	3.40	0.118	0.134
H	0.00	1.60	0.000	0.063
I	0.95	1.45	0.037	0.057
J	0.50	0.90	0.020	0.035
K	2.40	3.20	0.094	0.126
L	14.80	15.50	0.583	0.610
M	-	4.10	-	0.161
N	-	1.80	-	0.071
O	12.60	13.80	0.496	0.543
P	4.95	5.20	0.195	0.205

MARKING DIAGRAM



- P/N = Specific Device Code
- G = Green Compound
- YWW = Date Code
- F = Factory Code

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Taiwan Semiconductor:

[MBRF20100 C0](#) [MBRF2035 C0](#) [MBRF2045 C0](#) [MBRF2050 C0](#) [MBRF2060 C0](#) [MBRF2090 C0](#) [MBRF2090HC0](#)
[MBRF2035HC0](#) [MBRF2050HC0](#) [MBRF2045HC0](#) [MBRF20100D C0](#) [MBRF20120D C0](#) [MBRF20150D C0](#)
[MBRF20200D C0](#) [MBRF2060D C0](#) [MBRF20100DHC0](#) [MBRF20100HC0](#) [MBRF20120DHC0](#) [MBRF20150DHC0](#)
[MBRF20200DHC0](#) [MBRF2060DHC0](#) [MBRF2060HC0](#)