

10A, 200V - 600V Super Fast Rectifier

FEATURES

- AEC-Q101 qualified available
- High efficiency
- High current capability
- High reliability
- High surge current capability
- Low power loss
- UL Recognized File # E-326243
- RoHS Compliant
- Halogen-free according to IEC 61249-2-21

KEY PARAMETERS		
PARAMETER	VALUE	UNIT
I_F	10	A
V_{RRM}	200 - 600	V
I_{FSM}	80, 125	A
$T_J \text{ MAX}$	150	°C
Package	ITO-220AB	
Configuration	Dual dies	


APPLICATIONS

- DC to DC converter
- Switching mode converters and inverters
- Freewheeling application



MECHANICAL DATA

- Case: ITO-220AB
- Molding compound meets UL 94V-0 flammability rating
- Terminal: Matte tin plated leads, solderable per J-STD-002
- Mounting torque: 0.56 N·m maximum
- Meet JESD 201 class 2 whisker test
- Polarity: As marked
- Weight: 1.77g (approximately)



ITO-220AB



ABSOLUTE MAXIMUM RATINGS ($T_A = 25^\circ\text{C}$ unless otherwise noted)

PARAMETER	SYMBOL	SFF 10L04G	SFF 10L05G	SFF 10L06G	SFF 10L08G	UNIT
Marking code on the device		SFF 10L04G	SFF 10L05G	SFF 10L06G	SFF 10L08G	
Repetitive peak reverse voltage	V _{RRM}	200	300	400	600	V
Reverse voltage, total rms value	V _{R(RMS)}	140	210	280	420	V
Forward current	I _F	10				A
Surge peak forward current, 8.3ms single half sine wave superimposed on rated load	I _{FSM}	125	80			A
Junction temperature	T _J	-55 to +150				°C
Storage temperature	T _{STG}	-55 to +150				°C

THERMAL PERFORMANCE

PARAMETER	SYMBOL	TYP	UNIT
Junction-to-lead thermal resistance	$R_{\theta JL}$	2	°C/W
Junction-to-ambient thermal resistance	$R_{\theta JA}$	9	°C/W
Junction-to-case thermal resistance	$R_{\theta JC}$	3	°C/W

Thermal Performance Note: Units mounted on heat sink with 2"x3"x0.25" Al -plate

ELECTRICAL SPECIFICATIONS ($T_A = 25^\circ\text{C}$ unless otherwise noted)

PARAMETER		CONDITIONS	SYMBOL	TYP	MAX	UNIT
Forward voltage per diode ⁽¹⁾	SFF10L04G	I _F = 5A, T _J = 25°C	V _F	0.94	0.98	V
	SFF10L05G			1.04	1.30	V
	SFF10L06G			1.05	1.30	V
	SFF10L08G			1.21	1.70	V
	SFF10L04G	I _F = 5A, T _J = 125°C		0.82	0.90	V
	SFF10L05G			0.89	0.96	V
	SFF10L06G			0.92	1.00	V
	SFF10L08G			1.04	1.20	V
Reverse current @ rated V _R per diode ⁽²⁾		T _J = 25°C	I _R	-	10	μA
		T _J = 125°C		-	400	μA
Junction capacitance per diode	SFF10L04G	1MHz, V _R = 4.0V	C _J	60	-	pF
	SFF10L05G			50	-	pF
	SFF10L06G					
	SFF10L08G					
Reverse recovery time		I _F = 0.5A , I _R = 1.0A I _{rr} = 0.25A	t _{rr}	-	35	ns

Notes:

1. Pulse test with $PW = 0.3\text{ms}$
2. Pulse test with $PW = 30\text{ms}$

ORDERING INFORMATION

ORDERING CODE ⁽¹⁾⁽²⁾	PACKAGE	PACKING
SFF10LxG	ITO-220AB	50 / Tube
SFF10LxGH	ITO-220AB	50 / Tube

Notes:

1. "x" defines voltage from 200V(SFF10L04G) to 600V(SFF10L08G)
2. "H" means AEC-Q101 qualified

CHARACTERISTICS CURVES

($T_A = 25^\circ\text{C}$ unless otherwise noted)

Fig.1 Forward Current Derating Curve




Fig.2 Typical Junction Capacitance




Fig.3 Typical Reverse Characteristics




Fig.4 Typical Forward Characteristics




Fig.5 Typical Reverse Characteristics





Fig.6 Typical Forward Characteristics



CHARACTERISTICS CURVES

($T_A = 25^\circ\text{C}$ unless otherwise noted)

Fig.7 Typical Reverse Characteristics




Fig.8 Typical Forward Characteristics




Fig.9 Typical Reverse Characteristics






Fig.10 Typical Forward Characteristics



PACKAGE OUTLINE DIMENSIONS



DIM.	Unit (mm)		Unit (inch)	
	Min.	Max.	Min.	Max.
A	4.30	4.70	0.169	0.185
A2	2.30	2.96	0.091	0.117
b	0.50	0.90	0.020	0.035
b1	-	1.80	-	0.071
b2	0.95	1.45	0.037	0.057
c	0.46	0.76	0.018	0.030
c2	2.50	3.16	0.098	0.124
D	14.80	15.50	0.583	0.610
D1	2.40	3.20	0.094	0.126
D2	6.30	6.90	0.248	0.272
E	9.60	10.30	0.378	0.406
e	2.41	2.67	0.095	0.105
L	12.60	13.80	0.496	0.543
L4	-	4.10	-	0.161
P	3.00	3.40	0.118	0.134

MARKING DIAGRAM



P/N = Marking Code
 G = Green Compound
 YWW = Date Code
 F = Factory Code

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf assumes no responsibility or liability for any errors or inaccuracies.

Purchasers are solely responsible for the choice, selection, and use of TSC products and TSC assumes no liability for application assistance or the design of Purchasers' products.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Taiwan Semiconductor:](#)

[SFF10L04G](#) [SFF10L05G](#) [SFF10L06G](#) [SFF10L08G](#) [SFF10L04GH](#) [SFF10L05GH](#) [SFF10L06GH](#) [SFF10L08GH](#)