

Schottky Barrier Rectifier

FEATURES

- Low power loss, high efficiency
- Guardring for overvoltage protection
- High surge current capability
- Compliant to RoHS Directive 2011/65/EU and in accordance to WEEE 2002/96/EC
- Halogen-free according to IEC 61249-2-21 definition

MECHANICAL DATA

Case: TO-220AC

Molding compound, UL flammability classification rating 94V-0

Base P/N with suffix "G" on packing code - halogen-free

Base P/N with prefix "H" on packing code - AEC-Q101 qualified

Terminal: Matte tin plated leads, solderable per JESD22-B102

Meet JESD 201 class 1A whisker test,

with prefix "H" on packing code meet JESD 201 class 2 whisker test


Polarity: As marked

Mounting torque: 5 in-lbs maximum

Weight: 1.9g (approximately)



TO-220AC



MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS (T _A =25°C unless otherwise noted)										
PARAMETER	SYMBOL	SRA 2020	SRA 2030	SRA 2040	SRA 2050	SRA 2060	SRA 2090	SRA 20100	SRA 20150	UNIT
Maximum repetitive peak reverse voltage	V _{RRM}	20	30	40	50	60	90	100	150	V
Maximum RMS voltage	V _{RMS}	14	21	28	35	42	63	70	105	V
Maximum DC blocking voltage	V _{DC}	20	30	40	50	60	90	100	150	V
Maximum average forward rectified current	I _{F(AV)}	20								A
Peak forward surge current, 8.3 ms single half sine-wave superimposed on rated load	I _{FSM}	300								A
Maximum instantaneous forward voltage (Note 2) I _F = 20 A	V _F	0.55			0.70		0.92		1.02	V
Maximum reverse current @ rated VR T _J =25 °C T _J =100 °C T _J =125°C	I _R	0.5					0.1			mA
		15			10		-			
		-					5.0			
Typical thermal resistance	R _{θJC}	1.5								°C/W
Operating junction temperature range	T _J	- 55 to +125				- 55 to +150				°C
Operating junction temperature range - In DC forward mode	T _J	≤ 200								°C
Storage temperature range	T _{STG}	- 55 to +150								°C

Note 1 : Pulse test with PW=300μs, 1% duty cycle

ORDERING INFORMATION					
PART NO.	AEC-Q101 QUALIFIED	PACKING CODE	GREEN COMPOUND CODE	PACKAGE	PACKING
SRA20xx (Note 1)	Prefix "H"	C0	Suffix "G"	TO-220AC	50 / Tube

Note 1: "xx" defines voltage from 20V (SRA2020) to 150V (SRA20150)

EXAMPLE					
PREFERRED P/N	PART NO.	AEC-Q101 QUALIFIED	PACKING CODE	GREEN COMPOUND CODE	DESCRIPTION
SRA2060 C0	SRA2060		C0		
SRA2060 C0G	SRA2060		C0	G	Green compound
SRA2060HC0	SRA2060	H	C0		AEC-Q101 qualified

RATINGS AND CHARACTERISTICS CURVES

(TA=25°C unless otherwise noted)

FIG.1 FORWARD CURRENT DERATING CURVE




FIG. 2 MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT




FIG. 3 TYPICAL FORWARD CHARACTERISTICS




FIG. 4 TYPICAL REVERSE CHARACTERISTICS




FIG. 5 TYPICAL JUNCTION CAPACITANCE






FIG. 6 TYPICAL TRANSIENT THERMAL IMPEDANCE




PACKAGE OUTLINE DIMENSIONS



DIM.	Unit (mm)		Unit (inch)	
	Min	Max	Min	Max
A	-	10.50	-	0.413
B	2.62	3.44	0.103	0.135
C	2.80	4.20	0.110	0.165
D	0.68	0.94	0.027	0.037
E	3.54	4.00	0.139	0.157
F	14.60	16.00	0.575	0.630
G	0.00	1.60	0.000	0.063
H	13.19	14.79	0.519	0.582
I	4.95	5.20	0.195	0.205
J	4.42	4.76	0.174	0.187
K	1.14	1.40	0.045	0.055
L	5.84	6.86	0.230	0.270
M	2.20	2.80	0.087	0.110
N	0.35	0.64	0.014	0.025

MARKING DIAGRAM



Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Taiwan Semiconductor:

[SRA20100](#) [SRA20150](#) [SRA2020](#) [SRA2030](#) [SRA2040](#) [SRA2050](#) [SRA2060](#) [SRA2090](#) [SRA2090HC0](#)
[SRA2060HC0](#) [SRA2040HC0](#) [SRA2020HC0](#) [SRA2030HC0](#) [SRA20150HC0](#) [SRA20100HC0](#) [SRA2050HC0](#)
[SRA20100 C0](#) [SRA2060 C0](#) [SRA2050 C0](#) [SRA2090 C0](#) [SRA20150 C0](#) [SRA2040 C0](#) [SRA2030 C0](#) [SRA2020 C0](#)