

2A, 20V - 150V Surface Mount Schottky Barrier Rectifiers

FEATURES

- Low power loss, high efficiency
- Ideal for automated placement
- Guardring for overvoltage protection
- High surge current capability
- Compliant to RoHS Directive 2011/65/EU and in accordance to WEEE 2002/96/EC
- Halogen-free according to IEC 61249-2-21 definition



Sub SMA

MECHANICAL DATA

Case: Sub SMA

Molding compound, UL flammability classification rating 94V-0

Moisture sensitivity level: level 1, per J-STD-020

Part no. with suffix "H" means AEC-Q101 qualified

Packing code with suffix "G" means green compound (halogen-free)

Terminal: Matte tin plated leads, solderable per JESD22-B102

Meet JESD 201 class 2 whisker test

Polarity: Indicated by cathode band

Weight: 0.019 g (approximately)

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS (T _A =25°C unless otherwise noted)										
PARAMETER	SYMBOL	SS 22L	SS 23L	SS 24L	SS 25L	SS 26L	SS 29L	SS 210L	SS 215L	UNIT
Marking code		22L	23L	24L	25L	26L	29L	20L	2AL	
Maximum repetitive peak reverse voltage	V _{RRM}	20	30	40	50	60	90	100	150	V
Maximum RMS voltage	V _{RMS}	14	21	28	35	42	63	70	105	V
Maximum DC blocking voltage	V _{DC}	20	30	40	50	60	90	100	150	V
Maximum average forward rectified current	I _{F(AV)}	2								A
Peak forward surge current, 8.3 ms single half sine-wave superimposed on rated load	I _{FSM}	50								A
Maximum instantaneous forward voltage (Note 1) @ 2A	V _F	0.50			0.70		0.85		0.95	V
Maximum reverse current @ rated V _R T _J =25°C T _J =100°C T _J =125°C	I _R	0.4					0.1			mA
		15			10		-			
		-			-		5			
Voltage rate of change (Rated V _R)	dV/dt	10000								V/μs
Typical thermal resistance	R _{θJL}	17								°C/W
	R _{θJA}	75								
Operating junction temperature range	T _J	- 55 to +125			- 55 to +150					°C
Storage temperature range	T _{STG}	- 55 to +150								°C

Note 1: Pulse test with PW=300μs, 1% duty cycle

ORDERING INFORMATION					
PART NO.	PART NO. SUFFIX	PACKING CODE	PACKING CODE SUFFIX	PACKAGE	PACKING
SS2XL (Note 1)	H	RU	G	Sub SMA	1,800 / 7" Plastic reel (8mm tape)
		RV		Sub SMA	3,000 / 7" Plastic reel (8mm tape)
		RT		Sub SMA	7,500 / 13" Paper reel (8mm tape)
		MT		Sub SMA	7,500 / 13" Plastic reel (8mm tape)
		RQ		Sub SMA	10,000 / 13" Paper reel (8mm tape)
		MQ		Sub SMA	10,000 / 13" Plastic reel (8mm tape)
		R3		Sub SMA	1,800 / 7" Plastic reel (12mm tape)
		RF		Sub SMA	3,000 / 7" Plastic reel (12mm tape)
		R2		Sub SMA	7,500 / 13" Paper reel (12mm tape)
		M2		Sub SMA	7,500 / 13" Plastic reel (12mm tape)
		RH		Sub SMA	10,000 / 13" Paper reel (12mm tape)
		MH		Sub SMA	10,000 / 13" Plastic reel (12mm tape)

Note 1: "x" defines voltage from 20V (SS22L) to 150V (SS215L)

EXAMPLE					
PREFERRED PART NO.	PART NO.	PART NO. SUFFIX	PACKING CODE	PACKING CODE SUFFIX	DESCRIPTION
SS26LHRUG	SS26L	H	RU	G	AEC-Q101 qualified Green compound

RATINGS AND CHARACTERISTICS CURVES (T_A=25°C unless otherwise noted)

FIG.1 FORWARD CURRENT DERATING CURVE




FIG. 2 MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT




FIG. 3 TYPICAL FORWARD CHARACTERISTICS




FIG. 4 TYPICAL REVERSE CHARACTERISTICS




FIG. 5 TYPICAL JUNCTION CAPACITANCE






FIG. 6 TYPICAL TRANSIENT THERMAL IMPEDANCE




PACKAGE OUTLINE DIMENSIONS

Sub SMA



DIM.	Unit (mm)		Unit (inch)	
	Min	Max	Min	Max
B	1.70	1.90	0.067	0.075
C	2.70	2.90	0.106	0.114
D	0.16	0.30	0.006	0.012
E	1.23	1.43	0.048	0.056
F	0.80	1.20	0.031	0.047
G	3.40	3.80	0.134	0.150
H	2.45	2.60	0.096	0.102
I	0.35	0.85	0.014	0.033
J	0.00	0.10	0.000	0.004

SUGGESTED PAD LAYOUT



Symbol	Unit (mm)	Unit (inch)
A	1.4	0.055
B	1.2	0.047
C	3.1	0.122
D	1.9	0.075
E	4.3	0.169

MARKING DIAGRAM



- P/N = Marking Code
 G = Green Compound
 YW = Date Code
 F = Factory Code

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Taiwan Semiconductor:

[SS210L](#) [SS215L](#) [SS22L](#) [SS23L](#) [SS24L](#) [SS25L](#) [SS26L](#) [SS29L](#) [SS210L R2](#) [SS24L R2](#) [SS26L R3G](#) [SS26L RQG](#)
[SS29LHR3G](#) [SS23LHR3G](#) [SS29L R2G](#) [SS23LHR3](#) [SS26L RQ](#) [SS23L R3](#) [SS210L RQG](#) [SS23LHRQ](#)
[SS25LHR3G](#) [SS29LHR3](#) [SS22L RQG](#) [SS24L R3](#) [SS26LHR2G](#) [SS210LHR2G](#) [SS215LHR3G](#) [SS29LHRQ](#) [SS23L](#)
[R3G](#) [SS22L R2G](#) [SS24LHR3G](#) [SS23L R2G](#) [SS210LHR3G](#) [SS24LHR2](#) [SS26LHR3G](#) [SS215L R3](#) [SS29LHR2](#)
[SS26LHRQG](#) [SS22L R3G](#) [SS25LHRQ](#) [SS210LHR2](#) [SS215LHR2](#) [SS23L R2](#) [SS24LHRQ](#) [SS22LHR3G](#) [SS22L R2](#)
[SS29L R2](#) [SS215LHR3](#) [SS29LHR2G](#) [SS215L R2G](#) [SS215LHR2G](#) [SS210LHR3](#) [SS23LHRQG](#) [SS26LHR3](#) [SS26L](#)
[R2G](#) [SS210L R2G](#) [SS215L R3G](#) [SS25LHRQG](#) [SS29L RQG](#) [SS215L R2](#) [SS25L R2](#) [SS23LHR2G](#) [SS26L R2](#)
[SS29LHRQG](#) [SS24L R3G](#) [SS23L RQ](#) [SS26LHR2](#) [SS24LHRQG](#) [SS210LHRQG](#) [SS22LHRQG](#) [SS29L R3](#)
[SS25LHR2G](#) [SS215LHRQG](#) [SS25LHR2](#) [SS29L R3G](#) [SS24LHR2G](#) [SS215L RQG](#) [SS25L R2G](#) [SS215LHRQ](#)
[SS25L RQG](#) [SS24L R2G](#) [SS22L R3](#) [SS24L RQG](#) [SS25L R3G](#) [SS210L R3G](#) [SS25LHR3](#) [SS23LHR2](#) [SS22LHR2G](#)
[SS24LHR3](#) [SS23L RQG](#) [SS26L R3](#) [SS210L R3](#) [SS26LHRVG](#) [SS29L RVG](#) [SS25L RVG](#) [SS26L RVG](#)
[SS26LHRUG](#) [SS22L RVG](#) [SS23L RVG](#) [SS23LHRUG](#)