

Mobile Printer

DPU-S Series



Measuring Instrument



PDA/Smart Device



Barcode



Portable Printer



Label



Medical Equipment

- Max printing speed: 100mm/sec (DPU-S245)
90mm/sec (DPU-S445)
- Interface: Bluetooth®, USB, Serial
- Compact and light-weight
- Easy paper operation
- Wide variety of driver and utility software suite

DPU-S445



DPU-S245



Made for



iPod iPhone iPad

Model	DPU-S245	DPU-S445
Printing	Method	Thermal line dot printing
	Number of dots/line	384
	Resolution (dots/mm)	8
	Paper width (mm)	58 ⁺⁰ ₋₁
	Printing width (mm)	48
	Speed (mm/sec) max	100
	Outside diameter of paper roll (mm) max	φ 38
	Character matrix (H×W dots)	24 × 12, 24 × 24, 16 × 8, 16 × 16
	Character dimensions (H×W mm)	3.0 × 1.5, 3.0 × 3.0, 2.0 × 1.0, 2.0 × 2.0
	Number of columns	24, 12, 32, 16
Type of Paper	Roll paper, Label roll paper	Roll paper, Label roll paper, Cut sheet paper
Character type	Extended graphics character set, Katakana character set, CP1252, Optional font, Downloaded character, User-defined character, JIS 1 & 2 level kanji	
Bar code	UPC-A/E, JAN (EAN) 8/13, ITF, CODE39, CODABAR, CODE128, PDF417, QR Code, MaxiCode, Data Matrix	
Power supply (V)	Li-Ion battery, Specified AC adapter	
Communication interface	Bluetooth®*1, USB, Serial	
Input buffer	4K bytes	
Command	ESC/P™ conformity	
Cutting	Tear bar	
Operating temperature (°C)	-10 to 50	0 to 50
Service life (km)	50*2	
Dimensions (W×D×H mm)	83 × 130 × 45*3	145.0 × 135.0 × 58.0*3
Mass (g)	Approx. 280*4	Approx. 490*4
Standard	FCC, CE, VCCI, CCC*5	
Option	AC adapter, Battery pack, Battery charger, AC cable, USB cable, Serial cable, Carrying case	
Software*6	Printer driver, Windows® CE (SDK), Android™ (SDK), iOS (SDK)	

*1 Only Bluetooth® model. *2 Use recommended thermal papers. *3 Excluding protrusion. *4 Including battery, excluding roll paper. *5 DPU-Sx45-00B-E model only. *6 Please see official homepage "www.sii-ps.com" for details.

Serial interface specification

Item	Specification
Baud rate	1200, 2400, 4800, 9600, 19200, 38400, 57600, 115200 bps
Data bit	7bits, 8bits
Parity bit	Odd, Even, or None
Stop bit	1bit, 2bits
Control method	H/W BUSY, Xon/Xoff

USB interface specification

USB printer-class 2.0 conformity

Bluetooth® interface specification

Based on Bluetooth® Ver. 2.1 + EDR

Easy paper operation



Cut sheet paper



SII

Seiko Instruments GmbH
Siemensstraße 9
D-63263 Neu-Isenburg, Germany
Phone +49 6102 297 0
info@seiko-instruments.de
www.seiko-instruments.de



SEIKO
SEIKO HOLDINGS GROUP

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Seiko Instruments:

[DPU-S445-00A-E](#) [DPU-S445-01A-E](#) [DPU-S245-00A-E](#) [DPU-S245-01A-E](#) [DPU-S445-00B-E](#) [DPU-S445-00C-E](#)