


SERPAC 1914AA

ELECTRONIC ENCLOSURES







PART NO.	DESCRIPTION (Included)	PART NO.	DESCRIPTION
9-1	Top	50	Non-Skid Feet
194AA	4AA Bottom	60	Standoff Hole
6005	#4X3/8" Self-Tapping Screw (8)	61	Standoff Post
1026	Access Door	SK9	Waterproof Seal Kit
73	Double Battery Contact (3)		
72	Single Battery Contact (2)		

Notes: Enclosure weight .66 lb / 299 g
1) Enclosure meets or exceeds IP40 and NEMA 1
2) Circuit Board drawings see sheet 3.
3) All components are RoHS Compliant.
4) Material: Top and Bottom ABS.
5) When used with SK9 the enclosure meets or exceeds IP 67 and NEMA 4X, 12 and 13 MIL-STD-810G 506.5 (.04 lb / 19g)

SERPAC 1914AA

ELECTRONIC ENCLOSURES



Notes:


- 1) Enclosure meets or exceeds IP40 and NEMA 1
- 2) Circuit Board drawings see sheet 3.
- 3) All components are RoHS Compliant.
- 4) Material: Top and Bottom ABS.

5) Customizable molding areas. $\triangle 5$

6) PCB Bosses accept #4 self tapping screw. $\triangle 6$

7) When used with SK9 the enclosure meets or exceeds

IP 67 and NEMA 4X, 12 and 13 MIL-STD-810G 506.5 (.04 lb / 19g)



SECTION A-A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[SERPAC:](#)

[1914AAAL](#) [1914AABK](#) [1914AAGY](#) [1914AA,AL](#) [1914AA,BK](#) [1914AA,GY](#)