

Trench Schottky Rectifier


FEATURES

- Patented Trench Schottky technology
- Excellent high temperature stability
- Low forward voltage
- Low power loss/ High efficiency
- High forward surge capability
- Compliant to RoHS directive 2011/65/EU and in accordance to WEEE 2002/96/EC
- Halogen-free according to IEC 61249-2-21 definition


ITO-220AB


TYPICAL APPLICATIONS

Trench Schottky barrier rectifier are designed for high frequency miniature switched mode power supplies such as adapters, lighting and on-board DC/DC converters.



MECHANICAL DATA

Case: ITO-220AB

Molding compound meets UL 94 V-0 flammability rating

Packing code with suffix "G" means green compound (halogen-free)

Terminal: Matte tin plated leads, solderable per JESD22-B102

Meet JESD 201 class 2 whisker test

Polarity: As marked

Mounting torque: 0.56 Nm max.

Weight: 1.7 g (approximately)

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS (T _A =25°C unless otherwise noted)													
PARAMETER				SYMBOL	TSF30H 100C		TSF30H 120C		TSF30H 150C		TSF30H 200C		UNIT
Maximum repetitive peak reverse voltage				V _{RRM}	100		120		150		200		V
Maximum average forward rectified current		per device		I _{F(AV)}	30								A
		per diode			15								
Peak forward surge current, 8.3 ms single half sine-wave superimposed on rated load per diode				I _{FSM}	150								A
Voltage rate of change (Rated V _R)				dV/dt	10000								V/μs
Isolation voltage from terminal to heatsink t = 1 min				V _{AC}	1500								V
					Typ	Max	Typ	Max	Typ	Max	Typ	Max	
Instantaneous forward voltage per diode (Note1)		I _F = 15A	T _J = 25°C	V _F	0.76	0.82	0.80	0.88	0.81	0.90	0.84	0.92	V
			T _J = 125°C		0.64	0.69	0.65	0.73	0.68	0.77	0.70	0.79	
		I _F = 30A	T _J = 25°C		0.86	0.92	0.90	0.96	0.89	0.98	0.91	1.00	
			T _J = 125°C		0.75	0.80	0.78	0.86	0.77	0.86	0.80	0.89	
Instantaneous reverse current per diode at rated reverse voltage			T _J = 25°C	I _R	150								μA
			T _J = 125°C		20								mA
Typical thermal resistance				R _{θJC}	4.5								°C/W
Operating junction temperature range				T _J	- 55 to +150								°C
Storage temperature range				T _{STG}	- 55 to +150								°C

Note 1: Pulse test with pulse width=300μs, 1% duty cycle

ORDERING INFORMATION				
PART NO.	PACKING CODE	PACKING CODE SUFFIX	PACKAGE	PACKING
TSF30HXXXC (Note 1)	C0	G	ITO-220AB	50 / Tube

Note 1: "xxx" defines voltage from 100V (TSF30H100C) to 200V (TSF30H200C)

EXAMPLE				
PREFERRED PART NO.	PART NO.	PACKING CODE	PACKING CODE SUFFIX	DESCRIPTION
TSF30H120C C0G	TSF30H120C	C0	G	Green compound

RATINGS AND CHARACTERISTICS CURVES

(T_A=25°C unless otherwise noted)

FIG.1 FORWARD CURRENT DERATING CURVE




FIG. 2 TYPICAL FORWARD CHARACTERISTICS




FIG. 3 TYPICAL REVERSE CHARACTERISTICS




FIG. 4 TYPICAL FORWARD CHARACTERISTICS




FIG. 5 TYPICAL FORWARD CHARACTERISTICS




FIG. 6 TYPICAL REVERSE CHARACTERISTICS




FIG. 7 TYPICAL REVERSE CHARACTERISTICS




FIG. 8 TYPICAL REVERSE CHARACTERISTICS




FIG. 9 TYPICAL REVERSE CHARACTERISTICS






FIG. 10 TYPICAL JUNCTION CAPACITANCE




PACKAGE OUTLINE DIMENSIONS

ITO-220AB



DIM.	Unit (mm)		Unit (inch)	
	Min	Max	Min	Max
A	4.30	4.70	0.169	0.185
B	2.50	3.16	0.098	0.124
C	2.30	2.96	0.091	0.117
D	0.46	0.76	0.018	0.030
E	6.30	6.90	0.248	0.272
F	9.60	10.30	0.378	0.406
G	3.00	3.40	0.118	0.134
H	0.95	1.45	0.037	0.057
I	0.50	0.90	0.020	0.035
J	2.40	3.20	0.094	0.126
K	14.80	15.50	0.583	0.610
L	-	4.10	-	0.161
M	12.60	13.80	0.496	0.543
N	-	1.80	-	0.071
O	2.41	2.67	0.095	0.105

MARKING DIAGRAM



P/N = Specific Device Code
G = Green Compound
YWW = Date Code
F = Factory Code

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Taiwan Semiconductor:](#)

[TSF30H150CM C0G](#) [TSF30H200CM C0G](#) [TSF30H100CM C0G](#)