



## 30A, 45V - 60V Trench Schottky Rectifiers

### FEATURES

- Patented Trench Schottky technology
- Excellent high temperature stability
- Low forward voltage
- Low power loss/ High efficiency
- High forward surge capability
- Compliant to RoHS directive 2011/65/EU and in accordance to WEEE 2002/96/EC
- Halogen-free according to IEC 61249-2-21 definition



### TO-220AB



### TYPICAL APPLICATIONS

Trench Schottky barrier rectifier is designed for high frequency miniature switched mode power supplies such as adapters, lighting and on-board DC/DC converters.

### MECHANICAL DATA

**Case:** TO-220AB

Molding compound meets UL 94 V-0 flammability rating

Packing code with suffix "G" means green compound (halogen-free)

**Terminal:** Matte tin plated leads, solderable per JESD22-B102

Meet JESD 201 class 1A whisker test

**Polarity:** As marked

**Mounting torque:** 0.56 Nm max.

**Weight:** 1.88 g (approximately)

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS (T <sub>A</sub> = 25°C unless otherwise noted)								
PARAMETER			SYMBOL	TST30U45C		TST30U60C		UNIT
Maximum repetitive peak reverse voltage			V <sub>RRM</sub>	45		60		V
Maximum average forward rectified current	per device		I <sub>F(AV)</sub>	30				A
	per diode			15				
Peak forward surge current, 8.3 ms single half sine-wave superimposed on rated load per diode			I <sub>FSM</sub>	250				A
Voltage rate of change (Rated V <sub>R</sub> )			dV/dt	10000				V/μs
				TYP.	MAX.	TYP.	MAX.	
Instantaneous forward voltage per diode ( Note1 )	I <sub>F</sub> = 15A	T <sub>J</sub> = 25°C	V <sub>F</sub>	0.45	0.54	0.48	0.57	V
	I <sub>F</sub> = 15A	T <sub>J</sub> = 125°C		0.40	0.49	0.43	0.52	
Maximum instantaneous reverse current per diode at rated reverse voltage		T <sub>J</sub> = 25°C	I <sub>R</sub>	500				μA
		T <sub>J</sub> = 125°C		60				mA
Typical thermal resistance per diode			R <sub>θJC</sub>	4				°C/W
Operating junction temperature range			T <sub>J</sub>	- 55 to +150				°C
Storage temperature range			T <sub>STG</sub>	- 55 to +150				°C

Note 1: Pulse test with pulse width = 300μs, 1% duty cycle

**ORDERING INFORMATION**

PART NO.	PACKING CODE	PACKING CODE SUFFIX	PACKAGE	PACKING
TST30UXXC	C0	G	TO-220AB	50 / Tube





Note 1: "XX" defines voltage from 45V (TST30U45C) to 60V (TST30U60C)

**EXAMPLE**


PREFERRED PART NO.	PART NO.	PACKING CODE	PACKING CODE SUFFIX	DESCRIPTION
TST30U45C C0G	TST30U45C	C0	G	Green compound

**RATINGS AND CHARACTERISTICS CURVES**


( $T_A = 25^\circ\text{C}$  unless otherwise noted)

**FIG.1 FORWARD CURRENT DERATING CURVE**

**FIG.2 TYPICAL FORWARD CHARACTERISTICS**

**FIG.3 TYPICAL FORWARD CHARACTERISTICS**

**FIG.4 TYPICAL REVERSE CHARACTERISTICS**



**FIG.5 TYPICAL REVERSE CHARACTERISTICS**




**FIG.6 TYPICAL JUNCTION CAPACITANCE**



**FIG. 5 MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT**



PACKAGE OUTLINE DIMENSIONS  
**TO-220AB**



DIM.	Unit (mm)		Unit (inch)	
	Min	Max	Min	Max
A	9.60	10.50	0.378	0.413
B	2.62	3.44	0.103	0.135
C	2.80	4.20	0.110	0.165
D	0.68	0.94	0.027	0.037
E	3.54	4.00	0.139	0.157
F	14.60	16.00	0.575	0.630
G	13.19	14.79	0.519	0.582
H	2.41	2.67	0.095	0.105
I	4.42	4.76	0.174	0.187
J	1.14	1.40	0.045	0.055
K	5.84	6.86	0.230	0.270
L	2.20	2.80	0.087	0.110
M	0.35	0.64	0.014	0.025

MARKING DIAGRAM



P/N = Specific Device Code  
G =Green Compound  
YWW = Date Code  
F = Factory Code

### Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Taiwan Semiconductor:

[TST30U45C C0G](#) [TST30U60C C0G](#) [TST30U45C](#) [TST30U60C](#)