

ThingMagic M2



66mm L x 36mm W x 5mm H

Features & Benefits:

- Fast integration and time-to-market
- Unparalleled investment protection
- Cost-effective and highly scalable
- Miniscule footprint
- Peripheral devices for encryption algorithms and key storage
- Common Blade technology for maximum design and solution flexibility
- Greatest tag compatibility, with TagIQ
- Minimal power consumption and maximum read range
- Software Adjustable Host Interfaces: UART (TTL), SPI, USB, I²C
- 7 General Purpose I/O Pins
- Simple and intuitive API

Multi-Protocol, Secure HF RFID Reader

ThingMagic M2 combines High Frequency (HF) tag and protocol support and outstanding performance in an embedded reader/writer module. With industry-leading privacy protection and anti-counterfeiting/anti-tampering technology, the M2 includes standards-based security that is used in the defense and financial services industries. M2 can read and write to transponders based on the ISO14443 (parts 2, 3, and 4) and ISO15693 air interface and communications standards. It also supports standard encryption algorithms (DES, 3DES, and AES), secure functions (SHA and MD5), and an internal Pseudo-Random Number Generator (PRNG).

ThingMagic M2 is performance-optimized for best-in-class output power (200mW), noise reduction, and power management. M2 uses advanced Universal Reader Architecture and SkyeAPI to abstract frequency, protocol, and tag selection and automate functions from the application. With advanced tag technology, it recognizes unique characteristics of each tag to maximize read/write performance.

Its small size enables this module to fit into almost any new or existing Original Equipment Manufacturer (OEM) design.

Applications

- Product Authentication and Anti-Counterfeiting
- Handheld Reading/Encoding
- Inventory Management, Item Level Tagging
- Consumables
- Patron Management
- Asset Tracking
- Label Printing/Encoding

ThingMagic M2

Ordering Information			
Module-CF	SM-M2-CF		
Module-MH	SM-M2-MH		
M2 Evaluation Kit	EV-M2-00		
Physical			
Dimensions	CF: 66mm length, 36mm width, 5mm height; MH: 70mm length, 53mm width, 9mm height		
Weight	CF: 8.7 grams; MH: 10.5 grams		
Frequency	13.56 MHz +/- 7 kHz		
Air Interface	Manufacturer	Product Family	Tags
ISO 15693	NXP TagSys ST Micro Infineon Fujitsu Texas Instruments EM Micro	ICODE 370 Series Long Range Vicinity FerVID Tag-It EM Series	SLIX-/S/L, SLI-/S/L 370L-/HL/DL, 370S-DM LRI/1k/2k, LRIS/2k/64k SRF55V/01P/02P/10P/02S/10S MB89R11/9B/8C Standard, Pro, Plus EM4/033/133/233
ISO 14443A	NXP Verayo	MIFARE Vera	Classic/1k/4k, Ultralight/C, DESFire EV1 M1, M4
ISO 14443B	ST Micro	Short Range	SRI/2k/4k/512, SRIX4k, SRT512
Antenna			
Options	Internal or 50Ω MMCX (female) output for external connection		
External Range Vicinity	16 cm		
External Range Proximity	8 cm		
Data/Control Interface			
Peripheral I/O Connection	7 programmable GPIO pins, ISO 7816 smart card slot (optional)		
Power Consumption			
Sleep Mode:	4 mA		
Idle Mode:	75 mA		
Scan Mode:	175 mA		
Host Interface, Data Rates			
UART (TTL):	9.6-115.2 kbps		
SPI:	Mode 1 up to 4 Mb/s		
USB:	2.0 Full Speed 12 Mb/s		
I ² C:	100/400 kHz		
Transponder			
Communication Rate	ISO 14443A: 106 kbps ISO 14443B: 106 kbps ISO 15693: 26 kbps		
Air Interface Protocols			
	ISO 14443 A/B (parts 2-4) ISO 15693		
Compliance			
FCC Part 15.225 EN 300-330, EN301-489, EN 61000-4-3, RoHS AS/NZS 4268:2003 DGT LP002 HKTA 1035 IDA TS SRD ETSI EN 300-330 (RED 2014/53/EU)			
Temperature			
Operating Temp	-10°C to 70°C		
Storage Temp.	-20°C to 85°C		

ThingMagic M2

Software & Security

SkyeAPI C/.NET API

Skyeware 4

SkyeOS

SkyeSecurity Encryption DES,3DES, AES, MIFRARE and CryptoRF Support

SkyeSecurity Clone/Tamper Protection

Specifications subject to change without notice.

ABOUT JADAK:

JADAK, a business unit of Novanta, is a market leader in machine vision, RFID, barcode, printing, and color and light measurement products and services for original equipment manufacturers. The company designs and manufactures embedded detection and analysis solutions that help customers solve unique inspection, tracking, scanning and documenting. The company is ISO 9001 and ISO 13485 registered.

Novanta is a trusted technology partner to OEMs in the medical and advanced industrial technology markets, with deep proprietary expertise in photonics, vision and precision motion technologies.

ThingMagic is the JADAK line of RFID products.

www.jadaktech.com



JADAK
A Novanta Company

USA Office

phone: +1 315.701.0678
email: info@jadaktech.com
web: jadaktech.com

European Office

phone: +31 (0)76.522.5588
email: info@jadak.eu

Asia Pacific Office

phone: +86 512.6283.7080

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[SkyeTek:](#)

[SM-M2-CF-HF](#) [SM-M2-MH-HF](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[SkyeTek:](#)

[EV-M2-00](#)