




## SSL32 - SSL34

3.0AMPS Surface Mount Schottky Barrier Rectifiers  
**SMC/DO-214AB**



### Features

- ◊ For surface mounted application
- ◊ Metal to silicon rectifier, majority carrier conduction
- ◊ Low forward voltage drop
- ◊ Easy pick and place
- ◊ High surge current capability
- ◊ Plastic material used carriers Underwriters Laboratory Classification 94V-0
- ◊ Epitaxial construction
- ◊ High temperature soldering: 260°C/10 seconds at terminals
- ◊ Green compound with suffix "G" on packing code & prefix "G" on datecode

### Mechanical Data

- ◊ Case: Molded plastic
- ◊ Terminals: Matte tin plating
- ◊ Polarity: Indicated by cathode band
- ◊ Packaging: 16mm tape per EIA STD RS-481
- ◊ Weight: 0.21 grams

### Dimensions in inches and (millimeters)

#### Marking Diagram



SL3X = Specific Device Code  
 G = Green Compound  
 Y = Year  
 M = Work Month

### Maximum Ratings and Electrical Characteristics

Rating at 25 °C ambient temperature unless otherwise specified.

Single phase, half wave, 60 Hz, resistive or inductive load.

For capacitive load, derate current by 20%

Type Number	Symbol	SSL32	SSL33	SSL34	Unit
Maximum Repetitive Peak Reverse Voltage	$V_{RRM}$	20	30	40	V
Maximum RMS Voltage	$V_{RMS}$	14	21	28	V
Maximum DC Blocking Voltage	$V_{DC}$	20	30	40	V
Maximum Average Forward Rectified Current	$I_{F(AV)}$		3		A
Peak Forward Surge Current, 8.3 ms Single Half Sine-wave Superimposed on Rated Load	$I_{FSM}$		100		A
Maximum Instantaneous Forward Voltage (Note 1) @ 3 A	$V_F$		0.41		V
Maximum Reverse Current @ Rated VR $T_A=25\text{ }^\circ\text{C}$ $T_A=100\text{ }^\circ\text{C}$	$I_R$	0.2	0.5		mA
		50	100		
Typical Thermal Resistance (Note 2)	$R_{\theta JL}$ $R_{\theta JA}$		17 55		$^\circ\text{C/W}$
Marking Code		SL32	SL33	SL34	
Operating Temperature Range	$T_J$		- 55 to + 125		$^\circ\text{C}$
Storage Temperature Range	$T_{STG}$		- 55 to + 150		$^\circ\text{C}$

Note 1: Pluse Test with PW=300 usec, 1% Duty Cycle

Note 2: Measure on P.C.B. Board with 16mm x 16mm Copper Pad Areas

### RATINGS AND CHARACTERISTIC CURVES (SSL32 THRU SSL34)

FIG.1 FORWARD CURRENT DERATING CURVE




FIG. 2 MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT




FIG. 3 TYPICAL FORWARD CHARACTERISTICS




FIG. 4 TYPICAL REVERSE CHARACTERISTICS





FIG. 5 TYPICAL JUNCTION CAPACITANCE



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Taiwan Semiconductor:](#)

[SSL32](#) [SSL33](#) [SSL34](#)