

NOTES:

MATERIAL:


OUTER SHELL :
SHIELD RING & PANEL NUT: } BRASS

FINISH:


OUTER SHELL: CHROME

OTHER BRASS PARTS : NICKEL



T * T TOOLS



RECOMMENDED
PANEL CUTOUT




MATING SIDE VIEW



WIRE SIDE VIEW

	TOOLS (JAW DIMENSION)	ADVISED TORQUE IN Nm
	17	1.7
	15	-

PART LIST	
ITEM NO.	DESCRIPTION
1	SHELL
2	LOCK WASHER
3	PANEL NUT
4	INSULATOR



SCALE 5:2

ORIGIN	COUNTRY	JURISDICTION	CLASSIFICATION
X	FR	Not listed	N/A
	US	EAR	ECCN =EAR99
		These commodities, technology or software are exported from the United States in accordance with the Export Administration Regulations. Diversion contrary to U.S. law is prohibited	

LINEAR MEASURE:			
THIRD ANGLE PROJECTION			
			
TOLERANCES			
UNLESS OTHERWISE SPECIFIED			
NO. OF PLACES	mm [INCH]		
WHOLE NO.	±0.5 [±.02]		
ONE PLACE	±0.2 [±.008]		
TWO PLACES	±0.1 [±.004]		
ANGLES ±°			

DRAWING TITLE			
JBX, SIZE 2, BACK PANEL MOUNTING RECEPTACLE			
CAT NO.			
JBXEP2			
CAGE NO: 09922	SIZE: C	APPROVAL	DRAWN: SKV 01-14-15
CUSTOMER			CHKD : EV 01-14-15
			DSGN : EV 01-14-15
			MFG : DH 01-14-15
			QC : BB 01-14-15
			DRAWING SCALE: 4:1
		DRAWING NO.	REV
INTERPRET THIS DRAWING IN ACCORDANCE WITH ASME Y14.5M - 1994.		JBXEP2C	
		A	
www.souriau.com		1 OF 1	

A

PRO-E

<i>CATALOG</i>	<i>NUMBER</i>	<i>DESCRIPTION</i>
----------------	---------------	--------------------

JBX EP 2 XXXXXDX-

BASIC SERIES

OPTION

SHELL TYPE

INSERT MATERIAL

SHELL SIZE

COLLET OPTION

KEYING

SURFACE PLATING

SEE INSULATOR DRAWING

4

3
















2

1


PRO-E

DWG. NO. JBX2INSFCC

FEMALE INSULATOR, CRIMP CONTACT

CONTACT LAYOUT	02	03	04	05
FRONT SIDE VIEW				
REAR SIDE VIEW				
CONTACT				
ISO VIEW				
ØC	2	1.6	1.3	1.3
ØF	2.4	1.9	1.4	1.4
MAX. AWG	12	14	18	18
MAX. CURRENT RATING (A)	30	17	15	15
CONTACT RESISTANCE (mΩ)	2.5	2.5	3	3
NUMBER OF CAVITY	2	3	4	5
MAX. CURRENT RATING	30	17	15	14
TEST VOLTAGE (Vrms)	2100	1700	2400	1900
WORKING VOLTAGE (Vdc/Vrms)	1000/700	830/560	1000/700	900/630

CONTACT TYPE :	F (FEMALE)
CONTACT TERMINATION :	C (CRIMP)
<u>MATERIAL</u> :	
CONTACT:	CUPRO-NICK
CLIP:	COPPER ALL
INSULATOR:	PEEK
<u>FINISH</u> :	
CONTACTS :	GOLD

[illegible]

JBXXX 2 X YY F C XXXX

BASIC SERIES

OPTION

SHELL TYPE

INSERT MATERIAL

SHELL SIZE

COLLET OPTION

KEYING

SURFACE PLATING

CONTACT LAYOUT

CONTACT TERMINATION

CONTACT TYPE

B	REVISED PER ECN 12286	RSK 06-10-15	EV 06-10-15
A	RELEASED PER ECN 12264	TJS 03-10-15	EV 03-10-15
REV	DESCRIPTION	BY DATE	CHKD DATE

DRAWING TITLE

JBX, SIZE 2, FEMALE INSULATOR, CRIMP CONTACT

CAT NO.

JBX2INSFC

CAGE NO: 09922

SIZE: B

CUSTOMER

SOURIAU

WWW.SOURIAU.COM

APPROVAL	DRAWN: TJS	02-04-15
	CHKD : EV	02-04-15
	DSGN : EV	02-04-15
	MFG : DH	02-04-15
	QC : BB	02-04-15
DRAWING SCALE: NA		
DRAWING NO.		REV
JBX2INSFCC		B
1 OF 3		

INTERPRET THIS DRAWING IN ACCORDANCE
WITH ASME Y14.5M - 1994.

PRO-E

1

2

THIS DRAWING IS A CONTROLLED DOCUMENT FOR SOURIAU USA, INC.
IT IS SUBJECT TO CHANGE WITHOUT NOTIFICATION.
CONTACT THE DOCUMENT CONTROL CENTER FOR THE LATEST REVISION.

THE INFORMATION CONTAINED IN THIS DRAWING IS CONFIDENTIAL AND MAY NOT BE DISCLOSED WITHOUT WRITTEN CONSENT FROM SOURIAU USA, INC.

B

A

THIS DRAWING IS A CONTROLLED DOCUMENT FOR SOURIAU USA, INC.
IT IS SUBJECT TO CHANGE WITHOUT NOTIFICATION.
CONTACT THE DOCUMENT CONTROL CENTER FOR THE LATEST REVISION.

THE INFORMATION CONTAINED IN THIS DRAWING IS CONFIDENTIAL AND MAY NOT BE
DISCLOSED WITHOUT WRITTEN CONSENT FROM SOURIAU USA, INC.

DWG. NO.
JBX2INSFCC

CONTACT LAYOUT		06	07	08	10
FRONT SIDE VIEW					
REAR SIDE VIEW					
CONTACT					
ISO VIEW					
CONTACT	ØC	1.3	1.3	0.9	0.9
	ØF	1.4	1.4	1.1	1.1
	MAX. AWG	18	18	20	20
	MAX. CURRENT RATING (A)	15	15	10	10
	CONTACT RESISTANCE (mΩ)	3	3	3.5	3.5
	NUMBER OF CAVITY	6	7	8	10
	MAX. CURRENT RATING	12	11	10	8
	TEST VOLTAGE (Vrms)	1900	1500	1700	1700
INSULATOR	WORKING VOLTAGE (Vdc/Vrms)	900/630	730/500	830/560	830/560

ORIGIN	COUNTRY	JURISDICTION	CLASSIFICATION
X	FR	Not listed	N/A
	US	EAR	ECCN =EAR99
These commodities, technology or software are exported from the United States in accordance with the Export Administration Regulations. Diversion contrary to U.S. law is prohibited			

LINEAR MEASURE:			mm (INCH)
THIRD ANGLE PROJECTION			
TOLERANCES UNLESS OTHERWISE SPECIFIED			
No. OF PLACES	mm [INCH]		
ONE PLACE	±3 [±.1]		
TWO PLACES	±0.5 [±.02]		
THREE PLACES	±0.25 [±.010]		
ANGLES±1°			

DRAWING TITLE				
JBX, SIZE 2, FEMALE INSULATOR, CRIMP CONTACT				
CAT NO.				
JBX2INSFC				
CAGE NO: 09922	SIZE: B		APPROVAL	
CUSTOMER	SOURIAU	DRAWN: TJS		02-04-15
		CHKD : EV		02-04-15
		DSGN : EV		02-04-15
		MFG : DH		02-04-15
		QC : BB		02-04-15
DRAWING SCALE: NA				
DRAWING NO.		REV		
JBX2INSFCC		B		
2 OF 3				
INTERPRET THIS DRAWING IN ACCORDANCE WITH ASME Y14.5M - 1994.		WWW.SOURIAU.COM		

WWW.SOURIAU.COM


THIS DRAWING IS A CONTROLLED DOCUMENT FOR SOURIAU USA, INC.
IT IS SUBJECT TO CHANGE WITHOUT NOTIFICATION.
CONTACT THE DOCUMENT CONTROL CENTER FOR THE LATEST REVISION.

THE INFORMATION CONTAINED IN THIS DRAWING IS CONFIDENTIAL AND MAY NOT BE
DISCLOSED WITHOUT WRITTEN CONSENT FROM SOURIAU USA, INC.

DWG. NO.
JBX2INSFCC

CONTACT LAYOUT		12	16	18	19
FRONT SIDE VIEW					
REAR SIDE VIEW					
CONTACT					
ISO VIEW					
CONTACT	ØC	0.7	0.7	0.7	0.7
	ØF	0.85	0.85	0.85	0.85
	MAX. AWG	22	22	22	22
	MAX. CURRENT RATING (A)	7	7	7	7
INSULATOR	CONTACT RESISTANCE (mΩ)	5	5	5	5
	NUMBER OF CAVITY	12	16	18	19
	MAX. CURRENT RATING	7	6	5.5	5
	TEST VOLTAGE (Vrms)	1700	1500	1400	1400
WORKING VOLTAGE (Vdc/Vrms)		830/560	730/500	660/460	660/460

ORIGIN	COUNTRY	JURISDICTION	CLASSIFICATION
X	FR	Not listed	N/A
	US	EAR	ECCN =EAR99
These commodities, technology or software are exported from the United States in accordance with the Export Administration Regulations. Diversion contrary to U.S. law is prohibited			

LINEAR MEASURE:			mm (INCH)
THIRD ANGLE PROJECTION			
			
TOLERANCES UNLESS OTHERWISE SPECIFIED			
No. OF PLACES	mm [INCH]		
ONE PLACE	±3 [±.1]		
TWO PLACES	±0.5 [±.02]		
THREE PLACES	±0.25 [±.010]		
ANGLES ±1°			

DRAWING TITLE						
JBX, SIZE 2, FEMALE INSULATOR, CRIMP CONTACT						
CAT NO.						
JBX2INSFC						
CAGE NO: 09922		SIZE: B		APPROVAL		
CUSTOMER		SOURIAU			DRAWN: TJS	02-04-15
					CHKD : EV	02-04-15
					DSGN : EV	02-04-15
					MFG : DH	02-04-15
					QC : BB	02-04-15
INTERPRET THIS DRAWING IN ACCORDANCE WITH ASME Y14.5M - 1994.		WWW.SOURIAU.COM			DRAWING SCALE: NA	
					DRAWING NO. REV	
					JBX2INSFCC B	
					3 OF 3	

B

A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Souriau:

[JBXEP2G02FCSDS](#) [JBXEP2G03FCSDS](#) [JBXEP2G04FCSDS](#) [JBXEP2G05FCSDS](#) [JBXEP2G06FCSDS](#)
[JBXEP2G07FCSDS](#) [JBXEP2G08FCSDS](#) [JBXEP2G10FCSDS](#) [JBXEP2G16FCSDS](#) [JBXEP2G18FCSDS](#)
[JBXEP2G19FCSDS](#) [JBXEP2G12FCSDS](#)