

ELECTRICAL:

EMI SHIELDING :

INSULATION RESISTANCE :

MAX. CURRENT RATING :

CONNECTOR TESTING VOLTAGE :

CONNECTOR WORKING VOLTAGE :

ENVIRONMENTAL:

ENDURANCE:

SHOCK:

VIBRATIONS:

PROTECTION INDEX:

ROHS COMPLIANT

SALT MIST :

OPERATING TEMPERATURE:

SHIELDED FOR THE RANGE 55dB UP TO 100MHz

>500M Ω PER ANSI-EIA-364-D METHOD 21

SEE INSULATOR DRAWING

SEE INSULATOR DRAWING

SEE INSULATOR DRAWING

1000 CYCLES AS PER MIL-STD 1344A, METHOD 2016.1





50 g , DURATION 6 ms; AS PER MIL-STD 1344A, METHOD 2004.1

10 TO 2000Hz g = 15g, AS PER MIL-STD 1344A, METHOD 2005.1

IP 40 AS PER CEI 529

48Hr PER SAE AS 1344 METHOD 1001.1 CEI 529

-55°C TO +125°C (-67°F TO +257°F)



	TOOLS (JAW DIMENSION)	ADVISED TORQUE IN Nm
	14	1.3

PART LIST	
ITEM NO.	DESCRIPTION
1	SHELL
2	LOCK WASHER
3	HEX NUT
4	INSULATOR

<i>CATALOG</i>	<i>NUMBER</i>	<i>DESCRIPTION</i>
----------------	---------------	--------------------

JBX ER 1 XXXXXDXR

BASIC SERIES

SHELL TYPE

SHELL SIZE

KEYING


SEE INSULATOR DRAWING

OPTION

INSERT MATERIAL

COLLET OPTION

SURFACE PLATING



ORIGIN	COUNTRY	JURISDICTION	CLASSIFICATION
X	FR	Not listed	N/A
	US	EAR	ECCN #EAR99
		These commodities, technology, or software are exported from the United States in accordance with the Export Administration Regulations. Diversion contrary to U.S. law is prohibited.	

LINEAR MEASURE: mm (INCH) mm (INCH)	
THIRD ANGLE PROJECTION	
	
TOLERANCES	
UNLESS OTHERWISE SPECIFIED	
No. OF PLACES	mm [INCH]
WHOLE No.	$\pm 0.5 \left[\pm .02 \right]$
ONE PLACE	$\pm 0.2 \left[\pm .008 \right]$
TWO PLACES	$\pm 0.1 \left[\pm .004 \right]$
ANGLE $\pm 1^\circ$	

A		RELEASED PER ECN 12258		SKV 06-10-15		EV 06-10-15	
REV		DESCRIPTION		BY DATE		CHKD DATE	
DRAWING TITLE							
JBX, SIZE 1, FRONT PANEL MOUNTING RECEPTACLE							
CAT NO.							
JBXER1							
CAGE NO: 09922		SIZE: C		APPROVAL		DRAWN: SKV 01-12-15	
CUSTOMER		SOURIAU				CHKD : EV 01-12-15	
						DSGN : EV 01-12-15	
						MFG : DH 01-12-15	
						QC : BB 01-12-15	
INTERPRET THIS DRAWING IN ACCORDANCE WITH ASME Y14.5M - 1994.		www.souriau.com		DRAWING SCALE: 5:1		DRAWING NO. REV	
				JBXERIC		A	
				1 OF 1			


THIS DRAWING IS A CONTROLLED DOCUMENT FOR SOURIAU USA, INC.
IT IS SUBJECT TO CHANGE WITHOUT NOTIFICATION.
CONTACT THE DOCUMENT CONTROL CENTER FOR THE LATEST REVISION.

THE INFORMATION CONTAINED IN THIS DRAWING IS CONFIDENTIAL AND MAY NOT BE
DISCLOSED WITHOUT WRITTEN CONSENT FROM SOURIAU USA, INC.


DWG. NO.
JBX11NSMSC

MALE INSULATOR, SOLDER CONTACT

CONTACT LAYOUT	02	03	04	05
FRONT SIDE VIEW				
REAR SIDE VIEW				
CONTACT				
ISO VIEW				
CONTACT	ØC	1.3	1.3	0.9
	ØF	1.1	1.1	0.8
	MAX. AWG	20	20	24
	MAX. CURRENT RATING (A)	15	15	10
INSULATOR	CONTACT RESISTANCE (mΩ)	3	3	3.5
	NUMBER OF CAVITY	2	3	4
	MAX. CURRENT RATING	15	12	9
	TEST VOLTAGE (Vrms)	1600	1300	1900
WORKING VOLTAGE (Vdc/Vrms)		760/530	600/420	900/630
		660/460		



CATALOG NUMBER DESCRIPTION



B	REVISED PER ECN 12286	RSK 06-10-15	EV 06-10-15
A	RELEASED PER ECN 12264	SKV 03-10-15	EV 03-10-15
REV	DESCRIPTION	BY DATE	CHKD DATE

DRAWING TITLE
JBX, SIZE 1, MALE INSULATOR, SOLDER CONTACT

CAT NO.
JBX11NSMS

CAGE NO: 09922SIZE: B

CUSTOMER

INTERPRET THIS DRAWING IN ACCORDANCE WITH ASME Y14.5M - 1994.

APPROVAL

DRAWN: SKV 02-02-15
CHKD : EV 02-02-15
DSGN : EV 02-02-15
MFG : DH 02-02-15
QC : BB 02-02-15

DRAWING SCALE: NA
DRAWING NO.
JBX11NSMSC

REV
B

1 OF 2

WWW.SOURIAU.COM

PRO-E

ORIGIN	COUNTRY	JURISDICTION	CLASSIFICATION
X	FR	Not listed	N/A
	US	EAR	ECCN =EAR99
These commodities, technology or software are exported from the United States in accordance with the Export Administration Regulations. Diversion contrary to U.S. law is prohibited			

LINEAR MEASURE:

mm

INCH

mm (INCH)

THIRD ANGLE PROJECTION

TOLERANCES UNLESS OTHERWISE SPECIFIED

No. OF PLACES

mm [INCH]

ONE PLACE

±3 [±.1]

TWO PLACES

±0.5 [±.02]

THREE PLACES


















±0.25 [±.010]

ANGLES±1°


THIS DRAWING IS A CONTROLLED DOCUMENT FOR SOURIAU USA, INC.
IT IS SUBJECT TO CHANGE WITHOUT NOTIFICATION.
CONTACT THE DOCUMENT CONTROL CENTER FOR THE LATEST REVISION.

THE INFORMATION CONTAINED IN THIS DRAWING IS CONFIDENTIAL AND MAY NOT BE
DISCLOSED WITHOUT WRITTEN CONSENT FROM SOURIAU USA, INC.

DWG. NO.
JBX11NSMSC

CONTACT LAYOUT		06	07	08	10	12
FRONT SIDE VIEW						
REAR SIDE VIEW						
CONTACT						
ISO VIEW						
CONTACT	ØC	0.7	0.7	0.7	0.5	0.5
	ØF	0.81	0.81	0.81	0.5	0.5
	MAX. AWG	22	22	22	28	28
	MAX. CURRENT RATING (A)	7	7	7	5	5
	CONTACT RESISTANCE (mΩ)	5	5	5	10	10
INSULATOR	NUMBER OF CAVITY	6	7	8	10	12
	MAX. CURRENT RATING	7	7	5	2.5	2.5
	TEST VOLTAGE (Vrms)	1400	1400	1200	600	500
	WORKING VOLTAGE (Vdc/Vrms)	660/460	660/460	600/420	300/200	170/120

ORIGIN	COUNTRY	JURISDICTION	CLASSIFICATION
X	FR	Not listed	N/A
	US	EAR	ECCN =EAR99
These commodities, technology or software are exported from the United States in accordance with the Export Administration Regulations. Diversion contrary to U.S. law is prohibited			

LINEAR MEASURE:			mm (INCH)
THIRD ANGLE PROJECTION			
TOLERANCES UNLESS OTHERWISE SPECIFIED			
No. OF PLACES	mm [INCH]		
ONE PLACE	±3 [±.1]		
TWO PLACES	±0.5 [±.02]		
THREE PLACES	±0.25 [±.010]		
ANGLES ±1°			

DRAWING TITLE			
JBX, SIZE 1, MALE INSULATOR, SOLDER CONTACT			
CAT NO. JBX11NSMS			
CAGE NO: 09922		SIZE: B	
CUSTOMER		SOURIAU	WWW.SOURIAU.COM
INTERPRET THIS DRAWING IN ACCORDANCE WITH ASME Y14.5M - 1994.		2 OF 2	PRO-E
APPROVAL	DRAWN:	SKV	02-02-15
	CHKD :	EV	02-02-15
	DSGN :	EV	02-02-15
	MFG :	DH	02-02-15
	QC :	BB	02-02-15
DRAWING SCALE: NA			
DRAWING NO.		REV	
JBX11NSMSC		B	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Souriau:

[JBXER1G06MSSDSR](#) [JBXER1G10MSSDPR](#)