

# Wire-wound Metal Power Inductors MCOIL™ LSEN series

## for General Electronic Equipment for Consumer

Code in front of Series have been extracted from Part number, which describes the segment of products, such as kinds and characteristics.

REFLOW

## PART NUMBER

\* Operating Temp.: -40~+125°C (Including self-generated heat)

L	S	E	N	C	2	0	1	6	K	K	T	1	R	0	M	
①	②	③	④	⑤	⑥	⑦	⑧									

## ① Series

Code	
(1)(2)(3)(4)	
LSEN	Wire-wound Metal Power Inductor for General Electronic Equipment for Consumer

## (1) Product Group

Code	
L	Inductors

## (2) Category

Code	Recommended equipment	Quality Grade
S	General Electronic Equipment for Consumer	3

## (3) Type

Code	
E	Metal Wire-wound (High filling type)

## (4) Features, Characteristics

Code	
N	Standard Power choke

## ② Features

Code	Feature
C	Bottom electrode (Ag-resin × Sn-plate)

## ③ Dimensions (L × W)

Code	Dimensions (L × W) [mm]
2016	2.0 × 1.6
2520	2.5 × 2.0

## ④ Dimensions (T)

Code	Dimensions (T) [mm]
KK	1.0

## ⑤ Packaging

Code	Packaging
T	Taping

## ⑥ Nominal inductance

Code (example)	Nominal inductance [μH]
R47	0.47
1R0	1.0
4R7	4.7


※R=Decimal point

## ⑦ Inductance tolerance

Code	Inductance tolerance
M	±20%

## ⑧ Internal code


## STANDARD EXTERNAL DIMENSIONS / STANDARD QUANTITY



## Recommended Land Patterns

## Surface Mounting

- Mounting and soldering conditions should be checked beforehand.
- Applicable soldering process to these products is reflow soldering only.



Type	A	B	C
2016	0.7	0.8	1.8
2520	0.9	1.0	2.2

Unit: mm

Type	L	W	T	e	Standard quantity [pcs] Taping
2016KK	2.0±0.2 (0.079±0.008)	1.6±0.2 (0.063±0.008)	1.0 max (0.039 max)	0.5±0.3 (0.020±0.012)	3000
2520KK	2.5±0.2 (0.098±0.008)	2.0±0.2 (0.079±0.008)	1.0 max (0.039 max)	0.65±0.3 (0.026±0.012)	3000

Unit: mm (inch)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TAIYO YUDEN:](#)

[LSENC2520KKT1R0M](#) [LSENC2520KKT2R2M](#) [LSENC2520KKT4R7M](#) [LSENC2520KKTR47M](#)  
[LSENC2016KKT1R0M](#) [LSENC2520KKT3R3M](#) [LSENC2520KKTR33M](#) [LSENC2016KKT2R2M](#) [LSENC2520KKT1R5M](#)  
[LSENC2016KKTR68M](#) [LSENC2016KKTR47M](#)