







PANEL CUT OUT




SHELL SIZE	Ø A ±0.15	B ±0.20 (without marking)	C ±0.20	D	Ø E	F ± 0.3	Thread	Tightening torque (Nut)
08	11.90	24.00	19.05 ±0.37	13.75 ± 0.20	14.60 ± 0.20	3.1	9/16 24 UNEF CLASS 2A	2 Nm
10	14.90	26.90	22.15	16.40 0/+0.2	17.30 0/+0.25	3.1	11/16 24 UNEF CLASS 2A	3 Nm
12	18.95	31.75	27.15	20.85 0/+0.3	22.10 0/+0.3	3.1	7/8 20 UNEF CLASS 2A	4 Nm
14	22.15	34.90	30.20	24.00 0/+0.3	25.40 0/+0.3	3 ± 0.1	1"20 UNEF CLASS 2A	5 Nm

DRILLING PATTERN FOR HOLD DOWN PINS

SHELL 8



SHELL 10/12/14



MATERIAL :

- Shell: Polyamid UL94 V-0
- Insert: Polychloropren (CR)
- Seal gasket : Sealing IP68/69K : Silicone
- O'ring: nitril
- Nut: Aluminium alloy black anodized
- Contact: Brass + gold plated

PERFORMANCE CHARACTERISTICS :

- Operating temperature: -40°C up to 105°C
- Insulation resistance: 5000 MΩ min
- Test potential: 2000 Vrms for #16 layout and 1500Vrms for #20 layout
- Corrosion salt spray: 500 hours
- Durability: 250 matings and unmatings

Sealing in mated and unmated conditions:


- IP68 : 1 bar during 1 week : immersion under 10 m of water (IEC 60529)
- IP69K : exposure to high pressure water of cleaning equipment (DIN 40050)

NOTE :


Insert arrangements : refer to C144-UTS1-A

TAILLE	Perçage 1		Perçage 2	
	A	B	C	D
T10	3.98	9.85	5.31	9.20
T12	4.92	12.17	6.56	11.37
T14	5.29	13.10	7.06	12.23

MALE CONNECTOR



FEMALE CONNECTOR



Shell size	I (male connector)	J (female connector)
8	3.8/6 for layout 8-2/8-3/8-4 4.7/7.25 for layout 8-3A/8-98/8-33	3.75/5.8 for layout 8-2/8-3/8-4 4.8/6.9 for layout 8-3A/8-98/8-33
10	4.9/7	4.9/7
12	4.8/7 3.85/5.9 for layout 12-14	5.2/7 3.85/5.9 for layout 12-14
14	4.8/7	5.3/7

UTS7 14 D 19 P . 32

Jam nut receptacle UTS

Shell size

D= Dipsolder contacts

Insert arrangement
(See table)

P = Male contact


S = Female contact

Orientations

Normal (no digit), W,X,Y,Z = different orientations

Specification

CUSTOMER DRAWING

d		05/12/13		--		DRILLING PATTERN: Modification of view and cotation		--	
ISS		DATE		Latest modification - by: LANDAIS.P				MOD N°	
Designed by:		SORIN V.		Date: 19/05/10		CUSTOMER DRAWING			
TITLE		JAM NUT WITH DIPSOLDER CONTACTS							
		UTS HI SEAL SPECIF.32							
Scale 2/1				General linear Tolerances: ± 0.2		NPRDS / PROJECT UTS-HI SEAL			
SOURIAU		WWW.SOURIAU.COM				This document is the property of SOURIAU It must not be reproduced or communicated without permission			
FORMAT A2		SOURIAU DRG N° C121-UTS1-A						SHEET 1 / 1	
NOT EXPORT CONTROLLED									

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Souriau:

[UTS710D6P](#) [UTS712D10P](#) [UTS714D19P](#) [UTS714D18S](#) [UTS714D7P](#) [UTS714D7S](#) [UTS710D6S](#) [UTS710D7P](#)
[UTS710D7S](#) [UTS712D10S](#) [UTS714D19S](#) [UTS712D14P](#) [UTS712D14S](#) [UTS712D2P](#) [UTS712D2S](#) [UTS712D3P](#)
[UTS712D3S](#) [UTS712D4P](#) [UTS712D4S](#) [UTS712D8P](#) [UTS712D8S](#) [UTS714D12P](#) [UTS714D12S](#) [UTS714D15P](#)
[UTS714D15S](#) [UTS714D18P](#) [UTS714D5P](#) [UTS714D5S](#) [UTS712D10P32](#) [UTS714D19S32](#) [UTS710D6P32](#)
[UTS712D8S32](#) [UTS712D10S32](#) [UTS712D8P32](#) [UTS714D19P32](#) [UTS712D4P32](#) [UTS714D15S32](#) [UTS714D15P32](#)
[UTS714D18S32](#) [UTS714D5P32](#) [UTS714D12P32](#) [UTS714D12S32](#) [UTS712D3S32](#) [UTS710D98P32](#) [UTS712D3P32](#)
[UTS710D98S](#) [UTS714D18P32](#) [UTS710D6S32](#) [UTS710D7S32](#) [UTS712D4S32](#) [UTS714D5S32](#) [UTS714D7P32](#)
[UTS710D98P](#) [UTS714D19PW](#) [UTS710D7P32](#) [UTS714D7S32](#) [UTS710D98S32](#) [UTS712D14P32](#) [UTS712D14S32](#)
[UTS712D2P32](#) [UTS712D2S32](#) [UTS712D4P32K](#) [UTS710D7S30](#) [UTS710DCGE](#) [UTS714D12PW](#) [UTS714D19PW32](#)
[UTS714D19PX32](#) [UTS714D19PY32](#) [UTS712D10SX](#) [UTS712D10SX32](#) [UTS712DCGE](#) [UTS714D19SW](#)
[UTS714DCGE](#) [UTS718D32P](#) [UTS718D32P32](#) [UTS718D32S](#) [UTS718DCGE](#) [UTS710D6PW](#) [UTS712D8SW](#)
[UTS714D12PX](#) [UTS714D5PW](#) [UTS710D6PW32](#) [UTS710D98PW](#) [UTS710D98PX](#) [UTS710D98PY](#) [UTS710D98PZ](#)
[UTS712D8PW](#) [UTS710D6SW](#) [UTS710D7S56](#) [UTS712D3P32Y](#) [UTS712D10PK](#)