


SPECIFICATION

Part No. : **CAB.955**
Product Name : Taoglas Cable Assembly
N Type Jack with O-Ring to 100mm(3.93") RG-316 SMA(M)ST
PLUG
Photo :




1. Cable Insertion Loss




2. RG-316 Cable Specification

2.1 Drawing – Cross Section



2.2 Structure and Dimensions




Conductor	Insulation	Braid Shield	Braid Shield	Jacket
- Material – Silver Coated Copper Clad Steel 26AWG(7/0.175mm) - Diameter - 0.53mm	- Material – FEP - Avg. Thickness- 0.51mm - Diameter – 1.53 ± 0.03mm - Colour - Clear	- Material–Silver -Coated Copper - Structure – 16/5/0.10mm - Coverage – 95% - Diameter – 1.98 ± 0.05mm	- Material–Silver -Coated Copper - Structure – 16/5/0.10mm - Coverage – 86% - Diameter – 2.38 ± 0.05mm	- Material – FEP - Avg. Thickness- 0.30mm - Diameter – 2.90 ± 0.10mm - Colour – Brown

2.3 Electrical & Physical Specification

Rating Temp Voltage:	105°C 30V					
Insulation Resistance:	3000 MΩ-Km (Min)					
Conductor Resistance:	302 Ω/Km 20°C (Max)					
Dielectric Strength:	AC 1 KV/Minute					
Spark Test	5.0 KV					
Nom. Impedance	50 ± 3 Ω					
Nom. Capacitance	95.8 ± 3 pF/m					
Nom. Vel. of Prop.	69%					
VSWR (0-6 GHz)	Max 1.3					
Attenuation	2GHz	2.4GHz	3GHz	4GHz	5GHz	6GHz
(dB/1M)	1.35	1.5	1.62	1.91	2.2	2.7



3. Technical Drawing

3.1 CAB.955



	Name	Material	Finish	QTY
1	N Type(F) ST	Brass	Ni Plated	1
2	Heat Shrink Tube (RG-316)	PE	Black	2
3	RG-316 Coaxial Cable	FEP	Brown	1
4	SMA(M) ST	Brass	Gold	1
5	Washer	Brass	Ni Plated	1
6	Nut	Brass	Ni Plated	1

3.2 Connectors



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Taoglas:](#)

[CAB.955](#)