

CASE FINISH	CURRENT (AMPS)	WORKING VOLTAGE				MAXIMUM DC RESISTANCE (OHMS)	MAXIMUM VOLTAGE DROP		MINIMUM CAPACITANCE (uF)	MIN. INSERTION LOSS PER MIL-STD-220 FULL LOAD, +25°C													
		-55°C TO +85°C		-55°C TO +125°C			DC	AC		14	30	50	75	100	150	300	500	1	100	1	10		
		AC	DC	AC	DC					KHz	KHz	KHz	KHz	KHz	KHz	KHz	MHz	MHz	MHz	GHz	GHz		
SOLDER	3.0	--	150	--	100	0.05	--	--	0.75	--	--	--	--	--	22	29	--	44	65	--	70	--	

PART MARKING:


SCI 
9000-100-0017
DATE CODE

PACKAGE MARKING:

STANDARD

MARKING NOTES:

N/A



MTG. HARDWARE

NOTES:

1) MOUNTING TORQUE NOT TO EXCEED 7in-lbs.

										10	REV	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. [MILLIMETERS] DO NOT SCALE.	TOLERANCES UNLESS OTHERWISE SPECIFIED Fractions Dec. .xx± Dec. .xxx±010 Angles ±0° 30'	ERIE, FAIRVIEW PENNSYLVANIA SPECTRUM CONTROL INC. Dwn MAYNARD Ckd 3/4/98	Description Low Pass EMI Filter
										CN 185632	CN 184877	CHANGE NOTICE NO.	CODE IDENT. NO. DLSP2	Sheet 1 of 1	9000-100-0017

Quality Products From The Specialists In Electro-Magnetic Compatibility

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Spectrum Control:](#)

[9000-100-0017](#)