



NOTES:

1. MAX. SOLDERING TEMP. : 245°C FOR 5 SECONDS MAX.

USE OF HEXAVALENT CHROMIUM,
MERCURY, LEAD, CADMIUM,
ASBESTOS, PCT, PCB, PBB, PBDE,
PBDE, IS PROHIBITED IN THE
MANUFACTURE OR COMPOSITION OF
THIS MATERIAL AS OUTLINED IN THE
INTERNATIONAL ROHS DIRECTIVE.



LEAD FINISH:	GOLD
CASING FINISH:	GOLD
CAPACITANCE	10pF MAX.
TEMP. RANGE	-55°C TO 125°C
CURRENT	5 AMP MAX.
WORKING VOLTAGE	125°C 200 VDC MAX.
D.C. RESISTANCE	.01ohms MAX.
SCHEMATIC	
MARKING:	NONE
PACKING:	BAG: SCIF-9925-000
	DATE CODE
	LOT NO.
	QTY. / BAG (200 MAX.)

TOLERANCES UNLESS OTHERWISE SPECIFIED		FAIRVIEW PENNSYLVANIA	
Dec. .x ± .x			
Dec. .xx ±		Description	
Dec. .xxx ±.005 [13]		Dwn. Hassett	FEEDTHRU FILTER
Angles ± 0° 30°		Date 12-30-05	
CODE IDENT. NO.		Engt. Struchen	SCIF-9925-000
0LSP2		Sheet 1 of 1	

Quality Products From The Specialists In Electro-Magnetic Compatibility

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[API Technologies:](#)

[SCIF-9925-000](#)