



NOTES:

1. SUGGESTED MOUNTING HOLE =  $\phi.117 \pm .002$
2. MAXIMUM INSTALLATION TEMP.: 500°F



LEAD FINISH: SILVER	
EYELET FINISH: SOLDER	
CAPACITANCE	50pF-175pF
TEMP. RANGE	-25°C TO 85°C
CURRENT	15 AMP MAX.
WORKING VOLTAGE	85°C 100 VDC MAX.
D.C. RESISTANCE	.01ohms MAX.
MIN. I.L. PER MIL-STD-220 AT 25°C NO LOAD	
FREQ. MHz	I.L. (db)
1000	16
SCHEMATIC	
MARKING: PART: NONE	
BAG: SCI	
51-713-095	
DATE CODE	
LOT#	
QTY/BAG (200 MAX.)	

			0	REV. NO.	TOLERANCES UNLESS OTHERWISE SPECIFIED	 ERIE, FAIRVIEW PENNSYLVANIA	
			CN 200088	CHANGE NOTICE	Fractions $\pm 1/64$		SPECTRUM CONTROL INC.
					Dec. .xx $\pm$	Dwn. KRDZALIC	Description
					Dec. .xxx $\pm .010$	Ckd. 2 / 7 / O1	Pi SOLDER-IN FILTER
					Angles $\pm 0^{\circ} 30'$	Apvd.	51-713-095
					CODE IDENT. NO. DLSP2	Scale NONE	

Ckd. 2/7/O1

Pi SOLDER-IN FILTER

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Spectrum Control:](#)

[51-713-095](#)