

## SPECIFICATION

Part No. : **PCB.SMAFSTJ.B.HT**

Product Name : SMA (F) Surface Mount PCB Jack

Feature : SMA(F) Jack  
Surface Mount PCB Jack  
Frequency Range: 0~12.4GHz  
Finish: Gold  
Leg Length: 1mm  
Total Length: 10.40mm  
RoHS & REACH Compliant




## 1. Introduction

The PCB.SMAFSTJ.B.HT connector was designed to be surface mounted on a PCB, it has a Solder Post for connection. The connector pin is directly soldered onto pads on the PCB. The connector is a standard SMA (F) Jack. The SMA connector is the most popular type connector for RF applications. Taoglas connectors are all RoHS compliant.

## 2. Specification

ELECTRICAL	
Impedance	50Ω
Frequency Range	0~12.4 GHz
Working Voltage	Max. 335 Vrms
Dielectric withstanding Voltage	≤1000 Vrms
Insulation Resistance	≥5000M Ω
MECHANICAL	
Connector Dimension	10.4 X Ø5.35 mm
Connector Pin Diameter	1.27 mm
Connector Type	SMA (F)
ENVIRONMENTAL	
Temperature	-40°C to +85°C
RoHS & REACH compliant	

### 3. Connector Drawing



	Name	Material	Finish	QTY
1	Body	Brass	Gold	1
2	Female Contact	Phosphor Bronze	Gold	1
3	Insulator	Teflon	White	1

Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time without notice.  
Taoglas reserves all rights to this document and the information contained herein. Reproduction, use or disclosure to third parties without express permission is strictly prohibited. Copyright © Taoglas Ltd.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Taoglas:](#)

[PCB.SMAFSTJ.B.HT](#)