



NOTES:

1. MAX. MTG. TORQUE = 3lb-in.
2. HARDWARE IS INCLUDED.



LEAD FINISH:	SILVER
BUSHING FINISH:	SILVER
CAPACITANCE	10pF ±20%
TEMP. RANGE	-55°C TO 125°C
CURRENT	10 AMP MAX.
WORKING VOLTAGE	85°C -- VDC MAX. 125°C 100 VDC MAX.
D.C. RESISTANCE	.01ohms MAX.
MIN. I.L. PER MIL-STD-220 AT 25°C NO LOAD	
FREQ. MHz	I.L. (db)
1	N/A
100	N/A
500	N/A
1 GHz	N/A
10 GHz	N/A

SCHEMATIC



MARKING:

PART: SF100M

BAG:

SCI 54F-779-073

DATE CODE

QTY/BAG (200 MAX.)

00

REV. N.D.

TOLERANCES UNLESS OTHERWISE SPECIFIED

Fractions ± 1/64

Dec. .xx±

Dec. .xxx± .005

Angles ±0° 30'

CODE IDENT. NO.
OLSP2

CN 40123-ENG

CHANGE NOTICE



SPECTRUM CONTROL INC.

Dwn. KAUFFMAN

Date 2-28-08

Engr. J.KRAUS

Scale NONE

FAIRVIEW
PENNSYLVANIA

Description FEED THRU
RESIN SEAL FILTER

54F-779-073

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Spectrum Control:](#)

[54F-779-073](#)