

RF AMPLIFIER

MODEL QBH-1505PM

Available as: QBH-1505PM, 4 Pin TO-8 (T4)
QBH-5105PM, 4 Pin 0.450" Surfacemount (SM3)
QBH-9-1505PM, SMA Connectorized Housing (H1)

Features

- Ultra Low Phase Noise Performance
- Superior Gain Stability
- **High Output Power: +28 dBm Typical**
- Environmental Screening Available

Specifications

CHARACTERISTIC	TYPICAL Ta= 25 °C	MIN/MAX Ta = -55 °C to +85 °C
Frequency	10 - 1000 MHz	10 - 1000 MHz
Gain (dB)	13.0	12.0 Min.
Gain Flatness (dB)	±0.25	±0.75 Max.
Power @ 1 dB Comp. (dBm) (10-500 MHz) (500-1000 MHz)	28.0 26.5	25.5 Min. 25.0 Min.
Reverse Isolation (dB)	17	15 Max.
VSWR In	1.5:1	2.0:1 Max.
VSWR Out	1.5:1	2.0:1 Max.
Noise Figure (dB)	6.0	9.0 Max.
Power Vdc	+12	+12
mA	195	210 Max.

Note: Care should always be taken to effectively ground the case of each unit.
(Measured in a 50 Ohm system @ +12 Volts DC nominal unless otherwise noted)

Revision 3-13-2017 (Added QBH-5105PM)

Typical Intermodulation Performance at 25 °C

Second Order Harmonic Intercept Point +46 dBm (Typ.)
Second Order Two Tone Intercept Point +40 dBm (Typ.)
Third Order Two Tone Intercept Point +34 dBm (Typ.)


Absolute (No Damage) Maximum Ratings

Ambient Operating Temperature -55°C to +100 °C
Storage Temperature -62°C to +125 °C
DC Voltage +15 Volts
Continuous RF Input Power +13 dBm
Short Term RF Input Power 50 Milliwatts (1 Minute Max.)
Maximum Peak Power 0.1 Watt (3 µsec Max.)

Guaranteed Phase Noise Performance (dBc/Hz)

Frequency	Typical	Guarantee
10 Hz	-150	-145
100 Hz	-160	-155
1 kHz	-170	-165
10 kHz	-177	-172
100 kHz	-180	-175
1 MHz	-180	-175

Typical Performance Data



*Residual Phase Noise Test Conditions:

- Carrier Frequency: 600 MHz
- Power Output: +27.0 dBm
- Temperature: 25 °C
- Agilent ES5500 System

Legend ——— +25 °C --- +85 °C -55 °C

Linear S-Parameters Data

FREQ. MHz	S11-- Mag	S11-- Ang	S21-- Mag	S21-- Ang	S12-- Mag	S12-- Ang	S22-- Mag	S22-- Ang
10	0.11	-61.9	4.70	-172.3	0.11	8.8	0.23	151.8
250	0.02	-83.6	4.66	116.7	0.11	-34.4	0.14	148.5
500	0.01	-171.7	4.55	54.5	0.12	-70.5	0.14	124.8
750	0.02	126.7	4.49	-7.5	0.13	-109.3	0.15	97.0
1000	0.05	15.7	4.51	-70.8	0.14	-151.2	0.13	40.7
1200	0.12	-44.2	4.58	-123.8	0.15	173.5	0.13	-25.7
1300	0.16	-70.8	4.60	-151.8	0.15	155.1	0.14	-68.5



Spectrum Microwave · 2144 Franklin Drive N.E. · Palm Bay, Florida 32905 · PH (888) 553-7531 · Fax (888) 553-7532

www.SpectrumMicrowave.com Spectrum Microwave · 2707 Black Lake Place · Philadelphia, Pennsylvania 19154 · PH (215) 464-4000 · Fax (215) 464-4001

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[API Technologies:](#)

[QBH-5105PM](#)