

SPECIFICATION

Part No.	:	WSA.2400.A.101151
Product Name	:	Phoenix WSA.2400 Bluetooth I-Bar 2.4GHz Antenna
Features	:	Wi-Fi/WLAN 2.4GHz Adhesive Mount Antenna 1m RG-174 cable with RP-SMA(M) connector Adhesive Mount Low Profile for Ease of Installation Fully Customizable Cable and Connector 105*30*7.7mm RoHS Compliant



1. Introduction

The Phoenix WSA.2400 I-Bar antenna is a robust and low profile antenna operating on the 2.4GHz band for Wi-Fi, Bluetooth, and ISM applications.

The Phoenix has a slim-line design, which allows for covert and convenient installation in any application, while its omnidirectional radiation pattern and 2dBi gain ensure constant reception and transmission. It is manufactured and tested in a TS16949 first tier automotive approved facility and has undergone full PPAP design, reliability and quality audits.

The Phoenix is especially suited for applications such as:

- First-tier automotive applications
- Telematics

The Phoenix has exceptional industry performance characteristics considering its very low profile (just 7.7mm) and compact size (105*30mm).

This UV resistant antenna is designed to be mounted on glass or plastic but not on metal. It comes with strong 3M double-sided adhesive for a permanent and secure fix to your application.

Cable lengths, types and connectors are fully customizable.


2. Specification

Wi-Fi		
Frequency		2400~2500MHz
Efficiency (%)		
In free space	0.3m	72.38
	1m	57.37
	2m	40.97
	3m	29.31
	5m	15.19
On glass	0.3m	73.09
	1m	57.94
	2m	41.36
	3m	29.59
	5m	15.34
On the 2mm ABS	0.3m	71.10
	1m	56.37
	2m	40.24
	3m	28.79
	5m	14.92
Average Gain(dBi)		
In free space	0.3m	-1.40
	1m	-2.41
	2m	-3.88
	3m	-5.33
	5m	-8.19
On glass	0.3m	-1.36
	1m	-2.37
	2m	-3.83
	3m	-5.29
	5m	-8.14
On the 2mm ABS	0.3m	-1.48
	1m	-2.49
	2m	-3.95
	3m	-5.41
	5m	-8.26


Peak Gain(dBi)		
In free space	0.3m	2.18
	1m	1.18
	2m	-0.22
	3m	-1.72
	5m	-4.52
On glass	0.3m	4.67
	1m	3.67
	2m	2.17
	3m	0.77
	5m	-2.13
On the 2mm ABS	0.3m	3.21
	1m	2.21
	2m	0.74
	3m	-0.69
	5m	-3.56
Return loss		< -10 dB
VSWR		≤ 2:1
Impedance		50Ω
Polarization		Linear
Radiation Pattern		Omnidirectional
Input Power		2W
MECHANICAL		
Dimensions		105*30*7.7mm
Casing		PC/ABS
Connector		RP-SMA(M)
Cable		RG-174
Weight		50g
ENVIRONMENTAL		
Temperature Range		-40°C to 85°C

3. Antenna Characteristics


3.1 Antenna Test Setup



In free space




On glass




On the 2mm ABS


3.2 Return Loss




3.3 Efficiency



3.4 Peak Gain




3.5 Average Gain




4. Antenna Radiation Patterns


4.1 Antenna Setup (Antenna testing Setup in ETS Anechoic Chamber)



In free space



On glass




On the 2mm ABS


4.2 2D Radiation Patterns

4.2.1 In free space


XY Plane



XZ Plane




YZ Plane




4.2.2 On glass


XY Plane



XZ Plane




YZ Plane





4.2.3 On the 2mm ABS

XY Plane




XZ Plane

YZ Plane




4.3 Antenna 3D Radiation Pattern


4.3.1 In free space



2400MHz




2450MHz




2500MHz


4.3.2 On glass



2400MHz




2540MHz




2500MHz


4.3.3 On the 2mm ABS



2400MHz




2540MHz



2500MHz

5. Drawing (Unit: mm)




	Name	Material	Finish	QTY
1	Housing	PC+ABS	Black	1
2	Double Sided Adhesive	3M 1600T	Blue Liner	1
3	2.4 GHz Label	Coated Paper	Light Green	1
4	Heat Shrink Tube	PE	Black	1
5	RG174 Coaxial Cable	PVC	Black	1
6	RP-SMA(M)	Brass	Au Plated	1


6. Packaging

Packaging Specifications


1pcs WSA.2400.A.101151 per PE Bag
Bag Dimensions - 70 x 80mm
Weight - 35g




10 PE Bags per large PE Bags
10 pcs MA301.A.AB.001 per large PE Bag
large PE Bags Dimensions - 440 x 240mm
Weight - 0.44KG



10 pcs WSA.2400.A.101151 per carton
Carton - 400 x 330 x 220mm
Weight - 5.2Kg



Pallet Dimensions 120 x 100x 150cm
54 Cartons per Pallet
9 Cartons per layer
6 Layers




7. Application Note


Antenna performance versus cable length is shown below.

7.1 Return Loss


In free space



On glass




On the 2mm ABS




7.2 Efficiency


In free space



On glass




On the 2mm ABS




7.3 Peak Gain


In free space



On glass




On the 2mm ABS




7.4 Average Gain


In free space



On glass



On the 2mm ABS



Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time without notice. Taoglas reserves all rights to this document and the information contained herein.

Reproduction, use or disclosure to third parties without express permission is strictly prohibited.

© Taoglas

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Taoglas:

[WSA.2400.A.101151](#)