





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	01/17/07	
A		REVISED COLOR	5/16/11	



RECOMMENDED
PCB LAYOUT
PCB THICKNESS .031 [0.8mm]



SPECIFICATIONS:

Material:

Insulator: Hi-temp thermoplastic, rated UL 94V-0

Insulator color: Natural

Contacts: Brass

Plating:

Tin over Nickel underplate overall

Electrical:

Operating voltage: 250 VAC max

Current rating: 1 Amps max

Contact resistance: 20 mohms max

Insulation resistance: 500 Mohms min

Dielectric withstanding voltage: 500 VAC for 1 minute

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant.



A=.049 [1.25] X No. of Spaces
B=.049 [1.25] X No. of Spaces + .070 [1.80]
C=.049 [1.25] X No. of Spaces + .118 [3.00]
D=.049 [1.25] X No. of Spaces + .251 [6.40]

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

MX 1.25mm WAFER SMT RIGHT ANGLE

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				TITLE			
INCHES	HOLES			SIZE	PART NO.	REV.	
.X ± .10	ØX ± .10			X	125SH-A-XX-TR-SMT	A	
.XX ± .020	ØXX ± .015						
.XXX ± .015	ØXXX ± .010						
APPROVALS				SCALE: NTS			
DRAWN	BW	01/17/07		SHEET 1 OF 1			
CHECKED							
APPROVED							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[125SH-A-08-TR-SMT](#) [125SH-A-12-TR-SMT](#) [125SH-A-09-TR-SMT](#) [125SH-A-11-TR-SMT](#) [125SH-A-06-TR-SMT](#)
[125SH-A-14-TR-SMT](#) [125SH-A-03-TR-SMT](#) [125SH-A-15-TR-SMT](#) [125SH-A-13-TR-SMT](#) [125SH-A-05-TR-SMT](#)
[125SH-A-10-TR-SMT](#) [125SH-A-07-TR-SMT](#) [125SH-A-02-TR-SMT](#) [125SH-A-04-TR-SMT](#)