


APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	01/17/07	
A		UPDATED DRAWING	2/21/17	HR/CH
B		UPDATED DRAWING	6/4/19	AY/IL



SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-0

Insulator color: Beige

Contacts: Brass

Plating:

Tin over Nickel underplate overall

Electrical:

Voltage rating: 250V AC/DC

Current rating: 1A AC/DC

Contact resistance: 10 mohms max Initial
30 mohms max After

Insulation resistance: 1000 Mohms min

Dielectric withstanding voltage: 500 VAC for 1 minute

Temperature Rating:

-25°C to +85°C

Environmental:

Lead free, RoHS compliant.



Positions: 02 thru 15, 20, 25, 30

A = .049 [1.25] x No. of Space

B = .049 [1.25] x No. of Positions + .026 [0.65]

C = .049 [1.25] x No. of Positions + .049 [1.25]

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES

.X	± .10	Ø.X	± .10
.XX	± .020	Ø.XX	± .015
.XXX	± .015	Ø.XXX	± .010

APPROVALS

DATE

DRAWN

BW

01/17/07

CHECKED

APPROVED

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
1.25MM PITCH WAFER, DIP TYPE,
RIGHT ANGLE, TIN PLATED

SIZE

X

PART NO.

125SH-C-XX-TR

REV.

B

REF: S00099T

SCALE: NTS

SHEET 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[125SH-C-10-TR](#) [125SH-C-02-TR](#) [125SH-C-14-TR](#) [125SH-C-15-TR](#) [125SH-C-03-TR](#) [125SH-C-08-TR](#) [125SH-C-05-TR](#) [125SH-C-04-TR](#) [125SH-C-11-TR](#) [125SH-C-09-TR](#) [125SH-C-06-TR](#) [125SH-C-12-TR](#) [125SH-C-07-TR](#) [125SH-C-13-TR](#)