





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-	7741	RELEASED	04/24/07	
A		REDRAWN	4/13/09	



RECOMMENDED PCB LAYOUT



SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-0

Insulator color: White

Contacts: Brass

Plating:

Tin over Copper underplate overall

Electrical:

Operating voltage: 250 VAC max

Current rating: 3 Amps max

Insulation resistance: 1000 Mohms min

Dielectric withstanding voltage: 800 VAC for 1 minute

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant.



Positions: 2 thru 15
A= No. of Spaces x .098 [2.50]
B= No. of Positions x .098 [2.50] +.098 [2.50]

ADAM TECH

909 Railway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

2.5mm WAFER, RIGHT ANGLE 2P TO 15P

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES				Holes			
.X	± .10	ØXX	± .10	.X	± .10	ØXX	± .10
.XX	± .020	ØXX	± .015	.XX	± .020	ØXX	± .015
.XXX	± .015	ØXXX	± .010	.XXX	± .015	ØXXX	± .010
APPROVALS				DATE			
DRAWN	BW		04/24/07	CHECKED			
APPROVED							
SIZE				PART NO.			
X				25SH-C-X-X-TR			
REF: S00016T				SCALE: NTS			
				SHEET 1 OF 1			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[25SH-C-12-TR](#) [25SH-C-02-TR](#) [25SH-C-15-TR](#) [25SH-C-08-TR](#) [25SH-C-11-TR](#) [25SH-C-14-TR](#) [25SH-C-10-TR](#)
[25SH-C-09-TR](#) [25SH-C-03-TR](#) [25SH-C-13-TR](#) [25SH-C-06-TR](#) [25SH-C-07-TR](#) [25SH-C-04-TR](#) [25SH-C-05-TR](#)