





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	5/27/05	
A		REDRAWN	4/14/09	



RECOMMENDED PCB LAYOUT



SPECIFICATIONS:

Material: Insulator: PBT, rated UL 94V-0
Insulator color: Black
Contacts: Phosphor Bronze
Plating: Gold flash over Nickel underplate overall
Electrical: Current rating: 1 Amp max.
Contact resistance: 20 mohms max. initial
Insulation resistance: 5,000 Mohms min.
Dielectric withstanding voltage: 500 VAC for 1 minute
Temperature Rating: Operating temperature: -40°C to +105°C
Environmental: Lead free, RoHS compliant

Positions: 01 thru 40
A = .079 [2.00] x No. of Positions
B = .079 [2.00] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES				ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710			
HOLES .X ± .10 ØX ± .10 .XX ± .020 ØXX ± .015 .XXX ± .015 ØXXX ± .010				TITLE . .079 [2.00] SINGLE ROW RECEPTACLE STRIP . .169 [4.30] HEIGHT			
APPROVALS							
DATE							
DRAWN	SS	5/27/05		SIZE	PART NO.	REV.	
CHECKED				X	2RS1-XX-G	A	
APPROVED				REF: S00039T	SCALE: NTS	SHEET 1 OF 1	



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[2RS1-04-G](#) [2RS1-14-G](#) [2RS1-03-G](#) [2RS1-06-G](#) [2RS1-07-G](#) [2RS1-02-G](#) [2RS1-10-G](#) [2RS1-19-G](#) [2RS1-20-G](#)
[2RS1-18-G](#) [2RS1-08-G](#) [2RS1-11-G](#) [2RS1-16-G](#) [2RS1-05-G](#) [2RS1-12-G](#) [2RS1-13-G](#) [2RS1-15-G](#) [2RS1-17-G](#)
[2RS1-09-G](#)