





APPROVED: \_\_\_\_\_  
DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/7/05	
A		ADDED DIM.	4/25/13	



PCB LAYOUT



SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-0

Insulator color: White

Contacts: Brass

Plating:

Tin over Copper underplate overall

Electrical:

Operating voltage: 100 VAC max

Current rating: 2 Amps max

Contact resistance: 10 mohms max

Insulation resistance: 1,000 Mohms min @ 500 VDC

Dielectric withstanding voltage: 1,000 VAC for 1 minute

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant



Positions: 2 thru 15  
A = .079 [2.00] x No. of Positions + .075 [1.90]  
B = .079 [2.00] x No. of Spaces

**ADAM TECH**

909 Railway Avenue, Union, NJ 07083  
Phone: 908-687-5000 Fax: 908-687-5710

TITLE  
.079 [2.00] SHROUDED HEADER  
STRAIGHT, PCB

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES							
.X	± .10	ØXX	± .10	HOLD	DATE	SIZE	REV.
.XX	± .020	ØXXX	± .015			X	A
.XXX	± .015	ØXXX	± .010				
APPROVALS							
DRAWN	SS	4/7/05					
CHECKED							
APPROVED							
REF:				SCALE: NTS SHEET 1 OF 1			

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

<u><a href="#">2SH-C-02-TS</a></u>	<u><a href="#">2SH-C-03-TS</a></u>	<u><a href="#">2SH-C-04-TS</a></u>	<u><a href="#">2SH-C-06-TS</a></u>	<u><a href="#">2SH-C-13-TS</a></u>	<u><a href="#">2SH-C-16-TS</a></u>	<u><a href="#">2SH-C-08-TS</a></u>	<u><a href="#">2SH-C-09-TS</a></u>
<u><a href="#">2SH-C-14-TS</a></u>	<u><a href="#">2SH-C-05-TS</a></u>	<u><a href="#">2SH-C-10-TS</a></u>	<u><a href="#">2SH-C-07-TS</a></u>	<u><a href="#">2SH-C-15-TS</a></u>	<u><a href="#">2SH-C-12-TS</a></u>	<u><a href="#">2SH-C-11-TS</a></u>	