


APPROVED: _____

DATE: _____ TITLE: _____

CUSTOM CABLE ASSEMBLIES ARE
NON-CANCELLABLE/NON-RETURNABLE

Rev	AWO #	Description	Date	Appr
-		RELEASED	3/7/24	
A		UPDATE DRAWING	3/13/24	LH/KC
B		UPDATE DRAWING	3/15/24	LH/KC
C		ADDED SPEC.	3/19/24	LH/KC
D		ADDED SPEC.	8/21/24	LH/RC



PIN ASSIGNMENT:

P1		WIRE	P2	
Signal Name	Pin		Pin	Signal Name
GND	A1/B1/A12/B12	Black	A1/B1/A12/B12	GND
VBUS	A4/B4/A9/B9	Red	A4/B4/A9/B9	VBUS
CC	A5	Blue	A5	CC
Vconn	B5	Yellow	B5	Vconn
DP1	A6/B6	Green	A6/B6	DP1
DN1	A7/B7	White	A7/B7	DN1
SSTXp1	A2	High speed pair 1	B11	SSRXp1
SSTXn1	A3		B10	SSRXn1
SSRXp1	B11	High speed pair 2	A2	SSTXp1
SSRXn1	B10		A3	SSTXn1
SSTXp2	B2	High speed pair 3	A11	SSRXp2
SSTXn2	B3		A10	SSRXn2
SSRXp2	A11	High speed pair 4	B2	SSTXp2
SSRXn2	A10		B3	SSTXn2
SBU1	A8	Purple	B8	SBU2
SBU2	B8	Orange	A8	SBU1
SHELL		Braid	SHELL	

SPECIFICATIONS:

Connectors:

P1&P2= USB3.1 Connector Type-C Female, W/Shell, Pin: Gold plated, W/Latching, rated UL 94V-0

Insulator Color: Black, Outer molded Color: Black, PVC

Mating with CA-USB31-CMLX-CFLX-XM

Cable:

UL20276 (32AWG*1P+AL+MY)*4+32AWG*1P+32AWG*4C+24AWG*2C+A+B VW-1

O.D.: .197" [5mm], Jacket Color: Black. PVC

Electrical:

Voltage: 20V

Current: 5A

Contact resistance: 2 ohms max

Insulation resistance: 10 Mohms min, 300V DC

Mechanical:

Cable retention force: 100g downward vertical at 60CM; 40N for 1 minute

Electrical Test:

All assemblies must be 100% tested for
shorts, open continuity and physical appearance.

Environmental:

Lead free, RoHS compliant.



ADAM TECH P/N	L+T	
CA-USB31-CFLX-CFLX-1M	47.244"±1.181"	[1000±30mm]
CA-USB31-CFLX-CFLX-1.2M	47.244"±1.181"	[1200±30mm]
CA-USB31-CFLX-CFLX-2M	78.740"±1.575"	[2000±40mm]
CA-USB31-CFLX-CFLX-3M	118.110"±1.969"	[3000±50mm]
CA-USB31-CFLX-CFLX-XM	Contact factory for custom lengths	

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS
ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	± .10
.XX	± .020	Ø.XX	± .015
.XXX	± .015	Ø.XXX	± .010

DRAWN	WX	3/4/24
CHECKED	KC	3/4/24
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY
AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN
PERMISSION FROM ADAM TECH

**ADAM
TECH**

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE (HSecurLinC) CABLE, USB3.1 CONNECTOR TYPE-C FEMALE
TO USB3.1 CONNECTOR TYPE-C FEMALE, W/LATCHING
TRANSMISSION EFFICIENCY: 5G






SIZE X	PART NO. CA-USB31-CFLX-CFLX-XM	REV. D
REF: S00197C	SCALE: NTS	SHEET 1 OF 2

APPROVED: _____






DATE: _____ TITLE: _____

CUSTOM CABLE ASSEMBLIES ARE
NON-CANCELLABLE/NON-RETURNABLE

CA-USB31-CFLX-CFLX-XM
(Code see chat)

CODE	RECEPTACLE	CASE COLOR
A		JET BLACK
C		NUT BROWN
E		SIGNAL BLUE
G		BLUE GRAY
J		BEIGE

Rev	AWO #	Description	Date	Appr
SEE SHT 1 OF 2 FOR REVISION				

CODE	RECEPTACLE	CASE COLOR
B		CLARET VIOLET
D		LEAF GREEN
F		CREAM WHITE
H		YELLOW GREEN
K		CURRY

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS
ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
X ±.10	ØX ±.10
.XX ±.020	ØXX ±.015
.XXX ±.015	ØXXX ±.010

DRAWN	WX	3/4/24
CHECKED	KC	3/4/24
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY
AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN
PERMISSION FROM ADAM TECH

ADAM
TECH

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE (HSecurLinC) CABLE, USB3.1 CONNECTOR TYPE-C FEMALE
TO USB3.1 CONNECTOR TYPE-C FEMALE, W/LATCHING
TRANSMISSION EFFICIENCY: 5G

SIZE X	PART NO. CA-USB31-CFLX-CFLX-XM	REV. D
REF: S00197C	SCALE: NTS	SHEET 2 OF 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[CA-USB31-CFLA-CFLA-1M](#)