





APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	8/20/04	
A		REVISED AND REDRAWN	8/28/06	
B		REDRAWN	3/10/11	
C		UPDATE	5/19/16	AY/LL



RECOMMENDED PCB LAYOUT



POSITIONS	Dimension	
	A	B
2	NA	.262 [6.65]
4	.118 [3.00]	.380 [9.65]
6	.236 [6.00]	.498 [12.65]
8	.354 [9.00]	.616 [15.65]
10	.472 [12.00]	.734 [18.65]
12	.591 [15.00]	.852 [21.65]
14	.709 [18.00]	.970 [24.65]
16	.827 [21.00]	1.088 [27.65]
18	.945 [24.00]	1.206 [30.65]
20	1.063 [27.00]	1.325 [33.65]
22	1.181 [30.00]	1.443 [36.65]
24	1.299 [33.00]	1.561 [39.65]

SPECIFICATIONS:

Material:

Insulator: Hi-Temp Thermoplastic, rated UL 94V-0

Insulator color: Black

Contacts: Brass

Plating:

Tin over Nickel underplate overall

Electrical:

Operating voltage: 250 V

Current rating: 20 & 22 Awg: 5 Amps max

24 Awg: 4 Amps max

26 Awg: 3 Amps max

28 Awg: 2 Amps max

30 Awg: 1 Amp max

Contact resistance: 10 mohms max

Dielectric strength: 1,500 VAC for 1 minute

Mechanical:

Withdrawal Force: 2.5kg Min.

Retention force: 2.5kg min.

Mating durability cycles: 30 min.

Temperature Rating:

Operating Temperature: -25°C top +85°C

Environmental:

Lead free, RoHS compliant.



ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

.118 [3.00] DUAL ROW HEADER

HORIZONTAL, PCB TYPE

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				TITLE			
INCHES				.118 [3.00] DUAL ROW HEADER			
HOLES				HORIZONTAL, PCB TYPE			
.X ± .10				DRAWN			
.XX ± .020				DY			
.XXX ± .015				3/09/11			
.XXX ± .010				DATE			
APPROVALS				SIZE			
DRAWN				PART NO.			
CHECKED				DML-XX-A-H-T-A			
APPROVED				REV. C			
REF: S0023T				SCALE: NTS			
2				SHEET 1 OF 1			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[DML-10-A-H-T-A](#) [DML-16-A-H-T-A](#) [DML-06-A-H-T-A](#) [DML-14-A-H-T-A](#) [DML-04-A-H-T-A](#) [DML-08-A-H-T-A](#) [DML-12-A-H-T-A](#) [DML-24-A-H-T-A](#)