





APPROVED: \_\_\_\_\_

DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/7/13	
A		UPDATED DRAWING	9/25/18	HR/DH



SECTION A-A



RECOMMENDED PCB LAYOUT

Positions: 02 thru 24

A = .197 [5.00] x No. of Positions

B = .197 [5.00] x No. of Spaces

**SPECIFICATIONS:**

Material:

Insulator: PA66, rated UL 94V-0

Insulator color: Green

Contact: Brass, Tin plated.

Electrical:

Operation voltage: 300 VAC max

Current rating: 15 Amps

Contact resistance: 20 mohms max

Insulation resistance: 500 Mohms min @ 500 VDC

Dielectric withstanding voltage: 2,000 VAC for 1 minute

Temperature Rating:

Operating temperature: -40°C to +105°C

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED  
ALL DIMENSIONS ARE INCHES [MM]  
TOLERANCES: EXCEPT AS NOTED  
INCHES HOLES  
.X ± .10 ØX ± .10  
.XX ± .020 ØXX ± .015  
.XXX ± .015 ØXXX ± .010

APPROVALS

DATE

DRAWN

AY

11/7/13

CHECKED

NP

11/7/13

APPROVED

**ADAM  
TECH**  
INTERCONNECTS

909 Rahway Avenue,  
Union, NJ 07083  
Phone: 908-687-5000  
Fax: 908-687-5710

TITLE

EURO BLOCK, .197 [5.00] PITCH, VERTICAL

SIZE

X

PART NO.

EBPA-XX-C

REV.

A

REF: S00067C

SCALE: NTS

SHEET 1 OF 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[EBPA-05-C](#) [EBPA-06-C](#) [EBPA-08-C](#) [EBPA-03-C](#) [EBPA-04-C](#) [EBPA-07-C](#) [EBPA-02-C](#)