


SPEED (SECONDS)	MODEL NUMBER
15	15M5011E-4PS
30	30M5011E-4PS
60	60M5011E-4PS

SPECIFICATIONS													
WIRING	INPUT		OUTPUT			SHAFT ROTATION FOR VOLTAGE INCREASE	TERMINAL CONNECTIONS FOR INCREASING VOLTAGE AS VIEWED FROM TOP						
	VOLTS	HERTZ	VOLTS	CONSTANT CURRENT LOAD			INPUT	OUTPUT					
				MAX. AMPS	MAX. KVA								
SINGLE PHASE SERIES PARALLEL	240	50/60	0-280	100	28.0	CW	2-2	B-B					
UNLESS OTHERWISE SPECIFIED, TOLERANCE IS ± DECIMALS HOLES ANGLES DRAFT XX .000-12 .0002 .03 1° 1-1/2° XXX .005			UNITS IN [mm]			TITLE: SPECIFICATION CONTROL DRAWING MOTORIZED VARIABLE TRANSFORMER 15, 30 & 60M5011E-4PS							
MATERIAL:			ALL DIMENSIONS APPLY AFTER PLATING										
The information and design disclosed herein was originated by and is the property of STACO ENERGY PRODUCTS CO., which reserves all patent, proprietary, design, manufacturing, reproduction, use and sale rights thereto, and to any article disclosed therein except to the extent rights are expressly granted to others. The foregoing does not apply to vendor proprietary parts.						 DAYTON, OHIO U.S.A.		CUSTOMER APPROVAL		DATE			
								TIM RAU		DATE	5/21/96	FIRST USED ON	DO NOT SCALE DWG.
								CHECKER	DATE	WEIGHT APPROX.	CODE IDENT. NO. 83008	DWG. SIZE	DWG. NO.
								ENGINEER	DATE	SCALE	.2=1	SHEET 1 OF 1	D

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Staco:

M5011E-4PS