

6

5

4

3



2

1



Rev	AWO #	Description	Date	Appr
-		RELEASED	1/7/05	

APPROVED: _____

DATE: _____ TITLE: _____



PCB LAYOUT



SPECIFICATIONS:

Material:

Insulator: Hi-temp thermoplastic, rated UL 94V-0

Insulator color: Black

Contacts: Brass

Plating:

Gold flash over Nickel underplate overall

Electrical:

Operating voltage: 250 VAC max.

Current rating: 1 Amp max.

Contact resistance: 20 mohms max. initial

Insulation resistance: 5,000 Mohms min.

Dielectric withstanding voltage: 1,000 VAC for 1 minute

Temperature Rating:

Operating temperature: -40°C to +105°C

Environmental:

Lead free, RoHS compliant

Positions: 04 thru 100
A = .050 [1.27] x No. of Positions Per Row
B = .050 [1.27] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED			ADAM TECH 909 Railway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710		
INCHES			TITLE		
.X ± .10			.050 [1.27] DUAL ROW PIN HEADER		
.XX ± .020					
.XXX ± .015					
.XXX ± .015					
APPROVALS					
DRAWN					
SS					
1/7/05					
CHECKED					
APPROVED					
SIZE			REV.		
X			-		
PART NO.					
HPH2-A-XX-UA					
SCALE: NTS					
SHEET 1 OF 1					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[HPH2-B-04-UA](#) [HPH2-A-18-UA](#) [HPH2-A-04-UA-SMT](#) [HPH2-A-08-UA](#) [HPH2-A-14-UA](#) [HPH2-A-20-UA](#) [HPH2-A-16-UA](#) [HPH2-A-10-UA-SMT](#) [HPH2-A-10-UA](#)