

APPROVED: _____



DATE: _____ TITLE: _____

Part Number	Size (mm)	As supplied (mm)		After recovered (mm)		Length
		I.D (D)	W.T (W)	I.D (max) (d)	W.T (min) (w)	
HST-00-BK-X	0.8	1.0±0.2	0.15±0.05	0.6	0.25	See Order Information
HST-01-BK-X	1.0	1.5±0.3	0.20±0.05	0.7	0.33	
HST-02-BK-X	1.5	2.0±0.3	0.20±0.05	0.8	0.34	
HST-03-BK-X	2.0	2.5±0.3	0.20±0.05	1.1	0.34	
HST-04-BK-X	2.5	3.0±0.3	0.25±0.05	1.25	0.42	
HST-05-BK-X	3.0	3.5±0.3	0.25±0.05	1.5	0.42	
HST-06-BK-X	3.5	4.0±0.3	0.25±0.05	1.75	0.42	
HST-07-BK-X	4.0	4.5±0.3	0.25±0.05	2.0	0.42	
HST-08-BK-X	4.5	5.0±0.3	0.25±0.05	2.25	0.42	
HST-09-BK-X	5.0	5.5±0.3	0.28±0.05	2.5	0.52	
HST-10-BK-X	6.0	6.5±0.3	0.28±0.05	3.0	0.52	
HST-11-BK-X	7.0	7.6±0.3	0.30±0.07	3.5	0.56	
HST-12-BK-X	8.0	8.6±0.3	0.30±0.07	4.0	0.56	
HST-13-BK-X	9.0	9.6±0.3	0.30±0.07	4.5	0.56	
HST-14-BK-X	10.0	10.7±0.4	0.30±0.07	5.0	0.56	
HST-15-BK-X	11.0	11.7±0.4	0.30±0.07	5.5	0.56	
HST-16-BK-X	12.0	12.7±0.4	0.30±0.07	6.0	0.56	
HST-17-BK-X	13.0	13.7±0.4	0.35±0.08	6.5	0.69	
HST-18-BK-X	14.0	14.7±0.4	0.35±0.08	7.0	0.69	
HST-19-BK-X	15.0	15.7±0.5	0.35±0.08	7.5	0.69	
HST-20-BK-X	16.0	16.7±0.5	0.35±0.08	8.0	0.69	
HST-21-BK-X	17.0	17.7±0.5	0.35±0.08	8.5	0.69	
HST-22-BK-X	18.0	19.0±0.5	0.40±0.10	9.0	0.77	
HST-23-BK-X	20.0	21.0±0.5	0.40±0.10	10.0	0.77	
HST-24-BK-X	22.0	23.0±0.5	0.40±0.10	11.0	0.77	
HST-25-BK-X	25.0	26.0±1.0	0.45±0.10	12.5	0.87	
HST-26-BK-X	28.0	29.0±1.0	0.45±0.10	14.0	0.87	
HST-27-BK-X	30.0	31.5±1.0	0.45±0.10	15.0	0.87	
HST-28-BK-X	35.0	36.5±1.0	0.50±0.10	17.5	0.97	
HST-29-BK-X	40.0	42.0±1.5	0.50±0.10	20.0	0.97	
HST-30-BK-X	45.0	47.0±1.5	0.50±0.10	22.5	0.97	
HST-31-BK-X	50.0	53.0±2.0	0.55±0.10	25.0	0.97	
HST-32-BK-X	60.0	63.0±3.0	0.60±0.15	30.0	1.17	
HST-33-BK-X	70.0	71.0±3.0	0.60±0.15	35.0	1.17	
HST-34-BK-X	80.0	81.0±3.0	0.65±0.15	40.0	1.20	
HST-35-BK-X	90.0	91.0±3.0	0.75±0.15	45.0	1.30	
HST-36-BK-X	100	101.0±3.0	0.75±0.15	50.0	1.30	
HST-37-BK-X	120	121.0±4.0	0.80±0.20	60.0	1.40	
HST-38-BK-X	150	151.0±4.0	0.80±0.20	75.0	1.50	
HST-39-BK-X	180	181.0±4.0	0.80±0.20	90.0	1.60	

SPECIFICATIONS:
Material: Polyolefin
Electrical:
Shrinkage: 2:1
UL Style: UL224, 105°C VW-1 600V
Temperature Rating:
Operating temperature: -55°C to +125°C
Environmental:
Lead free, RoHS compliant



Rev	AWO #	Description	Date	Appr
-		RELEASED	1/28/21	
A		ADDED SPEC.	5/24/21	LH/RC
B		ADDED PAGE 2	7/9/21	LH/RC
C		ADDED LENGTH 18MM	6/15/23	LH/NL
D		UPDATE SPEC.	8/8/23	LH/RC
E		ADDED LENGTH	3/19/24	LH/NL



HST-00-BK-X (0.8 SIZE only Black)

HST-XX-XX-X

TYPE SEE CHART

Color
BK=Black
WT=White
RD=Red
BU=Blue
YW=Yellow
GN=Green
BN=Brown
OR=Orange
VT=Violet
GY=Gray
CL=Clear

Length
1= 1FT(12"inch)
2= 2FT(24"inch)
3= 3FT(36"inch)
4= 4FT(48"inch)
A= 18mm
B= 50.8mm
C= 12.7mm

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS
ARE MILLIMETERS. TOLERANCES: EXCEPT AS NOTED

DRAWN	LH	1/28/21
CHECKED	RC	1/28/21
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY
AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN
PERMISSION FROM ADAM TECH

**ADAM
TECH**

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE		REV.	
HEAT SHRINK TUBING, SINGLE WALL, FLAME RETARDANT POLYOLEFIN		E	
SIZE X	PART NO. HST-XX-XX-X		
REF:	-	SCALE:	NTS
		SHEET 1 OF 2	

6

5

4

3

2

1

Rev

AWO #

Description

Date


Appr

APPROVED: _____

DATE: _____ TITLE: _____

RELEASED

CARTON



PO:XXXXXXXX (SOXXXXXX)	ADAM TECH
ADAM TECH P/N: HST-XX-XX-4	
Q'TY: XXXX PCS	
LOT DTAE: XXXX	
POLYOLEFIN HEAT SHRINK TUBING	RoHS

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS
ARE MILLIMETERS. TOLERANCES: EXCEPT AS NOTED

DRAWN

LH

1/28/21

CHECKED

RC

1/28/21

APPROVED

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY
AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN
PERMISSION FROM ADAM TECH**ADAM**
TECH909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE

HEAT SHRINK TUBING, SINGLE WALL,
FLAME RETARDANT POLYOLEFINSIZE
X

PART NO.

HST-XX-XX-X

REV.
E

REF:

-

SCALE: NTS

SHEET 2 OF 2

6

5

4

3

2

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[HST-04-BK-4](#) [HST-07-WT-4](#) [HST-13-BK-4](#) [HST-16-WT-4](#) [HST-06-WT-4](#) [HST-23-WT-4](#) [HST-05-WT-4](#) [HST-14-BK-](#)
[4](#) [HST-15-BK-4](#) [HST-01-WT-4](#) [HST-10-BK-4](#) [HST-02-WT-4](#) [HST-20-BK-4](#) [HST-03-WT-4](#) [HST-16-BK-4](#) [HST-17-](#)
[BK-4](#) [HST-06-BK-4](#) [HST-07-BK-4](#) [HST-24-BK-4](#) [HST-08-BK-4](#) [HST-11-WT-4](#) [HST-05-BK-4](#) [HST-08-WT-4](#) [HST-22-](#)
[BK-4](#) [HST-13-WT-4](#) [HST-09-WT-4](#) [HST-11-BK-4](#) [HST-18-BK-4](#) [HST-18-WT-4](#) [HST-03-BK-4](#) [HST-19-BK-4](#) [HST-](#)
[02-BK-4](#) [HST-12-BK-4](#) [HST-25-WT-4](#) [HST-24-WT-4](#) [HST-10-WT-4](#) [HST-19-WT-4](#) [HST-04-WT-4](#) [HST-22-WT-4](#)
[HST-17-WT-4](#) [HST-14-WT-4](#) [HST-15-WT-4](#) [HST-23-BK-4](#) [HST-25-BK-4](#) [HST-01-BK-4](#) [HST-20-WT-4](#) [HST-09-BK-4](#)
[HST-12-WT-4](#)