





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	4/8/05	
A		REVISED DIM.	8/11/11	



PCB LAYOUT



SPECIFICATIONS:

Material: Insulator: Nylon, rated UL 94V-2
Insulator color: Ivory
Contacts: Brass
Plating: Tin over Copper underplate overall
Electrical: Operating voltage: 250 VAC max
Current rating: 3 Amps max
Insulation resistance: 1,000 Mohms min
Dielectric withstanding voltage: 1,000 VAC for 1 minute
Operating temperature: -25°C to +85°C
Environmental: Lead free, RoHS compliant

Positions: 2 thru 20
A = .100 [2.54] x No. of Positions
B = .100 [2.54] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES .X ± .10 .XX ± .020 .XXX ± .015 APPROVALS DRAWN SS CHECKED APPROVED				Holes ØX ± .10 ØXX ± .015 ØXXX ± .010 DATE 4/8/05 SIZE X PART NO. LHA-XX-TS REV. A			
ADAM TECH 909 Railway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710 100 [2.54] LOCKING HEADER STRAIGHT, PCB				REF: S00016T SCALE: NTS SHEET 1 OF 1			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[LHA-09-TS](#) [LHA-06-TS](#) [LHA-03-TS](#) [LHA-08-TS](#) [LHA-10-TS](#) [LHA-04-TS](#) [LHA-05-TS](#) [LHA-02-TS](#) [LHA-07-TS](#) [LHA-12-TS](#) [LHA-15-TS](#) [LHA-11-TS](#) [LHA-13-TS](#) [LHA-20-TS](#) [LHA-14-TS](#)