


50 Ω nominal input / conjugate match balun to STLC2690

Datasheet – production data



Description

The BAL-2690D3U is a balun designed to transform single ended signals to differential signals in Bluetooth applications.

The BAL-2690D3U has been customized for the STLC2690 Bluetooth transceiver with 0.8 dB insertion losses in the bandwidth (2400 MHz - 2500 MHz) and with a specific requirement for the SCC22 parameter.

The BAL-2690D3U has been designed using STMicroelectronics IPD (integrated passive device) technology on non conductive glass substrate to optimize RF performance.

Features

- 50 Ω nominal input / 30+j25 output differential impedance
- Low insertion loss
- Low amplitude imbalance
- Low phase imbalance
- Small footprint: BAL-2690D3U < 1 mm²

Benefits

- Very low profile (<700 μ m)
- High RF performances
- RF BOM and area reduction

Applications

Balun transformer for applications such as:

- Bluetooth STLC2690
- Mobile phone

Figure 1. Top view





Figure 2. Application schematic



TM: IPAD is a trademark of STMicroelectronics

1 Characteristics




Table 1. Absolute maximum rating (limiting values)

Symbol	Parameter	Value			Unit
		Min.	Typ.	Max.	
P_{IN}	Input power RF_{IN}			20	dBm
V_{ESD}	ESD ratings MIL STD883G (HBM: C = 100 pF, R = 1.5 k Ω , air discharge)	2000			V
	ESD ratings machine model, (MM: C = 200 pF, R = 25 Ω , L = 500 nH)	500			
	ESD ratings charged device model (JESD22-C101D)	500			
T_{OP}	Operating temperature	-40		+125	$^{\circ}C$

Table 2. Electrical characteristics - RF performance ($T_{amb} = 25^{\circ}C$)

Symbol	Parameter	Value			Unit
		Min.	Typ.	Max.	
Z_{OUT}	Nominal differential output impedance		30 + j25		Ω
Z_{IN}	Nominal input impedance		50		
F	Frequency range (bandwidth)	2402	2441	2480	MHz
I_L	Insertion loss in bandwidth		0.8	1.1	dB
Ripple	Ripple in bandwidth			0.6	dB
R_L	Return loss in bandwidth	14			dB
Φ_{imb}	Phase imbalance	-10		10	$^{\circ}$
A_{imb}	Amplitude imbalance	-1		1	dB
R_{CMRR}	Common mode rejection ratio (SSC12)	20			dB
S_{CC22}	Magnitude for common mode harmonic rejection coefficient at 2fo	0.7		1	dB
	Phase for common mode harmonic rejection coefficient at 2fo	-45		0	$^{\circ}$

1.1 Measurements



2 Package information

- Epoxy meets UL94, V0
- Lead-free package

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK® packages, depending on their level of environmental compliance. ECOPACK® specifications, grade definitions and product status are available at: www.st.com. ECOPACK® is an ST trademark.

2.1 Flip-Chip package information

Figure 9. Flip-Chip package outline




Table 3. Flip-Chip package mechanical data

Parameter	Description	Min.	Typ.	Max.	Unit
A	Bump height + substrate thickness	0.570	0.630	0.690	mm
A1	Bump height	0.155	0.205	0.255	mm
A2	Substrate thickness		0.400		mm
b	Bump diameter	0.215	0.255	0.295	mm
D	Y dimension of the die	0.860	0.910	0.960	mm
D1	Y pitch		0.474		mm
E	X dimension of the die	0.860	0.910	0.960	mm
E1	X pitch		0.474		mm
SE			0.237		mm
fD	Distance from bump to edge of die on Y axis		0.213		mm
fE	Distance from bump to edge of die on X axis		0.213		mm
ccc				0.05	mm
\$			0.025		mm

Figure 10. Footprint




Figure 11. Footprint - 3 mils stencil - non solder mask defined

Copper pad diameter:
220 μm recommended
180 μm minimum
260 μm maximum

Solder mask opening:
320 μm recommended
300 μm minimum
340 μm maximum

Solder stencil opening:
220 μm recommended




Figure 12. Footprint - 3 mils stencil - solder mask defined

Solder mask opening:
220 μm recommended
180 μm minimum
260 μm maximum

Copper pad diameter:
320 μm recommended
300 μm minimum

Solder stencil opening:
220 μm recommended




Figure 13. Footprint - 5 mils stencil - non solder mask defined

Copper pad diameter:
220 μm recommended
180 μm minimum
260 μm maximum

Solder mask opening:
320 μm recommended
300 μm minimum
340 μm maximum

Solder stencil opening:
330 μm recommended*

*depending on paste, it can go down to 270 μm




Figure 14. Footprint - 5 mils stencil - solder mask defined

Solder mask opening:
220 μm recommended
180 μm minimum
260 μm maximum

Copper pad diameter:
320 μm recommended
300 μm minimum

Solder stencil opening:
330 μm recommended*

*depending on paste, it can go down to 270 μm




Figure 15. Recommend land pattern (used for balun characterization)




Figure 16. Example of transceiver application board land pattern





Figure 17. Marking



3 Ordering information

Table 4. Ordering information

Order code	Marking	Package	Weight	Base qty	Delivery mode
BAL-2690D3U	RP	Flip-Chip	1.02 mg	5000	Tape and reel

4 Revision history

Table 5. Document revision history

Date	Revision	Changes
25-Jan-2010	1	First issue.
08-Feb-2010	2	Updated Table 1 and Figure 16 .
21-Sep-2015	3	Updated Figure 9 and Figure 9 . Added Figure 11 , Figure 12 , Figure 13 , Figure 14 and Table 3 .

IMPORTANT NOTICE – PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries (“ST”) reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST’s terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers’ products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2015 STMicroelectronics – All rights reserved

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[STMicroelectronics:](#)

[BAL-2690D3U](#)