






APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	8/26/11	
A		REDRAWN	12/26/14	AY/NP



Recommended PCB Layout



SPECIFICATIONS:

Material:

Insulator: Hi-temp thermoplastic, rated UL 94V-0

Insulator color: Black

Contacts: Copper Alloy

Shell: Copper Alloy, Nickel Plated

Plating:

Gold Flash over Nickel underplate on contact area,

Tin over Copper underplate on PCB tails.

Electrical:

Voltage rating: 30 VDC

Current rating: 1 Amps max

Contact resistance: 50 Mohms Max.

Insulation resistance: 100 Mohms Min.

Dielectric withstanding voltage: 300 VAC for 1 minute

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS		DATE
DRAWN	TW	8/26/11
CHECKED	AY	8/26/11
APPROVED		

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE
MINI USB, TYPE B, 5PIN, VERTICAL
PCB MOUNT, LONG SHIELD PIN

SIZE	PART NO.	REV.
X	MUSB-B5-S-VT-LSP	A
REF: S00097C		SCALE: NTS
SHEET 1 OF 1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[MUSB-B5-S-VT-LSP](#)