






APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	2/17/17	
A		UPDATE DRAWING	3/16/17	AY/MC
B		UPDATE DRAWING	4/3/19	AY/TY




MICRO SIM CARD



RECOMMENDED PCB LAYOUT

[SIM Card Pin Assignments]

PIN	Name
C1	Vcc
C2	RST
C3	CLK
C4	Reserved
C5	GND
C6	Vpp
C7	I/O
C8	Reserved



SPECIFICATIONS:

Material:
Insulation: Hi-Temp Thermoplastic, Color: Black
Contact: Copper Alloy
Shell: Stainless Steel, Nickel plated over all
Gold flash on solder area

Plating:
Gold flash over Nickel underplate overall

Electrical:
Voltage rating: 30 VAC
Current rating: 0.5 A
Contact resistance: 100 mohms max.
Insulation resistance: 1000 Mohms min @ 500 VDC
Dielectric withstanding voltage: 500 VAC for 1 minute
Environmental:
Lead free, RoHS compliant



PACKAGED ON TAPE & REEL

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED		ADAM TECH INTERCONNECTS		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
INCHES .X ± .10 .XX ± .020 .XXX ± .015		HOLES Ø.X ± .10 Ø.XX ± .015 Ø.XXX ± .010		TITLE NANO SIM CARD CONNECTOR, 6 PIN PUSH PUSH TYPE, H= 1.37MM	
APPROVALS		DATE		SIZE X	
DRAWN AY		2/17/17		PART NO. NSCCP-D-06-G-SMT-SW-T/R	
CHECKED MC		2/17/17		REV. B	
APPROVED				REF: S00275T	
				SCALE: NTS	
				SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[NSCCP-D-06-G-SMT-SW-T/R](#)