





Rev	AWO #	Description	Date	Appr
-		RELEASED	6/22/15	

APPROVED: _____


DATE: _____ TITLE: _____



RECOMMENDED PCB LAYOUT



SECTION A-A



SPECIFICATIONS:

Material:

Insulator: Hi-Temp Thermoplastic, Glass reinforced, rated UL 94V-0

Insulator color: Black

Contacts: Copper Alloy

Plating:

Tin over Copper underplate overall

Electrical:

Current rating: 1 Amps max

Contact resistance: 30 mohms max initial

Insulation resistance: 500 Mohms min

Dielectric withstanding voltage: 500 VAC for 1 minute

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant

Positions: 2 thru 36
A = .039 [1.00] x No. of Spaces
B = A + .083 [2.10]
C = A + .157 [4.00]

ADAM TECH

909 Railway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

LIF FLEX CIRCUIT CONNECTOR
SIDE ENTRY, SMT

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				INCHES				Holes			
.X	± .10	ØXX	± .10	.XX	± .020	ØXXX	± .015	.XXX	± .015	ØXXX	± .010
APPROVALS				DATE							
DRAWN	AY		6/22/15								
CHECKED	AY1		6/22/15								
APPROVED											
TITLE				SIZE				PART NO.			
X				X				PCB-C5-XX-SA-SMT			
REF: S00165C				SCALE: NTS				SHEET 1 OF 1			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[PCB-C5-07-SA-SMT](#) [PCB-C5-20-SA-SMT](#) [PCB-C5-08-SA-SMT](#) [PCB-C5-05-SA-SMT](#) [PCB-C5-12-SA-SMT](#) [PCB-C5-10-SA-SMT](#) [PCB-C5-26-SA-SMT](#) [PCB-C5-06-SA-SMT](#) [PCB-C5-09-SA-SMT](#) [PCB-C5-11-SA-SMT](#) [PCB-C5-04-SA-SMT](#) [PCB-C5-18-SA-SMT](#) [PCB-C5-22-SA-SMT](#)