

Rev	AWO #	Description	Date	Appr
-		RELEASED	1/23/14	SLS

6

5

4

3

2

1

APPROVED: \_\_\_\_\_

DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

D

D

C




C

B

B

A

A



RECOMMENDED PCB LAYOUT

**SPECIFICATIONS:**

Material:

Body: Zinc Alloy, Nickel plated

Contacts: Brass, Gold plated

Insulator: POM

Electrical:

Nominal Impedance: 75 ohms

Frequency range: 0–1 GHz

Working Voltage: 500 VRMS max

VSWR: 1.3 Max.

Dielectric Withstanding Voltage: 1500 VRMS min.

Contact Resistance: 3 Milliohms max. (Center Contact)

2 Milliohms max. (Outer Contact)

Insulator Resistance: 5,000 Megohms min.

Temperature Range: –55°C to +155°C

Environmental:

Lead free, RoHS compliant.



**ADAM TECH**

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE

BNC CONNECTOR, VERTICAL PCB,  
75Ω, MACHINE CONTACT

SIZE PART NO.

X RF1-95-T-00-75 -MC

REV.

-

REF.

SCALE: NTS

SHEET 1 OF 1

6

5

4

3

2

1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Adam Tech:](#)

[RF1-95-T-00-75-MC](#)