




Description

The SM2T3V3A is a Transil diode designed specifically for portable equipment and miniaturized electronic devices subject to ESD transient overvoltages. Its low stand-off voltage makes it suitable for low voltage applications very sensitive to EOS and ESD events.

Transil diodes provide high overvoltage protection by clamping action.

Features

- Unidirectional Transil diode
- High peak pulse power: 200 W (10/1000 μ s)
- Stand-off voltage 3.3 V
- Low clamping factor V_{CL}/V_{BR}
- Fast response time
- JEDEC registered package outline

TM: Transil is a trademark of STMicroelectronics

1 Characteristics

Table 1. Absolute rating (limiting value)

Symbol	Parameter		Value	Unit
P_{PP}	Peak pulse power dissipation ⁽¹⁾	$T_j \text{ initial} = T_{amb}$	200	W
P	Power dissipation on infinite heatsink	$T_{amb} = 100^\circ\text{C}$	2.5	W
I_{FSM}	Non repetitive surge peak forward current	$t_p = 10 \text{ ms}$ $T_j \text{ initial} = T_{amb}$	25	A
T_{stg} T_j	Storage temperature range Maximum operating junction temperature		-65 to +175 150	$^\circ\text{C}$
T_l	Lead solder temperature (10 seconds duration)		260	$^\circ\text{C}$


1. 10/1000 μs pulse waveform

Table 2. Thermal resistance

Symbol	Parameter	Value	Unit
$R_{th(j-l)}$	Junction to leads	20	$^\circ\text{C/W}$
$R_{th(j-a)}$	Junction to ambient on PCB with recommended pad layout	250	$^\circ\text{C/W}$

Table 3. Electrical characteristics - parameters ($T_{amb} = 25^\circ\text{C}$)

Symbol	Parameter
V_{RM}	Stand-off voltage.
V_{BR}	Breakdown voltage.
V_{CL}	Clamping voltage.
I_{RM}	Leakage current @ V_{RM} .
I_{PP}	Peak pulse current.
αT	Voltage temperature coefficient
V_F	Forward voltage drop


Table 4. Electrical characteristics - values ($T_{amb} = 25^\circ\text{C}$)


Order code	$I_{RM} \text{ max @ } V_{RM}$		$V_{BR} \text{ min @ } I_R^{(1)}$		$V_{CL} \text{ max @ } I_{PP} \text{ 10/1000 } \mu\text{s}$		$V_{CL} \text{ max @ } I_{PP} \text{ 10/1000 } \mu\text{s}$		$\alpha T \text{ max}^{(2)}$	$C \text{ max}^{(3)}$
	μA	V	V	mA	V	A	V	A	$10^{-4}/^\circ\text{C}$	pF
SM2T3V3A	500	3.3	3.6	1	6.5	25	6.8	30	-5.3	2500

1. Pulse test $t_p < 50 \text{ ms}$

2. $\Delta V_{BR} = \alpha T * (T_{amb} - 25) * V_{BR} (25^\circ\text{C})$

3. $V_R = 0 \text{ V}$, $F = 1 \text{ MHz}$

Figure 1. Pulse waveform



2 Package information

- Epoxy meets ul94, v0
- Band indicates cathode

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK® packages, depending on their level of environmental compliance. ECOPACK® specifications, grade definitions and product status are available at: www.st.com. ECOPACK® is an ST trademark.

Figure 2. Package dimensions - parameters





Table 5. Package dimensions - values

Ref.	Dimensions					
	Millimetres			Inches		
	Min.	Typ.	Max.	Min.	Typ.	Max.
A	0.85	1.00	1.15	0.033	0.039	0.045
A1	-0.05		0.105	-0.002		0.002
b	0.40		0.65	0.016		0.025
b2	0.70		1.00	0.027		0.039
c	0.10		0.25	0.004		0.010
D	1.75	1.90	2.05	0.069	0.007	0.081
E	1.75	1.90	2.05	0.069	0.007	0.081
H	3.60	3.75	3.90	0.142	0.148	0.154
L	0.50	0.63	0.80	0.047	0.025	0.031
L2	1.20	1.35	1.50	0.047	0.053	0.059
L3		0.50 ref			0.019 ref	
R	0.07			0.003		
R1	0.07			0.003		

Figure 3. Recommended footprint (dimensions in mm)



3 Ordering information

Table 6. Ordering information

Order code	Marking	Package	Weight	Base quantity	Delivery mode
SM2T3V3A	MUL	STmite	15.5 mg	12000	Tape and reel

4 Revision history

Table 7. Document revision history

Date	Revision	Changes
10-Oct-2005	1	First Issue
09-Dec-2010	2	Cathode band added to package illustration.
10-Aug-2015	3	Updated features on cover page. Minor text changes

IMPORTANT NOTICE – PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2015 STMicroelectronics – All rights reserved

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[STMicroelectronics:](#)

[SM2T3V3A](#)