
## Multilayer Organic (MLO®) Diplexers 0805 CDMA





#### **MLO® TECHNOLOGY**

The 0603 diplexer is a best in class low profile multilayer organic passive device that is based on KYOCERA AVX patented multilayer organic high density interconnect technology. The MLO™ diplexer uses high dielectric constant and low loss materials to realize high Q passive printed elements such as inductors, and capacitors in a multilayer stack up. The MLO™ diplexers can support multiple wireless standards such as WCDMA, CDMA, WLAN, GSM, and BT. These diplexers are less than 0.5mm in height and are ideally suited for band switching for dual band systems. All diplexers are expansion matched to printed circuit boards thereby resulting in improved reliability vs. ceramic and Si components.


#### **APPLICATIONS**

Multiband applications including WCDMA, WLAN, WiMax, GPS, and cellular bands

## LAND GRID ARRAY ADVANTAGES

- · Low Insertion Loss
- · Excellent Solderability
- · Low Parasitics
- · Low Profile





#### **OUALITY INSPECTION**

Finished parts are 100% tested for electrical parameters and visual characteristics.


#### **OPERATING TEMPERATURE**

-40°C to +85°C

### **TERMINATION**

Finishes available in Ni Au, Ni Sn and OSP coatings which are compatible with automatic soldering technologies which include reflow, wave soldering, vapor phase and manual.


#### **ORIENTATION IN TAPE**



## **POWER CAPACITY**

4.5W Maximum

## COMPONENT DIMENSIONS AND FUNCTIONS



Terminal No.	Terminal Name
1	High Frequency Port
2	GND
3	Low Frequency Port
4	GND
5	Common Port
6	GND


## PART NUMBER: DP05A19207TR


Specification @ 25°C	
Size [mm(inches)]	2.12 x 1.28 (0.083 x 0.050)
Height [mm(inches)]	0.55 (0.021)
Volume (mm^3)	1.5
Frequency Range (F1) (MHz)	859±35
Frequency Range (F2) (MHz)	1920±70
Insertion Loss (F1, at Fc) (dB)	-0.4
Insertion Loss (F2, at Fc) (dB)	-0.6
Attenuation (F1) at (F2) (dB)	-23
Attenuation (F2) at (F1) (dB)	-23
VSWR (Input @ F1)	1.4
VSWR (Input @ F2)	1.3
VSWR (Lowband @ F1)	1.4
VSWR (Highband @ F2)	1.4


# Multilayer Organic (MLO®) Diplexers 0805 CDMA



## **S PARAMETER MEASUREMENTS**







Note: Measurements were taken using an Anritsu 4 port VNA; Diplexer was mounted on a custom evaluation board. To reduce systematic errors from the VNA, the coaxial measurement cables, and evaluation board, a Short-Open-Load-Thru (SOLT) calibration was performed, using a custom fabricated calibration substrate. This is the most common coaxial calibration methods.

# **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

# Kyocera AVX:

DP05A19207TR/500 DP05A19207TR DP05A1920TTR/500 DP05A1920TTR DP05A1920TTR\500