


RF/Microwave Capacitors

RF/Microwave Multilayer Capacitors (MLC)

800C Series NP0 Porcelain, High RF Power Ultra-Low ESR



GENERAL DESCRIPTION

KYOCERA AVX's 800 C Series offers superb performance in demanding high RF power applications requiring consistent and reliable operation. The combination of highly conductive metal electrode systems, optimized case geometries, and proprietary dielectrics, yields the lowest ESR. KYOCERA AVX's new NP0 low loss rugged dielectrics are designed to provide superior heat transfer in high RF power applications. Ultra-low ESR and superior thermal performance ensure that the 800C Series products are your best choice for high RF power applications from VHF through microwave frequencies.

TYPICAL APPLICATIONS

- Bypass
- Coupling
- Tuning
- DC Blocking
- Impedance Matching

TYPICAL CIRCUIT APPLICATIONS

- HF/RF Power Amplifiers
- Transmitters
- Antenna Tuning
- Plasma Chambers
- Medical (MRI coils)

ENVIRONMENTAL TEST

Thermal Shock	MIL-STD-202, Method 107, Condition A.
Moisture Resistance	MIL-STD-202, Method 106.
Low Voltage Humidity	MIL-STD-202, Method 103, Condition A, with 1.5 Volts DC applied while subjected to an environment of 85°C with 85% relative humidity for 240 hours min.
Life Test	MIL-STD-202, Method 108, for 2000 hours, at 125°C. Voltage applied. 200% of WVDC for capacitors rated at 500 volts DC or less. 120% of WVDC for capacitors rated at 1250 volts DC or less. 100% of WVDC for capacitors rated above 1250 volts DC.

FEATURES

- Case C Size (.250" x .250")
- High Q
- Low ESR/ESL
- High RF Power
- 3600 WVDC
- Capacitance Range: 2.2 pF to 3000 pF
- Ultra-Stable Performance
- High RF Current/Voltage
- High Reliability
- RoHS Compliant, Pb free

PACKAGING OPTIONS



Tape & Reel



Tray
(180 pcs)



ENVIRONMENTAL CHARACTERISTICS

Quality Factor (Q)	Greater than 5,000 (2.2 pF to 1000 pF) @ 1 MHz. Greater than 5,000 (1100 pF to 3000 pF) @ 1 KHz.
Temperature Coefficient of Capacitance (TCC)	0 ±30 PPM/°C (-55°C to +125°C)
Insulation Resistance (IR)	2.2 pF to 3000 pF: 10 ⁵ Megohms min. @ +25°C at rated WVDC. 10 ⁴ Megohms min. @ +125°C at rated WVDC. Max. test voltage is 500 VDC.
Working Voltage (WVDC)	See Capacitance Values Table
Dielectric Withstanding Voltage (DWV)	250% of WVDC for capacitors rated at 500 volts DC or less for 5 seconds. 150% of WVDC for capacitors rated above 500 volts DC and ≤1250 volts DC for 5 seconds. 120% of WVDC for capacitors rated above 1250 volts DC for 5 seconds.
Retrace	Less than ±(0.02% or 0.02 pF), whichever is greater.
Aging Effects	None
Piezoelectric Effects	None
Capacitance Drift	±(0.02% or 0.02 pF), whichever is greater.
Operating Temperature Range	From -55°C to +125°C (No derating of working voltage).
Termination Styles	See Mechanical Configurations
Terminal Strength	Terminations for chips withstand a pull of 10 lbs. min., 20 lbs. typical, for 5 seconds in direction perpendicular to the termination surface of the capacitor. Test per MIL-STD-202, method 211.

CAPACITANCE VALUES

CAP CODE	CAP (pF)	TOL.	RATED WVDC	CAP CODE	CAP (pF)	TOL.	RATED WVDC	CAP CODE	CAP (pF)	TOL.	RATED WVDC
2R2	2.2	B, C, D	3600	240	24	F, G, J, K	3600	241	240	F, G, J, K	1000
2R4	2.4			270	27			271	270		
2R7	2.7			300	30			301	300		
3R0	3.0			330	33			331	330		
3R3	3.3			360	36			361	360		
3R6	3.6			390	39			391	390		
3R9	3.9			430	43			431	430		
4R3	4.3			470	47			471	470		
4R7	4.7			510	51			511	510		
5R1	5.1			560	56			561	560		
5R6	5.6			620	62		621	620			
6R2	6.2			680	68		681	680			
6R8	6.8			750	75		751	750			
7R5	7.5			820	82		821	820			
8R2	8.2			910	91		911	910			
9R1	9.1			101	100		102	1000			
100	10			111	110		112	1100			
110	11			121	120		122	1200			
120	12	131		130	152		1500				
130	13	151		150	182		1800				
150	15	161		160	222		2200				
160	16	181		180	242		2400				
180	18	201	200	272	2700						
200	20	221	220	302	3000						
220	22									500	

HOW TO ORDER

800

C

220

J

TN

3600

X

T

Series

Case Size

Capacitance

Capacitance Tolerance Code

See mechanical dimensions below

EIA Capacitance Code in pF.
First two digits = significant figures or "R" for decimal place.
Third digit = number of zeros or after "R" significant figures

Packaging

Laser Marking (Optional)

WVDC

Termination Code

T = Tape and Reel, 500 pc. qty.
Surface Mount Termination Only
Please see last Column Mechanical Configuration Table for other options

Please see 2nd Column Mechanical Configuration Table

Code	B	C	D	F	G	J	K
Tol.	±0.1 pF	±0.25 pF	±0.5 pF	±1%	±2%	±5%	±10%

The above part number refers to a 800 C Series (case size C) 22 pF capacitor, J tolerance (±5%),3600 WVDC, with TN termination (RoHS Compliant, Tin Plated over Non-Magnetic Barrier Termination), laser marking and T&R packaging.









RF/Microwave Capacitors

RF/Microwave Multilayer Capacitors (MLC)

800C Series NP0 Porcelain, High RF Power Ultra-Low ESR









MECHANICAL CONFIGURATIONS

Series & Case Size	Term. Code	Case Size & Type	Outlines W/T Is A Termination Surface	Body Dimensions Inches (mm)			Lead And Termination Dimensions And Materials				
				Length (L)	Width (W)	Thickness (T)	Overlap (Y)	Materials	Pkg Type	Pkg Code	
800C	T	<div>C</div> <div></div> <div>Solderable Barrier</div>	<div>Y→ ←</div> <div></div> <div>W</div> <div>→ L ←</div> <div>→ T ←</div>	230+.025 -.010 (5.84+0.64-0.25)	250 ±.015 (6.35 ±0.38)	.200 (5.08) max.	.040 (1.02) max.	RoHS Compliant Tin Plated over Nickel Barrier Termination	T&R, 250 or 500 pcs Tray, 36 or 180 pcs	T250 or T J36 or J180	
800C	MS	<div>C</div> <div></div> <div>Microstrip</div>	<div>↓</div> <div></div> <div>W_L</div> <div>→ L ←</div> <div>↓</div> <div></div> <div>T_L</div> <div>→ T ←</div>	245 ±.025 (6.22 ±0.64)				Leads are Attached with High Temperature Solder	High Purity Silver Leads L _L = .500 (12.7) min. W _L = .240 ±.005 (6.10 ±.127) T _L = .004 ±.001 (.102 ±.025)	Tray, 24 or 60 pcs	J24 or J60
800C	AR	<div>C</div> <div></div> <div>Axial Ribbon</div>	<div>↓</div> <div></div> <div>W_L</div> <div>→ L ←</div> <div>↓</div> <div></div> <div>T_L</div> <div>→ T ←</div>						Silver Leads L _L = .500 (12.7) min. W _L = ** See below T _L = .004 ±.001 (.102 ±.025)	Tray, 24 or 60 pcs	J24 or J60

Custom lead styles and lengths are available; consult factory. All leads are high purity silver attached with high temperature solder and are RoHS compliant.

** $W_L = .110$ (2.79) for capacitance values ≤ 680 pF; $W_L = .130$ (3.30) for capacitance values > 680 pF

NON-MAGNETIC MECHANICAL CONFIGURATIONS

Series & Case SIZE	Term. Code	Case Size & Type	Outlines W/T is a Termination Surface	Body Dimensions Inches (mm)			Lead and Termination Dimensions And Materials			
				Length (L)	Width (W)	Thickness (T)	Overlap (Y)	Materials	Pkg Type	Pkg Code
800C	TN	 Non-Mag Solderable Barrier.		230+.025-.010 (5.84+0.64-0.25)	50 ±.015 (6.35 ±0.38)	.200 (5.08) max.	.040 (1.02) max.	RoHS Compliant Tin Plated over Non-Magnetic Barrier Termination	T&R, 250 or 500 pcs Tray, 36 or 180 pcs	T250 or T J36 or J180
800C	MN	 Non-Mag Microstrip245		±.025 (6.22 ±0.64)				High Purity Silver Leads $L_L = .500$ (12.7) min. $W_L = .240 \pm .005$ (6.10 ±.127) $T_L = .004 \pm .001$ (.102 ±.025) Leads are Attached with High Temperature Solder	Tray, 24 or 60 pcs	J24 or J60
800C	AN	 Non-Mag Axial Ribbon		245 ±.025 (6.22 ±0.64)				Silver Leads $L_L = .500$ (12.7) min. $W_L = **$ See below $T_L = .004 \pm .001$ (.102 ±.025)	Tray, 24 or 60 pcs	J24 or J60

SUGGESTED MOUNTING PAD DIMENSIONS

Horizontal Electrode Orientation

Vertical Electrode Orientation

Case C Vertical Mount


Cap Value	Pad Size	A Min.	B Min.	C Min.	D Min.
All Values	Normal	.200	.050	.200	.300
	High Density	.180	.030	.200	.260

Case C Horizontal Mount

Cap Value	Pad Size	A Min.	B Min.	C Min.	D Min.
All Values	Normal	.280	.050	.200	.300
	High Density	.260	.030	.200	.260

Dimensions are in inches.

PERFORMANCE DATA



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Kyocera AVX:

[800C2R2BTN3600XT](#) [800C2R7BTN3600XT](#) [800C4R3BTN3600XT](#) [800C4R7BTN3600XT](#) [800C5R1BTN3600XT](#)
[800C5R6BTN3600XT](#) [800C6R8BTN3600XT](#) [800C8R2BTN3600XT](#) [800C9R1BTN3600XT](#) [800CR37BMS3000X](#)
[800C8R2BW2500XT](#) [800C1R0BT2500XT](#)