


RF/Microwave Capacitors

RF/Microwave Multilayer Capacitors (MLC)

HQ Series, High RF Power Capacitors



PRODUCT OFFERING

Hi-Q, high RF power, surface mount MLC capacitors from AVX Corporation are characterized with ultra-low ESR and dissipation factor at high frequencies. They are designed to handle high power and high voltage levels for applications in RF power amplifiers, inductive heating, high magnetic field environments (MRI coils), medical and industrial electronics.


HOW TO ORDER

HQCC	A	A	271	J	A	T	1A
AVX Style HQCC HQCE HQLC** HQLC** HQLC**	Voltage 300V = 9 500V = 7 800V = U 1000V = A 1500V = S 2500V = W 3000V = H 3600V = J 5000V = K 7200V = M	Temperature Coefficient COG = A P90 = M	Capacitance Code (2 significant digits + no. of zeros) Examples: 4.7 pF = 4R7 10 pF = 100 100 pF = 101 1,000 pF = 102	Capacitance Tolerance B = 0.1pF (<8.2pF) C = ±0.25pF (<8.2pF) D = ±0.50pF (<8.2pF) F = ±1% (10pF) G = ±2% J = ±5% K = ±10% M = ±20%	Test Level A = Standard	Termination SMD Termination (HQCC/HQCE) T = Plated Ni and Sn (RoHS Compliant) J = 5% Min Pb 7 = Plated Ni and Au H = Cu/Sn (Non-Magnetic) Leaded Termination (HQLC/HQLE) A = Axial Ribbon M = Microstrip 4 = Axial Ribbon (Non-Magnetic) 5 = Microstrip (Non-Magnetic)	Packaging 1A = 7" Reel* 6A = Waffle Pack *HQCC & HQCE only

**Note: HQLC/HQLE are only available with leaded termination styles. All capacitance values by size/dielectric still apply.

DIMENSIONS

HQCC/HQCE



STYLE	HQCC	HQCE
(L) Length	5.84 +0.51 -0.25 (0.230 +0.020 -0.010)	9.65 +0.38 -0.25 (0.380 +0.015 -0.010)
(W) Width	6.35 ± 0.38 (0.250 ± 0.015)	9.65 ± 0.25 (0.380 ± 0.010)
(T) Thickness Max.	3.68 (0.145) max. for capacitance values ≤ 680pF 4.19 (0.165) max. for capacitance values > 680pF	4.32 (0.170) max.
(t) Overlap	1.02 (0.040) max.	1.02 (0.040) max.


mm (inches)

Not RoHS Compliant



For RoHS compliant products,
please select correct termination style.

HQLC/HQLE



STYLE	HQCC	HQCE
(L) Length	6.22 ± 0.64 (0.245 ± 0.025)	9.65 +0.89 -0.25 (0.380 +0.035 -0.010)
(W) Width	6.35 ± 0.38 (0.250 ± 0.015)	9.65 ± 0.25 (0.380 ± 0.010)
(T) Thickness Max.	3.68 (0.145) max. for capacitance values ≤ 680pF 4.19 (0.165) max. for capacitance values > 680pF	4.32 (0.170) max.
(L ₁) Lead Length	12.7 min. (0.500)	19.05 (0.750)
(W ₁) Lead Width	6.10 ± 0.127 (0.240 ± 0.005)	8.89 ± 0.25 (0.350 ± 0.010)
(T ₁) Lead Thickness	0.102 ± 0.025 (0.004 ± 0.001)	0.25 ± 0.13 (0.010 ± 0.005)
Lead Material	High Purity Silver Leads Leads are attached with High Temperature Solder	High Purity Silver Leads Leads are attached with High Temperature Solder

mm (inches)


RF/Microwave Capacitors

RF/Microwave Multilayer Capacitors (MLC)

HQ Series, High RF Power Capacitors



MOUNTING DIMENSIONS



HQCC						mm (inches)					
Mounting Orientation	Layout Type	A min.	B min.	C min.	D min.						
Horizontal	Normal	7.112 (0.280)	1.270 (0.050)	5.080 (0.200)	7.620 (0.300)						
	High Density	6.604 (0.260)	0.762 (0.030)	5.080 (0.200)	6.604 (0.260)						
Vertical (<680pF)	Normal	3.810 (0.150)	1.270 (0.050)	5.080 (0.200)	7.620 (0.300)						
	High Density	3.302 (0.130)	0.762 (0.030)	5.080 (0.200)	6.604 (0.260)						
Vertical (>680pF)	Normal	4.699 (0.185)	1.270 (0.050)	5.080 (0.200)	7.620 (0.300)						
	High Density	4.191 (0.165)	0.762 (0.030)	5.080 (0.200)	6.604 (0.260)						

HQCE						mm (inches)					
Mounting Orientation	Layout Type	A min.	B min.	C min.	D min.						
Horizontal	Normal	10.287 (0.405)	1.270 (0.050)	8.255 (0.325)	10.795 (0.425)						
	High Density	9.779 (0.385)	0.762 (0.030)	8.255 (0.325)	9.779 (0.385)						
Vertical	Normal	4.699 (0.185)	1.270 (0.050)	8.255 (0.325)	10.795 (0.425)						
	High Density	4.191 (0.165)	0.762 (0.030)	8.255 (0.325)	9.779 (0.385)						

DIELECTRIC PERFORMANCE CHARACTERISTICS

Capacitance Range	1.0pF to 2,700pF (25°C, 1.0 ±0.2 Vrms at 1kHz, for ≤ 1000 pF use 1MHz)
Capacitance Tolerances	±0.10pF, ±0.25pF, ±0.50pF, ±1%, ±2%, ±5%, ±10%, ±20%
Dissipation Factor 25°C	0.1% Max (+25°C, 1.0 ±0.2 Vrms at 1kHz, for ≤ 1000 pF use 1MHz)
Operating Temperature Range	-55°C to +125°C
Temperature Characteristic	C0G: 0 ± 30 ppm/°C (-55°C to +125°C), P90: 90 ± 30 ppm/°C (-55°C to +125°C)
Insulation Resistance	100K MΩ min. @ +25°C and 500VDC 10K MΩ min. @ +125°C and 500VDC
Dielectric Strength	250% of WVDC for capacitors rated at 500 volts DC or less for 5 seconds. 150% of WVDC for capacitors rated at 1250 volts DC or less for 5 seconds. 120% of WVDC for capacitors rated above 1250 volts DC or less for 5 seconds.

RF/Microwave Capacitors

RF/Microwave Multilayer Capacitors (MLC)

HQ Series, High RF Power Capacitors



HQCC/HQLC CAPACITANCE VALUES (A DIELECTRIC)

Cap Code	Cap (pF)	Tol.	Rated WVDC	Cap Code	Cap (pF)	Tol.	Rated WVDC	Cap Code	Cap (pF)	Tol.	Rated WVDC	Cap Code	Cap (pF)	Tol.	Rated WVDC
1R0	1.0	B, C, D	2500	8R2	8.2	B, C, D	2500	680	68	F, G, J K, M	2500	471	470	F, G, J K, M	1500
1R2	1.2			100	10	820		82	561			560	1000		
1R5	1.5			120	12	101		100	681			680			
1R8	1.8			150	15	121		120	821			820			
2R2	2.2			180	18	151		150	102			1000			
2R7	2.7			220	22	181		180	122			1200			
3R3	3.3			270	27	221		220	152			1500	500		
3R9	3.9			330	33	271		270	182			1800			
4R7	4.7			390	39	331		330	1500			222	2200		300
5R6	5.6			470	47	391		390				272	2700		
6R8	6.8			560	56										

HQCC/HQLC CAPACITANCE VALUES (M DIELECTRIC)

Cap Code	Cap (pF)	Tol.	Rated WVDC		Cap Code	Cap (pF)	Tol.	Rated WVDC		Cap Code	Cap (pF)	Tol.	Rated WVDC		
			Standard	Extended				Standard	Extended				Standard	Extended	
1R0	1.0	B, C, D	2500	3600	100	10	F, G, J K, M	2500	3600	161	160	F, G, J K, M	2500	3000	
1R1	1.1				110	11				181	180				
1R2	1.2				120	12				201	200				
1R3	1.3				130	13				221	220				
1R4	1.4				150	15				241	240				
1R5	1.5				160	16				271	270				
1R6	1.6				180	18				301	300		1500	2000	
1R7	1.7				200	20				331	330				
1R8	1.8				220	22				331	330				
1R9	1.9				240	24				361	360				
2R0	2.0				270	27				391	390	1000			1500
2R1	2.1				300	30				431	430				
2R2	2.2				330	33				471	470				
2R4	2.4				360	36				511	510				
2R5	2.5				390	39				561	560				
3R0	3.0				430	43				621	620				
3R3	3.3				470	47				681	680				
3R6	3.6				510	51				751	750				
3R9	3.9				560	56				821	820				
4R3	4.3				620	62				911	910		500	800	
4R7	4.7	680	68	102	1000										
5R1	5.1	750	75	112	1100										
5R6	5.6	820	82	122	1200										
6R2	6.2	F, G, J K, M	2500	3600	910	91	3000	152	1500	300	500				
6R8	6.8				101	100		182	1800						
7R5	7.5				111	110		222	2200						
8R2	8.2				121	120		242	2400						
9R1	9.1				131	130		272	2700						
					151	150									

HQCE/HQLE CAPACITANCE VALUES (A DIELECTRIC)

Cap Code	Cap (pF)	Tol.	Rated WVDC		Cap Code	Cap (pF)	Tol.	Rated WVDC		Cap Code	Cap (pF)	Tol.	Rated WVDC	
			Standard	Extended				Standard	Extended				Standard	Extended
1R0	1.0	C, D	3600	7200	150	15	G, J, K, M	3600	7200	221	220	G, J, K, M	3600	NA
1R2	1.2				180	18				271	270			
1R5	1.5				220	22				331	330			
1R8	1.8				270	27				391	390			
2R2	2.2				330	33				471	470		2500	
2R7	2.7				390	39				561	560			
3R3	3.3				470	47				681	680		1000	
3R9	3.9				560	56				821	820			
4R7	4.7				680	68				102	1000			
5R6	5.6				820	82				122	1200			
6R8	6.8	101	100	152	1500	1800								
8R2	8.2	121	120	182	1800									
100	10	G, J, K, M			151	150			5000	222	2200			
120	12				181	180								

HQCE/HQLE CAPACITANCE VALUES (M DIELECTRIC)

Cap Code	Cap (pF)	Tol.	Rated WVDC		Cap Code	Cap (pF)	Tol.	Rated WVDC		Cap Code	Cap (pF)	Tol.	Rated WVDC	
			Standard	Extended				Standard	Extended				Standard	Extended
1R0	1.0	B, C, D	3600	7200	180	18	F, G, J, K, M	3600	7200	331	330	F, G, J, K, M	3600	NA
1R2	1.2				220	22				391	390			
1R5	1.5				270	27				471	470		2500	
1R8	1.8				330	33				561	560			
2R2	2.2				390	39				681	680		1000	
2R7	2.7				470	47				821	820			
3R3	3.3				560	56				102	1000			
3R9	3.9				680	68				122	1200			
4R7	4.7				820	82				152	1500			
5R6	5.6				101	100				182	1800			
6R8	6.8	F, G, J, K, M	3600	5000	222	2200	G, J K, M	500						
8R2	8.2				121	120			272	2700				
100	10				151	150			332	3300				
120	12				181	180			472	4700				
150	15	221	220	512	5100									
		271	270											





RF/Microwave Capacitors

RF/Microwave Multilayer Capacitors (MLC)



HQ Series, High RF Power Capacitors



HQCC PERFORMANCE CHARACTERISTICS (A DIELECTRIC)





HQCC PERFORMANCE CHARACTERISTICS (M DIELECTRIC)







RF/Microwave Capacitors

RF/Microwave Multilayer Capacitors (MLC)

HQ Series, High RF Power Capacitors







HQCE PERFORMANCE CHARACTERISTICS (A DIELECTRIC)





RF/Microwave Capacitors

RF/Microwave Multilayer Capacitors (MLC)

HQ Series, High RF Power Capacitors








HQCE PERFORMANCE CHARACTERISTICS (M DIELECTRIC)



RF/Microwave Capacitors

RF/Microwave Multilayer Capacitors (MLC)

HQ Series, High RF Power Capacitors



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Kyocera AVX:

[HQCEMA180JAT6A](#) [HQCEMA101JAT6A](#) [HQCC7M152GAH6A](#) [HQCC7M182GAH6A](#) [HQCC9M222GAH6A](#)
[HQCC9M272GAH6A](#) [HQCCAM102GAH6A](#) [HQCCAM122GAH6A](#) [HQCCAM561GAH6A](#) [HQCCAM681GAH6A](#)
[HQCCAM821GAH6A](#) [HQCCSM361GAH6A](#) [HQCCSM471GAH6A](#) [HQCCWM100GAH6A](#) [HQCCWM101GAH6A](#)
[HQCCWM120GAH6A](#) [HQCCWM121GAH6A](#) [HQCCWM150GAH6A](#) [HQCCWM151GAH6A](#) [HQCCWM180GAH6A](#)
[HQCCWM181GAH6A](#) [HQCCWM200GAH6A](#) [HQCCWM221GAH6A](#) [HQCCWM240GAH6A](#) [HQCCWM271GAH6A](#)
[HQCCWM2R0BAH6A](#) [HQCCWM2R4BAH6A](#) [HQCCWM300GAH6A](#) [HQCCWM330GAH6A](#) [HQCCWM3R3BAH6A](#)
[HQCCWM3R9BAH6A](#) [HQCCWM430GAH6A](#) [HQCCWM470GAH6A](#) [HQCCWM4R7BAH6A](#) [HQCCWM510GAH6A](#)
[HQCCWM560GAH6A](#) [HQCCWM5R6BAH6A](#) [HQCCWM680GAH6A](#) [HQCCWM750GAH6A](#) [HQCCWM7R5BAH6A](#)
[HQCCWM8R2BAH6A](#) [HQCCWM910GAH6A](#) [HQCC7M182FAH1A](#) [HQCC9M242FAH6A](#) [HQCC9M272KAH1A](#)
[HQCCAM102FAH1A](#) [HQCCAM102FAH6A](#) [HQCCAM102GAH1A](#) [HQCCAM102KAH6A](#) [HQCCAM112FAH1A](#)
[HQCCAM112JAH1A](#) [HQCCAM112MAH1A](#) [HQCCAM112MAH6A](#) [HQCCAM122FAH1A](#) [HQCCSA331KAH6A](#)
[HQCCSM301FAH6A](#) [HQCCSM301GAH6A](#) [HQCCSM301JAH6A](#) [HQCCSM301KAH6A](#) [HQCCSM471KAH1A](#)
[HQCCWA151FAH1A](#) [HQCCWA151FAH6A](#) [HQCCWA151KAH6A](#) [HQCCWA220GAH6A](#) [HQCCWM110FAH1A](#)
[HQCCWM110FAH6A](#) [HQCCWM110MAH6A](#) [HQCCWM120GAH1A](#) [HQCCWM120KAH6A](#) [HQCCWM120MAH6A](#)
[HQCCWM130FAH6A](#) [HQCCWM131JAH6A](#) [HQCCWM151FAH1A](#) [HQCCWM151MAH6A](#) [HQCCWM161FAH1A](#)
[HQCCWM161KAH6A](#) [HQCCWM200MAH6A](#) [HQCCWM241GAH6A](#) [HQCCWM270KAH1A](#) [HQCCWM270KAH6A](#)
[HQCCWM2R2DAH6A](#) [HQCCWM2R5BAH1A](#) [HQCCWM360GAH6A](#) [HQCCWM390JAH6A](#) [HQCCWM470MAH1A](#)
[HQCCWM560MAH6A](#) [HQCCWM620GAH6A](#) [HQCCWM620KAH6A](#) [HQCCWM6R2CAH1A](#) [HQCCWM750MAH6A](#)
[HQCCWM8R2CAH1A](#) [HQCE7M272GAH6A](#) [HQCE7M332GAH6A](#) [HQCE7M332MAH1A](#) [HQCE7M472GAH6A](#)
[HQCE7M512GAH6A](#) [HQCEAA102GAH1A](#) [HQCEAA102MAH6A](#) [HQCEAA152GAH1A](#) [HQCEAA152JAH6A](#)