


Automotive low drop power Schottky rectifier

Datasheet - production data



Features

- AEC-Q101 qualified
- Very small conduction losses
- Negligible switching losses
- Low forward voltage drop
- Surface mount miniature packages
- Avalanche capability specified
- PPAP capable



Description

Single chip Schottky rectifiers suited to switched mode power supplies and high frequency DC to DC converters.

Packaged in SOD123Flat, this device is especially intended for surface mounting and used in low voltage, high frequency inverters, free-wheeling and polarity protection in automotive applications.

Table 1: Device summary

Symbol	Value
$I_{F(AV)}$	2 A
V_{RRM}	40 V
V_F (typ.)	0.50 V
T_j (max.)	175 °C

1 Characteristics

Table 2: Absolute ratings (limiting values at 25 °C, unless otherwise specified)

Symbol	Parameter		Value	Unit
V_{RRM}	Repetitive peak reverse voltage	$T_j = -40 \text{ }^\circ\text{C to } +175 \text{ }^\circ\text{C}$	40	V
$I_{F(AV)}$	Average forward current $\delta = 0.5$, square wave	$T_L = 145 \text{ }^\circ\text{C}$	2	A
I_{FSM}	Surge non repetitive forward current	$t_p = 10 \text{ ms sinusoidal}$	50	A
P_{ARM}	Repetitive peak avalanche power	$t_p = 10 \mu\text{s}, T_j = 125 \text{ }^\circ\text{C}$	65	W
T_{stg}	Storage temperature range		-65 to +175	$^\circ\text{C}$
T_j	Operating junction temperature range ⁽¹⁾		-40 to +175	

Notes:

(1) $(dP_{tot}/dT_j) < (1/R_{th(j-a)})$ condition to avoid thermal runaway for a diode on its own heatsink.

Table 3: Thermal parameters

Symbol	Parameter	Max. value	Unit
$R_{th(j-l)}$	Junction to lead	20	°C/W

Table 4: Static electrical characteristics

Symbol	Parameter	Test conditions		Min.	Typ.	Max.	Unit
$I_R^{(1)}$	Reverse leakage current	$T_j = 25 \text{ }^\circ\text{C}$	$V_R = V_{RRM}$	-		35	µA
		$T_j = 125 \text{ }^\circ\text{C}$		-	6	10	mA
$V_F^{(2)}$	Forward voltage drop	$T_j = 25 \text{ }^\circ\text{C}$	$I_F = 2 \text{ A}$	-		0.63	V
		$T_j = 125 \text{ }^\circ\text{C}$		-	0.50	0.61	

Notes:

(1) Pulse test: $t_p = 5 \text{ ms}, \delta < 2\%$

(2) Pulse test: $t_p = 380 \mu\text{s}, \delta < 2\%$

To evaluate the conduction losses, use the following equation:

$$P = 0.46 \times I_{F(AV)} + 0.075 \times I_F^2(\text{RMS})$$

For more information, please refer to the following application notes related to the power losses.

- AN604 (Calculation of conduction losses in a power rectifier)
- AN4021 (Calculation of reverse losses in a power diode)

1.1 Characteristics (curves)

Figure 1: Average forward power dissipation versus average forward current




Figure 2: Average forward current versus ambient temperature ($\delta = 0.5$)




Figure 3: Normalized avalanche power derating versus pulse duration ($T_j = 125^\circ\text{C}$)




Figure 4: Relative variation of thermal impedance junction to lead versus pulse duration




Figure 5: Reverse leakage current versus reverse voltage applied (typical values)





Figure 6: Junction capacitance versus reverse voltage applied (typical values)



Characteristics

STPS2L40ZFY

Figure 7: Forward voltage drop versus forward current (typical values)





Figure 8: Thermal resistance junction to ambient versus copper surface under each lead (typical values)



2 Package information

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK® packages, depending on their level of environmental compliance. ECOPACK® specifications, grade definitions and product status are available at: www.st.com. ECOPACK® is an ST trademark.

- Epoxy meets UL94, V0
- Cooling method: by conduction (C)

2.1 SOD123Flat package information

Figure 9: SOD123Flat package outline





Table 5: SOD123Flat package mechanical data

Ref.	Dimensions		
	Millimeters		
	Min.	Typ.	Max.
A	0.86	0.98	1.10
b	0.80	0.90	1.00
c	0.08	0.15	0.25
c1	0.00		0.10
D	2.50	2.60	2.70
E	1.50	1.60	1.80
HD	3.30	3.50	3.70
L	0.45	0.65	0.85

Figure 10: SOD123Flat footprint dimensions (mm)



3 Ordering information

Table 6: Ordering information

Order code	Marking	Package	Weight	Base qty.	Delivery mode
STPS2L40ZFY	2Y4	SOD123Flat	12.5 mg	3000	Tape and reel

4 Revision history

Table 7: Document revision history

Date	Revision	Changes
13-Oct-2016	1	Initial release.

IMPORTANT NOTICE – PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2016 STMicroelectronics – All rights reserved

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[STMicroelectronics:](#)

[STPS2L40ZFY](#)