


# F98 Series

## Resin-Molded Chip, High CV Undertab



### FEATURES

- Compliant to the RoHS3 directive 2015/863/EU
- SMD Face Down Design
- Small and Low Profile
- 100% Surge Current Tested

### APPLICATIONS

- Smartphone
- Mobile Phone
- Wireless Module
- Hearing Aid




### CASE DIMENSIONS:

millimeters (inches)

Code	EIA Code	EIA Metric	L	W <sub>1</sub>	W <sub>2</sub>	H	S <sub>1</sub>	S <sub>2</sub>
M	0603	1608-09	1.60 <sup>+0.20</sup> <sub>-0.10</sub> (0.063 <sup>+0.008</sup> <sub>-0.004</sub> )	0.85 <sup>+0.20</sup> <sub>-0.10</sub> (0.033 <sup>+0.008</sup> <sub>-0.004</sub> )	0.65±0.10 (0.026±0.004)	0.80±0.10*3 (0.031±0.004)	0.50±0.10 (0.020±0.004)	0.60±0.10 (0.024±0.004)
S	0805	2012-09	2.00 <sup>+0.20</sup> <sub>-0.10</sub> (0.079 <sup>+0.008</sup> <sub>-0.004</sub> )	1.25 <sup>+0.20</sup> <sub>-0.10</sub> (0.049 <sup>+0.008</sup> <sub>-0.004</sub> )	0.90±0.10 (0.035±0.004)	0.80±0.10 (0.031±0.004)	0.50±0.10 (0.020±0.004)	1.00±0.10 (0.039±0.004)
U	0402	1106-06	1.10±0.05 (0.043±0.002)	0.60±0.05 (0.024±0.002)	0.35±0.05 (0.014±0.002)	0.55±0.05 (0.022±0.002)	0.30±0.05 (0.012±0.002)	0.50±0.05 (0.020±0.002)

\*3 F980J107MMAAXE: 1.0mm Max.




### MARKING


#### U CASE



#### M CASE



#### S CASE



### HOW TO ORDER

**F98**

Type

**0J**

Rated Voltage

**106**

Capacitance Code

pF code: 1st two digits represent significant figures, 3rd digit represents multiplier (number of zeros to follow)

**M**

Tolerance  
M = ±20%

**M**

Case Size  
See table above

**□**

Packaging  
See Tape & Reel Packaging Section

**□□□**

Specification Suffix  
LZT = Rated temperature 60°C  
AXE = Rated temperature 60°C and H dimension 1.0mm Max

### TECHNICAL SPECIFICATIONS

Category Temperature Range:	-55 to +125°C
Rated Temperature:	+85°C or +60°C
Capacitance Tolerance:	±20% at 120Hz
Dissipation Factor:	Refer to next page
ESR 100kHz:	Refer to next page
Leakage Current:	Provided that: After 5 minute's application of rated voltage, leakage current at 85°C or +60°C 10 times or less than 20°C specified value. After 5 minute's application of rated voltage, leakage current at 125°C 12.5 times or less than 20°C specified value.
Termination Finish:	M, S case: Gold Plating (standard), U case: Sn-3.5Ag Plating (standard)

# F98 Series

## Resin-Molded Chip, High CV Undertab



### CAPACITANCE AND RATED VOLTAGE RANGE (LETTER DENOTES CASE SIZE)

Capacitance		Rated Voltage								*Cap Code
μF	Code	2.5 (0e)	4V (0G)	6.3V (0J)	10V (1A)	16V (1C)	20V (1D)	25V (1E)	35V (1V)	
0.47	474					U				N
1.0	105					M	M	M	S	A
2.2	225				M/U	M				J
4.7	475		U	M/U	M/U**	M				S
10	106		U	M/U**	M	S				a
15	156		U							e
22	226		M/U**	M	M**/S					J
33	336		M	M	M**/S					n
47	476	M	M	M/S	S					s
68	686		M/S							w
100	107		M/S	M*4/S						A
220	227		S							J

Released ratings

\*4 (AXE) Rated temperature 60°C and H dimension 1.0mm Max. Please contact AVX when you need detail spec.

\*\* (LZT) Rated temperature 60°C. Please contact AVX when you need detail spec.

Please contact to your local AVX sales office when these series are being designed in your application.

### RATINGS & PART NUMBER REFERENCE

AVX Part No.	Case Size	Capacitance (μF)	Rated Voltage (V)	DCL (μA)	DF @ 120Hz (%)	ESR @ 100kHz (Ω)	100kHz RMS Current (mA)				*1 ΔC/C (%)	MSL
							25°C	60°C	85°C	125°C		
2.5 Volt												
F980E476MMA	M	47	2.5	1.2	30	4	79	—	71	32	±30	3
4 Volt												
F980G475MUA	U	4.7	4	0.5	20	20	27	—	25	11	±30	3
F980G106MUA	U	10	4	0.8	25	20	27	—	25	11	±30	3
F980G156MUA	U	15	4	9.0	40	25	24	—	22	10	±30	3
F980G226MMA	M	22	4	0.9	15	7.5	58	—	52	23	±30	3
F980G226MUALZT	U	22	4	25.0	40	20	27	25	—	11	±30	3
F980G336MMA	M	33	4	1.3	30	4	79	—	71	32	±30	3
F980G476MMA	M	47	4	1.9	40	8	56	—	50	22	±30	3
F980G686MMA	M	68	4	27.2	50	10	50	—	45	20	±30	3
F980G686MSA	S	68	4	2.7	30	4	106	—	95	42	±30	3
F980G107MMA	M	100	4	80.0	60	10	50	—	45	20	±30	3
F980G107MSA	S	100	4	4.0	35	4	106	—	95	42	±30	3
F980G227MSA	S	220	4	132	80	5	95	—	85	38	±30	3
6.3 Volt												
F980J475MMA	M	4.7	6.3	0.5	20	7.5	58	—	52	23	±30	3
F980J475MUA	U	4.7	6.3	0.6	20	20	27	—	25	11	±30	3
F980J106MMA	M	10	6.3	0.6	8	6	65	—	58	26	±30	3
F980J106MUALZT	U	10	6.3	6.3	30	30	22	20	—	9	±30	3
F980J226MMA	M	22	6.3	1.4	20	6	65	—	58	26	±30	3
F980J336MMA	M	33	6.3	4.2	35	8	56	—	50	22	±30	3
F980J476MMA	M	47	6.3	29.6	45	10	50	—	45	20	±30	3
F980J476MSA	S	47	6.3	3.0	25	6	87	—	78	35	±30	3
F980J107MMAAXE	M	100	6.3	126	80	10	50	45	—	20	±30	3
F980J107MSA	S	100	6.3	63.0	50	8	75	—	68	30	±30	3
10 Volt												
F981A225MMA	M	2.2	10	0.5	6	7.5	58	—	52	23	±30	3
F981A225MUA	U	2.2	10	0.5	15	15	32	—	28	13	±30	3
F981A475MMA	M	4.7	10	0.5	6	6	65	—	58	26	±30	3
F981A475MUALZT	U	4.7	10	4.7	25	25	24	22	—	10	±30	3
F981A106MMA	M	10	10	1.0	20	7.5	58	—	52	23	±30	3
F981A226MMALZT	M	22	10	11.0	30	8	56	50	—	22	±30	3
F981A226MSA	S	22	10	2.2	20	4	106	—	95	42	±30	3
F981A336MMALZT	M	33	10	33.0	45	8	56	50	—	22	±30	3
F981A336MSA	S	33	10	3.3	30	6	87	—	78	35	±30	3
F981A476MSA	S	47	10	9.4	35	5	95	—	85	38	±30	3
16 Volt												
F981C474MUA	U	0.47	16	0.5	6	25	24	—	22	10	±20	3
F981C105MMA	M	1	16	0.5	6	10	50	—	45	20	±30	3
F981C225MMA	M	2.2	16	0.5	6	10	50	—	45	20	±30	3
F981C475MMA	M	4.7	16	0.8	12	12	46	—	41	18	±30	3
F981C106MSA	S	10	16	1.6	18	4	106	—	95	42	±30	3
20 Volt												
F981D105MMA	M	1	20	0.5	6	10	50	—	45	20	±30	3
25 Volt												
F981E105MMA	M	1	25	0.5	8	10	50	—	45	20	±30	3
35 Volt												
F981V105MSA	S	1	35	0.7	20	8	75	—	68	30	±30	3

\*2: Leakage Current

After 5 minute's application of rated voltage, leakage current at 20°C.

Moisture Sensitivity Level (MSL) is defined according to J-STD-020.





The Important Information/Disclaimer is incorporated in the catalog where these specifications came from or available online at [www.avx.com/disclaimer/](http://www.avx.com/disclaimer/) by reference and should be reviewed in full before placing any order.

# F98 Series

## Resin-Molded Chip, High CV Undertab


### QUALIFICATION TABLE

TEST	F98 series (Temperature range -55°C to +125°C)	
	Condition	
<b>Damp Heat (Steady State)</b>	At 40°C, 90 to 95% R.H., 500 hours (No voltage applied) Capacitance Change ..... Refer to the table above (*1) Dissipation Factor ..... 150% or less of initial specified value Leakage Current ..... 200% or less of initial specified value	
<b>Temperature Cycles</b>	-55°C / +125°C, 30 minutes each, 5 cycles Capacitance Change ..... Refer to the table above (*1) Dissipation Factor ..... 150% or less of initial specified value Leakage Current ..... 200% or less of initial specified value	
<b>Resistance to Soldering Heat</b>	10 seconds reflow at 260°C, 5 seconds immersion at 260°C. Capacitance Change ..... Refer to the table above (*1) Dissipation Factor ..... Initial specified value or less Leakage Current ..... Initial specified value or less	
<b>Surge</b>	After application of surge in series with a 1kΩ resistor at the rate of 30 seconds ON, 30 seconds OFF, for 1000 successive test cycles at 85°C, capacitors shall meet the characteristic requirements in the table above. (Not applied to LZT and AXE.) Capacitance Change ..... Refer to the table above (*1) Dissipation Factor ..... 150% or less of initial specified value Leakage Current ..... 200% or less of initial specified value	
<b>Endurance</b>	After 1000 hours' application of rated voltage in series with a 3Ω resistor at 85°C or +60°C, capacitors shall meet the characteristic requirements in the table above. Capacitance Change ..... Refer to the table above (*1) Dissipation Factor ..... 150% or less of initial specified value Leakage Current ..... 200% or less of initial specified value	
<b>Shear Test</b>	After applying the pressure load of 5N for 10±1 seconds horizontally to the center of capacitor side body which has no electrode and has been soldered beforehand on a substrate, there shall be found neither exfoliation nor its sign at the terminal electrode.	
<b>Terminal Strength</b>	Keeping a capacitor surface-mounted on a substrate upside down and supporting the substrate at both of the opposite bottom points 45mm apart from the center of capacitor, the pressure strength is applied with a specified jig at the center of substrate so that the substrate may bend by 1mm as illustrated. Then, there shall be found no remarkable abnormality on the capacitor terminals.	


F98 Series  
Resin-Molded Chip, High CV Undertab




AVX SOLID ELECTROLYTIC CAPACITOR ROADMAP



FIVE CAPACITOR CONSTRUCTION STYLES



SERIES LINE UP : CONVENTIONAL SMD MnO<sub>2</sub>



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kyocera AVX:](#)

[F981A476MSAAS1](#)