


Y5V Dielectric

General Specifications



GENERAL DESCRIPTION

Y5V formulations are for general-purpose use in a limited temperature range. They have a wide temperature characteristic of +22% –82% capacitance change over the operating temperature range of –30°C to +85°C. These characteristics make Y5V ideal for decoupling applications within limited temperature range.



PART NUMBER (SEE PAGE 4 FOR COMPLETE PART NUMBER EXPLANATION)

0805

Size
(L" x W")

3

Voltage
6.3V = 6
10V = Z
16V = Y
25V = 3
50V = 5

G

Dielectric
Y5V = G

104

Capacitance Code (In pF)
2 Sig. Digits + Number of Zeros

Z

Capacitance Tolerance
Z = +80 –20%

A

Failure Rate
A = Not Applicable

T

Terminations
T = Plated Ni and Sn


2

Packaging
2 = 7" Reel
4 = 13" Reel


A

Special Code
A = Std. Product


Temperature Coefficient




Capacitance Change vs. DC Bias Voltage




Insulation Resistance vs. Temperature




0.1 μF - 0603 Impedance vs. Frequency



0.22 μF - 0805 Impedance vs. Frequency




1 μF - 1206 Impedance vs. Frequency



Y5V Dielectric


Specifications and Test Methods

Parameter/Test		Y5V Specification Limits	Measuring Conditions	
Operating Temperature Range		-30°C to +85°C	Temperature Cycle Chamber	
Capacitance		Within specified tolerance	Freq.: 1.0 kHz \pm 10% Voltage: 1.0Vrms \pm .2V For Cap > 10 μ F, 0.5Vrms @ 120Hz	
Dissipation Factor		\leq 5.0% for \geq 50V DC rating \leq 7.0% for 25V DC rating \leq 9.0% for 16V DC rating \leq 12.5% for \leq 10V DC rating		
Insulation Resistance		10,000M Ω or 500M Ω - μ F, whichever is less		
Dielectric Strength		No breakdown or visual defects	Charge device with 250% of rated voltage for 1-5 seconds, w/charge and discharge current limited to 50 mA (max)	
Resistance to Flexure Stresses	Appearance	No defects	Deflection: 2mm Test Time: 30 seconds 1mm/sec 	
	Capacitance Variation	\leq \pm 30%		
	Dissipation Factor	Meets Initial Values (As Above)		
	Insulation Resistance	\geq Initial Value x 0.1		
Solderability		\geq 95% of each terminal should be covered with fresh solder	Dip device in eutectic solder at 230 \pm 5°C for 5.0 \pm 0.5 seconds	
Resistance to Solder Heat	Appearance	No defects, <25% leaching of either end terminal	Dip device in eutectic solder at 260°C for 60 seconds. Store at room temperature for 24 \pm 2 hours before measuring electrical properties.	
	Capacitance Variation	\leq \pm 20%		
	Dissipation Factor	Meets Initial Values (As Above)		
	Insulation Resistance	Meets Initial Values (As Above)		
	Dielectric Strength	Meets Initial Values (As Above)		
Thermal Shock	Appearance	No visual defects	Step 1: -30°C \pm 2°	30 \pm 3 minutes
	Capacitance Variation	\leq \pm 20%	Step 2: Room Temp	\leq 3 minutes
	Dissipation Factor	Meets Initial Values (As Above)	Step 3: +85°C \pm 2°	30 \pm 3 minutes
	Insulation Resistance	Meets Initial Values (As Above)	Step 4: Room Temp	\leq 3 minutes
	Dielectric Strength	Meets Initial Values (As Above)	Repeat for 5 cycles and measure after 24 \pm 2 hours at room temperature	
Load Life	Appearance	No visual defects	Charge device with twice rated voltage in test chamber set at 85°C \pm 2°C for 1000 hours (+48, -0) Remove from test chamber and stabilize at room temperature for 24 \pm 2 hours before measuring.	
	Capacitance Variation	\leq \pm 30%		
	Dissipation Factor	\leq Initial Value x 1.5 (See Above)		
	Insulation Resistance	\geq Initial Value x 0.1 (See Above)		
	Dielectric Strength	Meets Initial Values (As Above)		
Load Humidity	Appearance	No visual defects	Store in a test chamber set at 85°C \pm 2°C/ 85% \pm 5% relative humidity for 1000 hours (+48, -0) with rated voltage applied. Remove from chamber and stabilize at room temperature and humidity for 24 \pm 2 hours before measuring.	
	Capacitance Variation	\leq \pm 30%		
	Dissipation Factor	\leq Initial Value x 1.5 (See above)		
	Insulation Resistance	\geq Initial Value x 0.1 (See Above)		
	Dielectric Strength	Meets Initial Values (As Above)		

Y5V Dielectric Capacitance Range

PREFERRED SIZES ARE SHADED

SIZE	0201				0402				0603				0805				1206				1210			
Soldering	Reflow Only				Reflow/Wave				Reflow/Wave				Reflow/Wave				Reflow/Wave				Reflow/Wave			
Packaging	All Paper				All Paper				All Paper				Paper/Embossed				Paper/Embossed				Paper/Embossed			
(L) Length	mm		(0.60 ± 0.09)		mm		(1.00 ± 0.10)		mm		(1.60 ± 0.15)		mm		(2.01 ± 0.20)		mm		(3.20 ± 0.20)		mm		(3.20 ± 0.20)	
(L) Length	(in.)		(0.024 ± 0.004)		(in.)		(0.040 ± 0.004)		(in.)		(0.063 ± 0.006)		(in.)		(0.079 ± 0.008)		(in.)		(0.126 ± 0.008)		(in.)		(0.126 ± 0.008)	
(W) Width	mm		(0.30 ± 0.09)		mm		(0.50 ± 0.10)		mm		(.81 ± 0.15)		mm		(1.25 ± 0.20)		mm		(1.60 ± 0.20)		mm		(2.50 ± 0.20)	
(W) Width	(in.)		(0.011 ± 0.004)		(in.)		(0.020 ± 0.004)		(in.)		(0.032 ± 0.006)		(in.)		(0.049 ± 0.008)		(in.)		(0.063 ± 0.008)		(in.)		(0.098 ± 0.008)	
(t) Terminal	mm		(0.15 ± 0.05)		mm		(0.25 ± 0.15)		mm		(0.35 ± 0.15)		mm		(0.50 ± 0.25)		mm		(0.50 ± 0.25)		mm		(0.50 ± 0.25)	
(t) Terminal	(in.)		(0.006 ± 0.002)		(in.)		(0.010 ± 0.006)		(in.)		(0.014 ± 0.006)		(in.)		(0.020 ± 0.010)		(in.)		(0.020 ± 0.010)		(in.)		(0.020 ± 0.010)	
WVDC	6.3	10	6	10	16	25	50	10	16	25	50	10	16	25	50	10	16	25	50	10	16	25	50	
Cap (pF)	820		A																					
Cap (pF)	1000		A																					
Cap (pF)	2200		A																					
Cap (pF)	4700		A																					
Cap (µF)	0.010	A	A																					
Cap (µF)	0.022	A																						
Cap (µF)	0.047	A																						
Cap (µF)	0.10				C	C					G	G												
Cap (µF)	0.22										G													
Cap (µF)	0.33										G													
Cap (µF)	0.47					C					G	G												
Cap (µF)	1.0				C	C					G	G	J			N	N	N			M	M	M	N
Cap (µF)	2.2					C					J					N	N	N						
Cap (µF)	4.7															N	N	N						
Cap (µF)	10.0															N	N	P						
Cap (µF)	22.0																							
Cap (µF)	47.0																							
WVDC	6.3	10	6	10	16	25	50	10	16	25	50	10	16	25	50	10	16	25	50	10	16	25	50	
SIZE	0201				0402				0603				0805				1206				1210			



Letter	A	C	E	G	J	K	M	N	P	Q	X	Y	Z
Max.	0.33	0.56	0.71	0.90	0.94	1.02	1.27	1.40	1.52	1.78	2.29	2.54	2.79
Thickness	(0.013)	(0.022)	(0.028)	(0.035)	(0.037)	(0.040)	(0.050)	(0.055)	(0.060)	(0.070)	(0.090)	(0.100)	(0.110)
	PAPER					EMBOSSED							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[KYOCERA AVX:](#)

[08055G124ZAT2A](#) [08055G154ZAT2A](#) [08055G824ZAT2A](#) [0805YG684ZAT2A](#) [0805YG103ZAT2A](#)
[0805YG104ZAT4A](#) [0805ZG104ZAT4A](#) [0805ZG335ZAT2A](#) [12065G684ZAT2A](#) [12063G104ZAT2A](#) [12065G184ZAT2A](#)
[1206YG104ZAT2A](#) [1206YG105ZAT2A-2K](#) [12105G155ZAT2A](#) [12105G224ZAT4A](#) [1206YG335ZAT2A](#)
[12103G684ZAT2A](#) [12105G684ZAT2A](#) [1210YG105ZAT2A](#) [1210ZG226ZAT2](#) [02016G333ZAT2A](#) [04023G103ZAT2A](#)
[04023G223ZAT2A](#) [04023G333ZAT2A](#) [04025G103ZAT2A](#) [04025G472ZAT2A](#) [0402YG333ZAT2A](#) [0402YG683ZAT2A](#)
[0402ZG473ZAT2A](#) [06033G154ZAT2A](#) [06033G224ZAT4A](#) [06033G473ZAT4A](#) [06033G563ZAT2A](#)
[06033G683ZAT2A](#) [06035G222ZAT2A](#) [06035G333ZAT2A](#) [06035G472ZAT2A](#) [06035G563ZAT2A](#) [0603YG154ZAT2A](#)
[0603YG473ZAT4A](#) [0603ZG154ZAT2A](#) [0603ZG334ZAT2A](#) [0603ZG473ZAT2A](#) [0603ZG684ZAT2A](#)
[08053G103ZAT2A](#) [08053G104ZAT2S](#) [08053G184ZAT2A](#) [08053G684ZAT2A](#) [02016G153ZAT2A](#) [02016G183ZAT2A](#)
[06035G683ZAT2A](#) [08056G106ZAT2A](#) [06036G105ZAT2A](#) [0805YG225ZAT7A](#) [0805ZG105ZAT4A](#)
[08056G225ZAT2A](#) [1206ZG475ZAT4A](#) [1210ZG106ZAT4A](#) [12106G107ZAT2A](#) [0402YG104ZAT7A](#) [0603YG684ZAT2A](#)
[06033G104ZAT2AM](#) [06033G104ZAT4AM](#) [0805YG105ZA72A](#) [1206ZG225ZAT4A](#) [1206ZG335ZAT2A](#)
[12066G106ZAT2A](#) [0805ZG335ZAT4A](#) [1206YG155ZAT2A](#) [1206YG335ZAT4A](#) [1206ZG685ZAT2A](#) [12103G335ZAT2A](#)
[1210ZG226ZAT4A](#) [0603YG104ZAT7A](#) [12066G226ZAT2A](#) [06036G474ZAT2A](#) [08055G102ZAT2A](#)
[0603ZG104ZAT7A](#) [12066G106ZAT4A](#) [08053G334ZAT4A](#) [12063G105ZAJ2A](#) [04025G223ZAT2A](#) [06033G104ZAT7A](#)
[06033G683ZAT4A](#) [06035G153ZAT2A](#) [0603YG562ZAT2A](#) [0603YG682ZAT2A](#) [08053G333ZAT2A](#) [08053G823ZAT2A](#)
[12063G684ZAT2A](#) [1206YG684ZAT2A](#) [1206YG475MAT2A](#) [06036G225ZAT2A](#) [1210YG685ZAT1A](#)
[1210YG685ZAT2A](#) [12106G107ZAT4A](#) [1210YG332ZAT2A](#) [08053G225ZAT2A](#) [02014G104ZAT2A](#) [0805YG155ZAT2A](#)