


TWA Series – DSCC 93026



TWA Wet Electrolytic Tantalum Capacitor




The TWA series is an axial leaded wet electrolytic tantalum capacitor and represents a new level of high CV (capacitance/voltage) previously unavailable in this technology. TWA incorporates a novel, very high capacitance cathode system that allows for higher CV designs, well beyond values specified in the Mil-PRF-39006 drawing.

TWA products are listed in DSCC 93026, which includes new high capacitance/voltage ratings. This design includes a welded tantalum can and header assembly that provides a hermetic seal to withstand harsh shock and vibration requirements of 39006. Wet tantalums do not require the same derating as solid tantalums. AVX recommends derating components by only 20% in order to enhance reliability.

Customized capacitance and voltage packages are possible and welcomed. Contact the factory about design possibilities beyond those contained in this datasheet.

OUTLINE DIMENSIONS



CASE DIMENSIONS: millimeters (inches)

DSCC Case Size	AVX Case Size	L +0.79 (0.031) -0.41 (0.016)	D Without Insulating Sleeve ±0.41 (0.016)	D With Insulating Sleeve Max	E ±6.35 (0.250)
T1	A	11.51 (0.453)	4.78 (0.188)	5.56 (0.219)	38.10 (1.500)
T2	B	16.28 (0.641)	7.14 (0.281)	7.92 (0.312)	57.15 (2.250)
T3	D	19.46 (0.766)	9.52 (0.375)	10.31 (0.406)	57.15 (2.250)
T4	E	26.97 (1.062)	9.52 (0.375)	10.31 (0.406)	57.15 (2.250)

VOLTAGE RATINGS (Operating Temperature -55°C to 125°C)

Voltage (DC)								
Rated Voltage: (Ur)	85°C	25	30	50	60	75	100	125
Derated Voltage: (Uc)	125°C	15	20	30	40	50	65	85
Surge Voltage: (Us)	85°C	28.8	34.5	57.5	69	86.3	115	144

TWA Series – DSCC 93026



TWA Wet Electrolytic Tantalum Capacitor

HOW TO ORDER

AVX PART NUMBER:

TWA	D	227	*	035	□	B	S	Z	0	0	00
Type	Case Size	Capacitance Code pF code: 1st two digits represent significant figures 3rd digit represents multiplier (number of zeros to follow)	Capacitance Tolerance K = ±10% M = ±20%	Voltage Code	Insulation Sleeve C = Without Sleeve S = With Sleeve	Packaging B = Tray Pack	Inspection Level S = Std. Conformance D = DSCC L = Group A	Reliability Z = Non-ER	Qualification Level 0 = COTS-Plus 9 = SRC9000	Termination Finish 0 = Sn/Pb 60/40	Custom Test Options 00 = Standard

DSCC PART IDENTIFICATION NUMBER (PIN):

93026	-XX	*	□
Drawing Number	Dash Number See Rating Tables	Capacitance Tolerance K = ±10% M = ±20%	Insulation Sleeve U = Without Sleeve S = With Sleeve

SPACE LEVEL OPTIONS TO SRC9000*:

TWA	D	227	*	035	□	B	L	Z	9	0	00
Type	Case Size	Capacitance Code pF code: 1st two digits represent significant figures 3rd digit represents multiplier (number of zeros to follow)	Capacitance Tolerance M = ±20% K = ±10%	Voltage Code	Insulation Sleeve C = Without Sleeve S = With Sleeve	Packaging B = Tray Pack	Inspection Level L = Group A	Reliability Z = Non-ER	Qualification Level 9 - SRW9000	Termination Finish 0 = Sn/Pb 60/40	Custom Test Options 00 = Standard

* Check with factory for availability and testing details

RIPPLE CURRENT MULTIPLIERS vs. Frequency, temperature and applied voltage^{1/2/}

Frequency of Applied Ripple Current		120Hz				800Hz				1kHz			
Ambient Still Air Temperature (°C)		≤55	85	105	125	≤55	85	105	125	≤55	85	105	125
% of 85°C	100%	0.60	0.39	—	—	0.71	0.43	—	—	0.72	0.45	—	—
	90%	0.60	0.46	—	—	0.71	0.55	—	—	0.72	0.55	—	—
Rated Peak	80%	0.60	0.52	0.35	—	0.71	0.62	0.42	—	0.72	0.62	0.42	—
	70%	0.60	0.58	0.44	—	0.71	0.69	0.52	—	0.72	0.70	0.52	—
Voltage	66-2/3%	0.60	0.60	0.46	0.27	0.71	0.71	0.55	0.32	0.72	0.72	0.55	0.32

Frequency of Applied Ripple Current		10kHz				40kHz				100kHz			
Ambient Still Air Temperature (°C)		≤55	85	105	125	≤55	85	105	125	≤55	85	105	125
% of	100%	0.88	0.55	–	–	1.00	0.63	–	–	1.10	0.69	–	–
85°C	90%	0.88	0.67	–	–	1.00	0.77	–	–	1.10	0.85	–	–
Rated	80%	0.88	0.76	0.52	–	1.00	0.87	0.59	–	1.10	0.96	0.65	–
Peak	70%	0.88	0.85	0.64	–	1.00	0.97	0.73	–	1.10	1.07	0.80	–
Voltage	66-2/3%	0.88	0.88	0.68	0.40	1.00	1.00	0.77	0.45	1.10	1.10	0.85	0.50

1/ At 125°C the rated voltage of the capacitors decreases to 66 2/3 of the 85°C rated voltage.

2/ The peak of the applied ac ripple voltage plus the applied dc voltage must not exceed the dc voltage rating of the capacitors.



TWA Series – DSCC 93026



TWA Wet Electrolytic Tantalum Capacitor

RATINGS & PART NUMBER REFERENCE

AVX Part Number	DSCC Part Number	Cap (µF) 25°C at 120Hz	DC Rated Voltage (V) at 85°C	ESR max (ohms) at 120Hz	DC Leakage max (µA)		Impedance max (Ohms) -55°C at 120Hz	Maximum Capacitance Change (%)			AC Ripple (mA rms) 85°C at 40kHz	Case Size	
					+25°C	+85°C & 125°C		-55°C	+85°C	+125°C		AVX	DSCC
25 VDC at 85°C 15 VDC at 125°C													
TWAA127*025□BSZ0000	93026- 29*□	120	25	1.3	1	5	25	-42	8	12	1250	A	T1
TWAB567*025□BSZ0000	93026- 30*□	560	25	0.83	2	10	12	-65	10	15	2100	B	T2
TWAD128*025□BSZ0000	93026- 31*□	1200	25	0.65	5	20	7	-70	12	18	2600	D	T3
TWAE188*025□BSZ0000	93026- 32*□	1800	25	0.5	6	25	7	-75	12	20	3100	E	T4
TWAE228*025□BSZ0000	93026- 64*□	2200	25	0.5	10	80	10	-90	30	50	3200	E	T4
30 VDC at 85°C 20 VDC at 125°C													
TWAA107*030□BSZ0000	93026- 33*□	100	30	1.3	1	5	25	-38	8	12	1200	A	T1
TWAB477*030□BSZ0000	93026- 34*□	470	30	0.85	2	10	15	-65	10	18	1800	B	T2
TWAD108*030□BSZ0000	93026- 35*□	1000	30	0.7	7	25	7	-70	10	18	2500	D	T3
TWAE158*030□BSZ0000	93026- 36*□	1500	30	0.6	12	35	6	-72	10	20	3000	E	T4
50 VDC at 85°C 30 VDC at 125°C													
TWAA686*050□BSZ0000	93026- 37*□	68	50	1.5	1	5	35	-25	8	15	1050	A	T1
TWAB227*050□BSZ0000	93026- 38*□	220	50	0.9	2	10	17.5	-50	8	15	1800	B	T2
TWAD477*050□BSZ0000	93026- 39*□	470	50	0.75	3	25	10	-50	8	15	2100	D	T3
TWAE687*050□BSZ0000	93026- 40*□	680	50	0.7	5	40	8	-58	10	20	2750	E	T4
60 VDC at 85°C 40 VDC at 125°C													
TWAA476*060□BSZ0000	93026- 41*□	47	60	2	1	5	44	-25	8	12	1050	A	T1
TWAB157*060□BSZ0000	93026- 42*□	150	60	1.1	2	10	20	-40	8	15	1650	B	T2
TWAD397*060□BSZ0000	93026- 43*□	390	60	0.9	3	25	15	-60	8	15	2100	D	T3
TWAE567*060□BSZ0000	93026- 44*□	560	60	0.8	5	40	10	-58	8	15	2750	E	T4
TWAE108*060□BSZ0000	93026- 65*□	1000	60	1	12	90	20	-90	30	50	3200	E	T4
75 VDC at 85°C 50 VDC at 125°C													
TWAA336*075□BSZ0000	93026- 45*□	33	75	2.5	1	5	66	-25	5	9	1050	A	T1
TWAB117*075□BSZ0000	93026- 46*□	110	75	1.3	2	10	24	-35	6	10	1650	B	T2
TWAD337*075□BSZ0000	93026- 47*□	330	75	1	3	30	12	-45	6	10	2100	D	T3
TWAE477*075□BSZ0000	93026- 48*□	470	75	0.9	5	50	12	-55	6	10	2750	E	T4
100 VDC at 85°C 65 VDC at 125°C													
TWAA156*100□BSZ0000	93026- 49*□	15	100	3.5	1	5	125	-18	3	10	1050	A	T1
TWAB686*100□BSZ0000	93026- 50*□	68	100	2.1	2	10	37	-30	4	12	1650	B	T2
TWAD157*100□BSZ0000	93026- 51*□	150	100	1.6	3	25	22	-35	6	12	2100	D	T3
TWAE227*100□BSZ0000	93026- 52*□	220	100	1.2	5	50	15	-40	6	12	2750	E	T4
125 VDC at 85°C 85 VDC at 125°C													
TWAA106*125□BSZ0000	93026- 53*□	10	125	5.5	1	5	175	-15	3	10	1050	A	T1
TWAB476*125□BSZ0000	93026- 54*□	47	125	2.3	2	10	47	-25	5	12	1650	B	T2
TWAD107*125□BSZ0000	93026- 55*□	100	125	1.8	3	25	35	-35	5	12	2100	D	T3
TWAE157*125□BSZ0000	93026- 56*□	150	125	1.6	5	50	20	-35	6	12	2750	E	T4

All technical data relates to an ambient temperature of +25°C. Capacitance and DF are measured at 120Hz, 0.5RMS with DC bias of 2.2V. DCL is measured at rated voltage after 5 minutes.

NOTE: AVX reserves the rights to supply higher voltage rating in the same case size, to the same reliability standards.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Kyocera AVX:

TWAE687K050CBDZ0000	TWAE227K100CBDZ0000	TWAD157K100CBDZ0000	TWAB157K060SBDZ0000
TWAA476K060SBDZ0000	TWAE567K060CBDZ0000	TWAA127K025CBDZ0000	TWAA686K050SBDZ0000
TWAB476K125CBDZ0000	TWAE477K075CBDZ0000	TWAE157K125SBDZ0000	TWAD337K075CBDZ0000
TWAE157K125CBDZ0000	TWAB117K075CBDZ0000	TWAB567K025SBDZ0000	TWAB227K050CBDZ0000
TWAE567K060SBDZ0000	TWAA336K075SBDZ0000	TWAE477K075SBDZ0000	TWAA107K030SBDZ0000
TWAA336M075SBDZ0000	TWAA686M050SBDZ0000	TWAB227M050SBDZ0000	TWAB476K125SBDZ0000
TWAB686K100SBDZ0000	TWAD108K030SBDZ0000	TWAD337M075SBDZ0000	TWAD397K060SBDZ0000
TWAE108K060SBDZ0000	TWAE108M060CTS0000	TWAE157M125SBDZ0000	TWAE158K030SBDZ0000
TWAE687K050SBDZ0000	TWAE227M100SBDZ0000	TWAD477M050SBDZ0000	TWAB117K075SBDZ0000
TWAB227K050SBDZ0000	TWAD107K125SBDZ0000	TWAD128K025SBDZ0000	TWAD157K100SBDZ0000
TWAD337K075SBDZ0000	TWAD477K050SBDZ0000	TWAE227K100SBDZ0000	TWAA106K125CBDZ0000
TWAA106K125SBDZ0000	TWAB157K060CBDZ0000	TWAB686M100SBDZ0000	TWAD107K125CBDZ0000
TWAD108K030CBDZ0000	TWAD108M060SBDZ0000	TWAD128K025CBDZ0000	TWAD397K060CBDZ0000
TWAD397M060SBDZ0000	TWAD477K050CBDZ0000	TWAE108K060CBDZ0000	TWAE108M060CBDZ0000
TWAE128K050CBDZ0000	TWAE156K030CBDZ0000	TWAE158K030CBDZ0000	TWAE188K025CBDZ0000
TWAE228K025CBDZ0000	TWAE228K025CBSD0000	TWAE228M025SBDZ0000	TWAE477M075CBDZ0000
TWAE567M060SBDZ0000	TWAE687M050SBDZ0000	TWAA476M060SBDZ0000	TWAB477K030SBDZ0000
TWAA127K025SBDZ0000	TWAE228K025SBDZ0000	TWAA476K060CBDZ0000	TWAD107M125SBDZ0000
TWAA686K050CBDZ0000	TWAB686K100CBDZ0000	TWAE227M100CBDZ0000	TWAA107K030CBDZ0000
TWAA336K075CBDZ0000	TWAA106M125SBDZ0000	TWAE477M075SBDZ0000	TWAE188K025SBDZ0000
TWAB477K030CBDZ0000	TWAB567K025CBDZ0000	TWAB476M125SBYZ0700	TWAB476M125SBDZ0000
TWAD157M100SBDZ0000	TWAD128M025CBDZ0000	TWAE337K125CBXZ0700	TWAE337M125SBSZ0000
TWAD397M060SBEZ0000	TWAE227K075SBXZ0000	TWAB477K030SBSZ0000	TWAE227M075SBXZ0000
TWAE227K075CBXZ0000	TWAE227M075CBXZ0000	TWAB477M030SBDZ0000	TWAE337K125SBSZ0000
TWAD826K125SBYZ0700			