N-channel 60 V, 1.9 mΩ typ., 120 A, STripFET™ F7 Power MOSFET in a PowerFLAT™ 5x6 package



PowerFLAT™ 5x6



Features

Order code	V_{DS}	$R_{DS(on)}$ max.	I_D
STL180N6F7	60 V	2.4 mΩ	120 A

- Among the lowest $R_{DS(on)}$ on the market
- Excellent FoM (figure of merit)
- Low C_{rss}/C_{iss} ratio for EMI immunity
- High avalanche ruggedness

Applications

- Switching applications

Description

This N-channel Power MOSFET utilizes STripFET™ F7 technology with an enhanced trench gate structure that results in very low on-state resistance, while also reducing internal capacitance and gate charge for faster and more efficient switching.

Product status link
STL180N6F7

Product summary	
Order code	STL180N6F7
Marking	180N6F7
Package	PowerFLAT™ 5x6
Packing	Tape and reel

1 Electrical ratings

Table 1. Absolute maximum ratings

Symbol	Parameter	Value	Unit
V_{DS}	Drain-source voltage	60	V
V_{GS}	Gate-source voltage	±20	V
I_D[(1)]	Drain current (continuous) at T_C = 25 °C	120	A
	Drain current (continuous) at T_C = 100 °C	120	A
I_{DM}[(1)(2)]	Drain current (pulsed)	480	A
I_D[(3)]	Drain current (continuous) at T_{pcb} = 25 °C	32	A
	Drain current (continuous) at T_{pcb} = 100 °C	20	A
I_{DM}[(2)(3)]	Drain current (pulsed)	128	A
P_{TOT}[(1)]	Total power dissipation at T_C = 25 °C	166	W
P_{TOT}[(3)]	Total power dissipation at T_{pcb} = 25 °C	4.8	W
T_j	Operating junction temperature range	-55 to 175	°C
T_{stg}	Storage temperature range		

1. *This value is rated according to $R_{thj\text{-}c}$ and limited by package.*
2. *Pulse width limited by safe operating area.*
3. *This value is rated according to $R_{thj\text{-}pcb}$.*

Table 2. Thermal data

Symbol	Parameter	Value	Unit
$R_{thj\text{-}pcb}$[(1)]	Thermal resistance junction-pcb	31.3	°C/W
$R_{thj\text{-}case}$	Thermal resistance junction-case	0.9	°C/W

1. *When mounted on FR-4 board of 1 inch², 2oz Cu, t < 10 s.*

2 Electrical characteristics

(T_C = 25 °C unless otherwise specified)

Table 3. On/off states

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
$V_{(BR)DSS}$	Drain-source breakdown voltage	I_D = 1 mA, V_{GS} = 0 V	60			V
I_{DSS}	Zero gate voltage drain current	V_{GS} = 0 V, V_{DS} = 60 V			1	µA
I_{GSS}	Gate-body leakage current	V_{GS} = 20 V, V_{DS} = 0 V			100	nA
$V_{GS(th)}$	Gate threshold voltage	V_{DS} = V_{GS}, I_D = 250 µA	2		4	V
$R_{DS(on)}$	Static drain-source on-resistance	V_{GS} = 10 V, I_D = 16 A		1.9	2.4	mΩ

Table 4. Dynamic

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
C_{iss}	Input capacitance	V_{DS} = 25 V, f = 1 MHz, V_{GS} = 0 V	-	4825	-	pF
C_{oss}	Output capacitance		-	2240	-	pF
C_{rss}	Reverse transfer capacitance		-	216	-	pF
Q_g	Total gate charge	V_{DD} = 30 V, I_D = 32 A, V_{GS} = 0 to 10 V (see Figure 13. Test circuit for gate charge behavior)	-	79.5	-	nC
Q_{gs}	Gate-source charge		-	24.2	-	nC
Q_{gd}	Gate-drain charge		-	24.1	-	nC

Table 5. Switching times

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
$t_{d(on)}$	Turn-on delay time	V_{DD} = 30 V, I_D = 16 A, R_G = 4.7 Ω, V_{GS} = 10 V (see Figure 12. Test circuit for resistive load switching times and Figure 17. Switching time waveform)	-	33.9	-	ns
t_r	Rise time		-	35.6	-	ns
$t_{d(off)}$	Turn-off delay time		-	68.9	-	ns
t_f	Fall time		-	42.2	-	ns

Table 6. Source-drain diode

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
V_{SD} (1)	Forward on voltage	I_{SD} = 32 A, V_{GS} = 0 V	-		1.2	V
t_{rr}	Reverse recovery time	I_D = 32 A, di/dt = 100 A/µs, V_{DD} = 48 V (see Figure 14. Test circuit for inductive load switching and diode recovery times)	-	60.3		ns
Q_{rr}	Reverse recovery charge		-	72.4		nC
I_{RRM}	Reverse recovery current		-	2.4		A

1. *Pulsed: pulse duration = 300 µs, duty cycle 1.5%*

2.1 Electrical characteristics (curves)

Figure 1. Safe operating area



Figure 2. Thermal impedance



Figure 3. Output characteristics



Figure 4. Transfer characteristics



Figure 5. Gate charge vs gate-source voltage



Figure 6. Static drain-source on-resistance



Figure 7. Capacitance variations



Figure 8. Normalized gate threshold voltage vs temperature



Figure 9. Normalized on-resistance vs temperature



Figure 10. Normalized $V_{(BR)DSS}$ vs temperature



Figure 11. Source-drain diode forward characteristics



3 Test circuits

Figure 12. Test circuit for resistive load switching times



Figure 13. Test circuit for gate charge behavior



Figure 14. Test circuit for inductive load switching and diode recovery times



Figure 15. Unclamped inductive load test circuit



Figure 16. Unclamped inductive waveform



Figure 17. Switching time waveform



4 Package information

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK® packages, depending on their level of environmental compliance. ECOPACK® specifications, grade definitions and product status are available at: www.st.com. ECOPACK® is an ST trademark.

4.1 PowerFLAT™ 5x6 type C package information

Figure 18. **PowerFLAT™ 5x6 type C package outline**



8231817_typeC_A0ER_Rev17

Table 7. PowerFLAT™ 5x6 type C package mechanical data

Dim.	mm		
	Min.	Typ.	Max.
A	0.80		1.00
A1	0.02		0.05
A2		0.25	
b	0.30		0.50
C	5.80	6.00	6.20
D	5.00	5.20	5.40
D2	4.15		4.45
D3	4.05	4.20	4.35
D4	4.80	5.00	5.20
D5	0.25	0.40	0.55
D6	0.15	0.30	0.45
e		1.27	
E	5.95	6.15	6.35
E2	3.50		3.70
E3	2.35		2.55
E4	0.40		0.60
E5	0.08		0.28
E6	0.20	0.325	0.45
E7	0.75	0.90	1.05
K	1.05		1.35
L	0.725		1.025
L1	0.05	0.15	0.25
θ	0°		12°

Figure 19. PowerFLAT™ 5x6 recommended footprint (dimensions are in mm)



8231817_FOOTPRINT_simp_Rev_17

4.2 PowerFLAT™ 5x6 packing information

Figure 20. **PowerFLAT™ 5x6 tape (dimensions are in mm)**



Ao	6.30 +/– 0.1
Bo	5.30 +/– 0.1
Ko	1.20 +/– 0.1
F	5.50 +/– 0.1
P1	8.00 +/– 0.1
W	12.00 +/– 0.3

(I) Measured from centreline of sprocket hole to centreline of pocket.

(II) Cumulative tolerance of 10 sprocket holes is ±0.20.

(III) Measured from centreline of sprocket hole to centreline of pocket

Base and bulk quantity 3000 pcs
All dimensions are in millimeters

8234350_Tape_rev_C

Figure 21. **PowerFLAT™ 5x6 package orientation in carrier tape**



Figure 22. **PowerFLAT™ 5x6 reel**



All dimensions are in millimeters

8234350_Reel_rev_C

Revision history

Table 8. **Document revision history**

Date	Revision	Changes
15-Nov-2017	1	Initial release
12-Dec-2018	2	Removed maturity status indication from cover page. Updated Section 2 Electrical characteristics and Section 4 Package information. Added Section 2.1 Electrical characteristics (curves). Minor text changes

Contents

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

STMicroelectronics:

STL180N6F7