



The RFE2500 AC-DC industrial power supplies are high efficiency and 1U in height. They have internal ORing MOSFETs and current share for parallel operation. Communication is possible with the power supplies using the optional isolated PMBus™ (I²C) interface. AC fail, DC good, remote output adjust, remote on/off and a 12V auxiliary output are fitted as standard.

Features	Benefits
• Internal ORing FETs and Current Share	• Suitable For N+1 Redundancy
• Up to 2500W in 1U Height	• Utilizes Less System Space
• Full Array of Signals Available	• Easy Remote Monitoring
• PMBus™ (I ² C) and LAN options	• Industry Standard Communication Interfaces
• Analog Output Adjustment	• Simple External Resistance or Voltage Connection

Model Selector						
Model	Output Voltage (V)	Adjustment Range (V) ⁽¹⁾	Max Current (A) (Vin>180Vac) ⁽²⁾	Max Power (W) (Vin>180Vac) ⁽²⁾	Max Current (A) (100<Vin<170Vac) ⁽²⁾	Max Power (W) (100<Vin<170Vac) ⁽²⁾
RFE2500-12	12	9.6 - 13.2	200	2400	125	1500
RFE2500-24	24	19.2 - 29	96	2304	62.5	1500
RFE2500-48	48	38.4 - 58	52	2496	31.25	1500

RFE2500-	12	/	S
	Output voltage 12, 24, 48		blank No PMBus™ / I ² C S PMBus™ / I ² C interface

Specifications

Model		RFE2500-12	RFE2500-24	RFE2500-48
Input				
AC Input Voltage Range (Operating)	Vac	85 - 265. See model selector for power derating ⁽²⁾		
Nominal Input Voltage Range	Vac	100 - 240 (Note: Safety certified for 90-264Vac)		
Input Frequency	Hz	47 - 63 (Note: Safety certified for 50/60Hz only)		
Input Current (Max) (110/230Vac)	A	15 / 12		
Inrush Current	A	<50		
Leakage Current	mA	Less than 0.8 / 1.6 at 115/230Vac, 60Hz		
Power Factor Correction	-	Meets EN61000-3-2, PF >0.98 at full load		
Harmonic Compliance	-	Meets IEC61000-3-2		
Hold Up Time	ms	>10, 100/230Vac Input, 80% loading		
Efficiency	%	90 / 92	90 / 92	91 / 93
Conducted EMI	-	Built to meet EN55032 Class B, FCC part 15 Class-B, VCCI Class-B		
Radiated EMI	-	Built to meet EN55032 Class A, FCC part 15 Class-A, VCCI Class-A		
Immunity	-	See immunity section		
Safety Certifications and Markings	-	IEC/UL/CSA/EN62368-1, 60950-1, CE Mark and UKCA Mark		

Immunity

Test	Standard	Test Level	Criteria	Notes
ESD	EN61000-4-2	2,3	B	See immunity data on website
Radiated Susceptibility	EN61000-4-3	2	A	
Electrical Fast Transient Burst	EN61000-4-4	2	B	
Surge	EN61000-4-5	3,4	B	
Conducted Susceptibility	EN61000-4-6	2	A	
Magnetic Fields	EN61000-4-8	4	A	
Voltage Dips / Interruptions	EN61000-4-11	>95% for 0.5 cycles 30% for 25/30 cycles >95% for 250/300 cycles	B B B	

Specifications

Model		RFE2500-12	RFE2500-24	RFE2500-48
Output				
Line Regulation	mV	30	60	120
Load Regulation	mV	60	120	240
External Load Capacitance	uF/A	1000		
Ripple & Noise	mV	240	240	480
Temperature Coefficient	%/°C	<0.02		
Minimum Load	-	No minimum load required		
Overcurrent Protection	%	115Vac: >110%; 230Vac: 105 - 120%		
Overvoltage Protection (1)	%	110 (Tracking). Cycle AC to reset or utilize Remote On/Off		
Overtemperature Protection	-	Shutdown with automatic reset. Warning signal provided ⁽¹⁾		
Remote Sense Compensation	V/wire	0.25	0.5	1.0
Remote On/Off	-	Yes, inhibit & enable		
AC Fail Signal	-	Open Collector, ON when AC is within 85-270Vac		
DC Good Signal	-	Open Collector, ON when output is above 85 to 95% of setpoint (tracking)		
Communication	-	Optional isolated PMBus™ (I ² C) interface (/S suffix) or plug-in LAN module. See model selectors		
Auxiliary Output	-	11.2 - 12.5V, 0.5A, 240mV ripple and noise		
Indicators	-	AC OK: Green LED, DC OK / Fail: Green / Red LED		
Parallel Operation	-	Yes, single wire current share, 5% accuracy of max current, up to 8 units		

RFE2500-48

-10 to +50: 100% load; +50 to +60 derate: 2%/°C of load; +60 to +70 derate: 2.5%/°C of load.
For models with reverse air contact factory.

-30 to +85

Operating: 10 - 90, Storage: 10 - 95

Internal variable speed fans. Airflow enters from the front. Contact factory for reverse airflow option.

3000 max. Derate output current 2%/100m above 2000m.

Output to Output 3kVac Input to Ground 2kVac Output to Ground

ac	500Vac	220
----	--------	-----

0 at 25°

Meets IEC61068 2.61 (Basic Transportation)

Meets IEC61066-2-04 (Basic Transportation)

Meets IEC61068-2-27 (Basic Transportation)

2.500

345 x 107 x 41

13.6 x 4.21 x 1.61

Isolated from output, Add suffix /S, PMBus™ compatible

208,356

3

(2) Derate 1.3%/Vac from 100Vac to 85Vac input

PIN #	FUNCTION
1	A0 (PMBus)
2	A1 (PMBus)
3	A2 (PMBus)
4	-SENSE
5	SMB_ALERT (PMBus)
6	SDA (PMBus)
7	SCL (PMBus)
8	SIGNAL RTN



TDK-Lambda France SAS

Tel: +33 1 60 12 71 65
tlf.fr-powersolutions@tdk.com
www.emea.lambda.tdk.com/fr



Italy Sales Office

Tel: +39 02 61 29 38 63
tlf.it-powersolutions@tdk.com
www.emea.lambda.tdk.com/it



Netherlands

tlf.nl-powersolutions@tdk.com
www.emea.lambda.tdk.com/nl



TDK-Lambda Germany GmbH

Tel: +49 7841 666 0
tlg.powersolutions@tdk.com
www.emea.lambda.tdk.com/de



Austria Sales Office

Tel: +43 2256 655 84
tlg.at-powersolutions@tdk.com
www.emea.lambda.tdk.com/at



Switzerland Sales Office

Tel: +41 44 850 53 53
tlg.ch-powersolutions@tdk.com
www.emea.lambda.tdk.com/ch



Nordic Sales Office

Tel: +45 8853 8086
tlg.dk-powersolutions@tdk.com
www.emea.lambda.tdk.com/dk



TDK-Lambda UK Ltd.

Tel: +44 (0) 12 71 85 66 66
tlu.powersolutions@tdk.com
www.emea.lambda.tdk.com/uk



TDK-Lambda Ltd.

Tel: +9 723 902 4333
tli.powersolutions@tdk.com
www.emea.lambda.tdk.com/il-en



TDK-Lambda Americas

Tel: +1 800-LAMBDA-4 or 1-800-526-2324
tla.powersolutions@tdk.com
www.us.lambda.tdk.com



TDK Electronics do Brasil Ltda

Tel: +55 11 3289-9599
sales.br@tdk-electronics.tdk.com
www.tdk-electronics.tdk.com/en



TDK-Lambda Corporation

Tel: +81-3-6778-1113
www.jp.lambda.tdk.com



TDK-Lambda (China) Electronics Co. Ltd.

Tel: +86 21 6485-0777
tlc.powersolutions@tdk.com
www.lambda.tdk.com.cn



TDK-Lambda Singapore Pte Ltd.

Tel: +65 6251 7211
tts.marketing@tdk.com
www.sg.lambda.tdk.com



TDK India Private Limited, Power Supply Division

Tel: +91 80 4039-0660
mathew.philip@tdk.com
www.sg.lambda.tdk.com



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TDK-Lambda:](#)

[RFE250012/S](#) [RFE250012](#) [RFE250048](#) [RFE250048/S](#) [RFE250024](#) [RFE250024/S](#)