


# **STPS8H100**

# High voltage power Schottky rectifier

Datasheet - production data



### **Features**

- Negligible switching losses •
- High junction temperature capability •
- Low leakage current •
- Good trade off between leakage current and • forward voltage drop
- Insulated package:
  - TO-220FPAC, insulating voltage = 2000 VRMS sine
- Avalanche capability specified •
- ECOPACK<sup>®</sup>2 compliant component for • D<sup>2</sup>PAK on demand

### Description

Schottky barrier rectifier designed for high frequency compact switched mode power supplies such as adaptors and on-board DC-DC converters.

### **Table 1: Device summary**

Symbol	Value
I <sub>F(AV)</sub>	8 A
Vrrm	100 V
T <sub>i</sub> (max)	175 °C
V <sub>F</sub> (typ)	0.56 V

December 2015

DocID5387 Rev 12

1/14

This is information on a product in full production.

# 1 Characteristics

Table 2: Absolute ratings (limiting values, at 25 °C, unless otherwise specified)

Symbol	Parameter			Value	Unit
Vrrm	Repetitive peak rev	erse voltage		100	V
I <sub>F(RMS)</sub>	Forward rms currer	nt		30	Α
	Average forward	TO-220AC, D <sup>2</sup> PAK	TO-220AC, D <sup>2</sup> PAK T <sub>c</sub> = 165 °C		
( )	current δ = 0.5, square wave	TO-220FPAC	T <sub>C</sub> = 150 °C	8	A
IFSM	Surge non repetitive forward current	tp = 10 ms sinusoidal		250	А
Parm	Repetitive peak avalanche power	tp = 10 μs, Τ <sub>j</sub> = 125 °C		750	W
T <sub>stg</sub>	Storage temperatur	emperature range		-65 to + 175	°C
Tj	Maximum operatino	m operating junction temperature <sup>(1)</sup>		+ 175	°C

#### Notes:

 $^{(1)}(dP_{tot}/dT_j) < (1/R_{th(j-a)})$  condition to avoid thermal runaway for a diode on its own heatsink.

#### **Table 3: Thermal parameter**

Symbol	Pa	Value	Unit	
Rth(j-c)	lunction to copp	TO-220AC, D <sup>2</sup> PAK	1.6	°C/W
	Junction to case	TO-220FPAC	4	

#### Table 4: Static electrical characteristics

Symbol	Parameter	Test conditions		Min.	Тур.	Max.	Unit
. (1)	Reverse leakage current	T <sub>j</sub> = 25 °C	N/ N/	-		4.5	μA
I <sub>R</sub> <sup>(1)</sup>		T <sub>j</sub> = 125 °C	Vr = Vrrm	-	2.0	6.0	mA
V <sub>F</sub> <sup>(2)</sup> F		T <sub>j</sub> = 25 °C	IF = 8 A	-		0.71	V
		T <sub>j</sub> = 125 °C		-	0.56	0.58	
		T <sub>j</sub> = 25 °C	- IF = 10 A -	-		0.77	
	Forward voltage drop	T <sub>j</sub> = 125 °C		0.59	0.64	v	
		$T_j = 25 \ ^{\circ}C$	L 16 A	-		0.81	
		T <sub>j</sub> = 125 °C	I <sub>F</sub> = 16 A	-	0.65	0.68	


#### Notes:


 $^{(1)}$ Pulse test: tp = 5 ms,  $\delta$  < 2%  $^{(2)}$ Pulse test: tp = 380 µs,  $\delta$  < 2%

To evaluate the conduction losses use the following equation:

 $P = 0.48 \ x \ I_{F(AV)} + 0.0125 \ I_{F^2(RMS)}$ 








57


DocID5387 Rev 12

3/14

#### Characteristics

#### STPS8H100








## 2 Package information

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK<sup>®</sup> packages, depending on their level of environmental compliance. ECOPACK<sup>®</sup> specifications, grade definitions and product status are available at: *www.st.com*. ECOPACK<sup>®</sup> is an ST trademark.

- Cooling method: by conduction (C)
- Epoxy meets UL 94,V0
- Recommended torque value: 0.55 N·m (for TO-220AC and TO-220FPAC)
- Maximum torque value: 0.7 N·m (for TO-220AC and TO-220FPAC)



## 2.1 D<sup>2</sup>PAK package information





This package drawing may slightly differ from the physical package. However, all the specified dimensions are guaranteed.




### STPS8H100

### Package information


00	Package information						
	Table 5:	D²PAK package me	chanical data				
		Dimensions					
Ref.	Millin	Millimeters		hes			
	Min.	Max.	Min.	Max.			
А	4.36	4.60	0.172	0.181			
A1	0.00	0.25	0.000	0.010			
b	0.70	0.93	0.028	0.037			
b2	1.14	1.70	0.045	0.067			
С	0.38	0.69	0.015	0.027			
c2	1.19	1.36	0.047	0.053			
D	8.60	9.35	0.339	0.368			
D1	6.90	8.00	0.272	0.311			
D2	1.10	1.50	0.043	0.060			
E	10.00	10.55	0.394	0.415			
E1	8.10	8.90	0.319	0.346			
E2	6.85	7.25	0.266	0.282			
е	2.54	typ.	0.1	00			
e1	4.88	5.28	0.190	0.205			
Н	15.00	15.85	0.591	0.624			
J1	2.49	2.90	0.097	0.112			
L	1.90	2.79	0.075	0.110			
L1	1.27	1.65	0.049	0.065			
L2	1.30	1.78	0.050	0.070			
R	0.4	typ.	0.0	15			
V2	0°	8°	0°	8°			







2.2 TO-220AC package information





### Package information

### STPS8H100


	Table 6: TO-220AC package mechanical data						
		Dimensions					
Ref.	Millin	neters	Ir	nches			
	Min.	Max.	Min.	Max.			
А	4.40	4.60	0.173	0.181			
С	1.23	1.32	0.048	0.051			
D	2.40	2.72	0.094	0.107			
E	0.49	0.70	0.019	0.027			
F	0.61	0.88	0.024	0.034			
F1	1.14	1.70	0.044	0.066			
G	4.95	5.15	0.194	0.202			
H2	10.00	10.40	0.393	0.409			
L2	16.40	D typ.	0.6	645 typ.			
L4	13.00	14.00	0.511	0.551			
L5	2.65	2.95	0.104	0.116			
L6	15.25	15.75	0.600	0.620			
L7	6.20	6.60	0.244	0.259			
L9	3.50	3.93	0.137	0.154			
М	2.6	typ.	0.1	02 typ.			
Diam	3.75	3.85	0.147	0.151			



2.3

TO-220FPAC package information







### Package information

### STPS8H100

ormation STPS8H100							
Table 7: TO-220FPAC package mechanical data							
		Dimensions					
Ref.	Milli	meters	Ir	nches			
	Min.	Max.	Min.	Max.			
A	4.4	4.6	0.173	0.181			
В	2.5	2.7	0.098	0.106			
D	2.5	2.75	0.098	0.108			
E	0.45	0.70	0.018	0.027			
F	0.75	1	0.030	0.039			
F1	1.15	1.70	0.045	0.067			
G	4.95	5.20	0.195	0.205			
G1	2.4	2.7	0.094	0.106			
Н	10	10.4	0.393	0.409			
L2	16	typ.	0.	63 typ.			
L3	28.6	30.6	0.126	1.205			
L4	9.8	10.6	0.386	0.417			
L5	2.9	3.6	0.114	0.142			
L6	15.9	16.4	0.626	0.646			
L7	9.00	9.30	0.354	0.366			
Dia.	3.00	3.20	0.118	0.126			



# **3** Ordering information

Order code	Marking	Package	Weight	Base qty	Delivery mode
STPS8H100D	STPS8H100D	TO-220AC	1.86g	50	Tube
STPS8H100FP	STPS8H100FP	TO-220FPAC	1.90g	50	Tube
STPS8H100G	STPS8H100G	D <sup>2</sup> PAK	1.48g	50	Tube
STPS8H100G-TR	STPS8H100G	D <sup>2</sup> PAK	1.48g	1000	Tape and reel

### Table 8: Ordering information

# 4 Revision history

#### Table 9: Document revision history

Date	Revision	Changes
Jul-2003	6D	Last update.
01-Jun-2006	10	Reformatted to current standard. Added ECOPACK statement. Changed nF to pF in Figure 11. Revision number set to 10 to align with on-line versioning.
08-Apr-2014	11	Updated D <sup>2</sup> PAK package information and Figure 2.
14-Dec-2015	12	Updated features in cover page. Minor text changes in Section 1: "Characteristics". Updated Section 2: "Package information".



### IMPORTANT NOTICE – PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2015 STMicroelectronics - All rights reserved



# **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

STMicroelectronics: <u>STPS8H100G-TR</u> <u>STPS8H100D</u> <u>STPS8H100FP</u>